

Specification Sheet

Part Number: CTT20R0HSM4

Heat stabilized cable ties provide excellent resistance to high heat exposures.

Head design contains clamping rails to provide full circumferential compression around bundles.

Bent tail allows for quick insertion into head.



Clamp Tie, 4" Long, 20lb Tensile Strength, PA66HS, Black, 1000/pkg

Article Number	112-51960
----------------	-----------

Type	CTT20R
------	--------

Color	Black (BK)
-------	------------

Quantity Per	pack
--------------	------

Product Description	The 360 degree compression ties are designed with underside clamping rails to allow for optimal surface contact and complete circumferential compression around the bundle. The bent tail design allows quick and simple installations by hand. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.
---------------------	--

Short Description	Clamp Tie, 4" Long, 20lb Tensile Strength, PA66HS, Black, 1000/pkg
-------------------	--

Global Part Name	CTT20R-PA66HS-BK
------------------	------------------

Minimum Tensile Strength (Imperial)	20
Minimum Tensile Strength (Metric)	89
Length L (Imperial)	4.0
Length L (Metric)	100
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.1
Width W (Metric)	2.5
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.6
Bundle Diameter Max (Imperial)	0.51
Bundle Diameter Max (Metric)	13.0
Thickness T (Imperial)	0.043
Thickness T (Metric)	1.1

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL ANSI/UL 62275 UL ANSI/UL 746B UL ANSI/UL 1565
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)