



Key-operated actuator, Flat Front, maintained, 2 positions, MS6, Key withdrawable: 0, I, Metal bezel

Part no. M30C-FWRS-MS6

187059

EL Number (Norway)

4315706

General specifications		
Product name		Eaton Moeller® series M30 Key-operated actuator
Part no.		M30C-FWRS-MS6
EAN		4015081821228
Product Length/Depth		36 millimetre
Product height		67 millimetre
Product width		46 millimetre
Product weight		0.06 kilogram
Certifications		IEC/EN 60947 VDE 0660 CSA certified DNV CE marking CSA file No. 012528 UL Category Control No.: NKCR CSA-C22.2 No. 94-91 GL CSA-C22.2 No. 14-05 UL 508 IEC/EN 60947-5 UL File No.: E29184 UL Listed CSA Class No.: 3211-03
Product Tradename		M30
Product Type		Key-operated actuator
Product Sub Type		None
Catalog Notes		Key withdraw convertible with coding adapters M22-XC-... Not suitable for master key systems
Features & Functions		
Bezel color		Titanium
Bezel material		Metal
Design		Key operation lock mechanism Flat front
Fitted with:		Front ring
Functions		Stay-put/spring-return function, can be changed with coding parts M22-XC-Y
Key code		MS6
General information		
Accessories		1 key included with supplied equipment.
Degree of protection		NEMA 4X, 13
Degree of protection (front side)		IP66
Lifespan, mechanical		100,000 Operations
Opening diameter		30 mm
Operating frequency		100 Operations/h
Operating torque		0.5 N·m
Overvoltage category		III
Pollution degree		3
Product category		RMQ-Titan
Size		Front dimensions: Ø 36 mm
Switching angle		60 °
Type		Key-operated button
Ambient conditions, mechanical		
Mounting position		As required
Shock resistance		15 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms Mechanical, According to IEC/EN 60068-2-27

Climatic environmental conditions		
Ambient operating temperature - min		-25 °C
Ambient operating temperature - max		70 °C
Climatic proofing		Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
Communication		
Connection to SmartWire-DT		With SWD-RMQ connections Yes
Actuator		
Actuator color		Black
Actuator function		Maintained Key withdrawable in position 1 Key withdrawable in position 0 Switching function latching
Actuator type		Key
Number of switch positions		2
Contacts		
Force for positive opening - min		0 N
Design verification		
Equipment heat dissipation, current-dependent Pvid		0 W
Heat dissipation capacity Pdis		0 W
Heat dissipation per pole, current-dependent Pvid		0 W
Rated operational current for specified heat dissipation (In)		0 A
Static heat dissipation, non-current-dependent Pvs		0 W
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Please enquire
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		Not applicable.
10.11 Short-circuit rating		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 9.0

Low-voltage industrial components (EG000017) / Front element for selector switch (EC000222)		
Electric engineering, automation, process control engineering / Low-voltage switch technology / Command and alarm device / Front element for selector switches (ecl@ss13-27-37-12-13 [AKF031019])		
Number of switch positions		2
Type of control element		Key
Suitable for illumination		No
Colour control element		Black
Colour indicator light cap		Other

Construction type lens		Round
Hole diameter	mm	30
Width opening	mm	0
Height opening	mm	0
Switching function latching		Yes
Spring-return		No
With front ring		Yes
Material front ring		Metal
Colour front ring		Titanium
Degree of protection (IP), front side		IP66
Degree of protection (NEMA)		4X, 13