



❗ Discontinued

Main

Range	EVlink
Product or component type	Charging station
Device application	Residential
Type of installation	Indoor
Mounting mode	Wall mount

Complementary

NEMA degree of protection	NEMA 1
Material	Enclosure plastic, white
[Us] rated supply voltage	240 V AC 60 Hz, single phase
Maximum supply current	30 A
Poles description	2P power circuit
Nominal output power	7.2 kW 30 A 208...240 V
Level or class	Level 2
Output type	Bottom of enclosure 1 black charging cable 18.04 ft (5.5 m) non retractable
Connector type	SAE J1772
Protection type	Ground fault protection CCID20 automatic test at the beginning of each charge cycle) Automatic restart after ground fault or main power loss
Control type	1 red illuminated push-button stop 1 orange illuminated push-button delay charging
Local signalling	Charging 8 green indicator light Delay start 8 green indicator light Power ON/fault detected 1 green/red indicator light
Height	12.72 in (323 mm)
Width	9.53 in (242 mm)
Depth	4.37 in (111 mm)
Net weight	17.00 lb(US) (7.71 kg)

Environment

Standards	CSA C22.2 UL 2594
Product certifications	FCC Class B

Packing Units

Package 1 Weight	19.03 lb(US) (8.632 kg)
------------------	-------------------------

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	---------------------------------------------------------------------------------------------------