

0512	2218	0703	0574
0512-0-15-XX-12-XX-04-0 Press-fit in 1,45 mounting hole	2218-0-15-XX-22-XX-10-0 Press-fit in 1,45 mounting hole	0703-0-15-XX-12-XX-04-0 Press-fit in 1,45 mounting hole	0574-0-15-XX-12-XX-04-0 Press-fit in 1,45 mounting hole
0468	0550	0671	0707
0468-0-15-XX-12-XX-04-0 Press-fit in 1,45 mounting hole	0550-0-15-XX-22-XX-10-0 Solder mount in 1,32 min. mounting hole	0671-0-15-XX-12-XX-10-0 Solder mount in 1,6 min. mounting hole	0707-0-15-XX-12-XX-10-0 Solder mount in 1,3 min. mounting hole
5739	8894	1534	
5739-0-18-XX-12-XX-10-0 Surface mount Also available on 16mm wide carrier tape: 3,000 parts per 330mm reel. Order as: 5739-0-58-XX-12-XX-10-0	8894-0-15-XX-12-XX-10-0 Hex press-fit in 1,5 plated thru hole	1534-0-15-XX-12-XX-04-0 Press-fit in 1,42 mounting hole	
SPECIFICATIONS SHELL MATERIAL: Brass Alloy 360, 1/2 Hard CONTACT MATERIAL: Beryllium Copper Alloy 172, HT PART MANUFACTURED IN INCHES, METRIC FOR REF ONLY TOLERANCES ON: LENGTHS: ± 0,13 DIAMETERS: ± 0,05 ANGLES: ± 2°	ORDER CODE: XXXX - X - 1X - XX - XX - XX - XX - 0 BASIC PART # _____ SPECIFY SHELL FINISH: _____ 01 5,08µm TIN/LEAD OVER NICKEL 80 5,08µm TIN OVER NICKEL 15 0,25µm GOLD OVER NICKEL SPECIFY CONTACT FINISH: _____ 02 2,54µm TIN/LEAD OVER NICKEL 84 2,54µm TIN OVER NICKEL 27 0,76µm GOLD OVER NICKEL SELECT CONTACT #12 or #22 CONTACT (DATA ON PAGE 207)		

