


PRODUCT NUMBER

10131780-R0017YYLF

WIRING LIST

COLOR	X2701	CN2
BLACK	1	1
RED	2	2
TWIST		
BLACK	3	3
RED	4	4
TWIST		
BLACK	5	5
RED	6	6
TWIST		



NOTES:

1. MATERIAL: SEE BOM ON SHEET 1.
2. THIS DIMENSION IS A FINISHED PRODUCT LENGTH.
3. ALL CABLE ASSEMBLIES SHALL BE TESTED 100% FOR CONTINUITY AS DEFINED IN WIRING LIST.
4. UNLESS OTHERWISE SPECIFIED ALL CABLE ASSEMBLIES SHALL BE TESTED:
HI-POT TESTED: DC 300V/10ms
DIELECTRIC RESISTANCE: 10M Ohms MIN.
CONNECTION RESISTANCE: 3 Ohms MAX.
5. LEAD FREE PRODUCTS MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

6. PACKAGE: LABEL SHOULD BE PRINTED WITH BLACK TEXT AS SHOW BELOW.
PUT THE LABEL ON THE PACKAGE BAG AND BOX.

A5E33679873
RS-AE/006 yywFCIN
10131780-R0017YYLF

---BARCODE READS 'yywFCIN'
'N' STANDS FOR NANTONG CITY

6	EA	TERMINAL: JST P/N: SSH-003T-P0.2-H	5
1	EA	HOUSING: 1.0PITCH, 8PIN, COLOR: WHITE P/N: SHR-08V-S-B	4
6	EA	TERMINAL: AICC P/N: 77138-101LF	3
1	EA	HOUSING: 2.0PITCH, 2*5PIN, COLOR: BLACK, AICC P/N: 90311-010LF	2
A/R	M	FLEXIBLE LITZ WIRE: AWG30, UL1061, BLACK/RED	1
Q'TY	UNIT	DESCRIPTION	ITEM
mat'l. code		surface <input checked="" type="checkbox"/> ISO 1302 <input checked="" type="checkbox"/> tolerance <input checked="" type="checkbox"/> ISO 406 <input checked="" type="checkbox"/> ISO 1101	projection
ltr	ecn no	dr	date
A	/	Carl	11/06'14
B	ELX-N-20951	Carl	05/25'15
C	ELX-N-22511	Carl	11/17'15
D	ELX-N-23070	Carl	01/19'16
E	ELX-N-24763	Carl	08/22'16
F	ELX-N-26899	Carl	05/04'17
G	ELX-N-28872	Carl	12/25'17
sheet index	revision sheet	G	1
product family		Cable Assembly	
title		CTW CABLE ASSEMBLY	
dwg no		sheet 1 of 1	size
10131780-R0017YYLF			A3
type		Customer	Drawing