

Part Number : 1200870236
Product Description : M8 Signal, A-Coded, Double-Ended Cordset, 3 Poles, Female (Straight) to Male (Straight), 0.34mm² (22 AWG), Yellow TPE Cable, 2.0m (6.56') Length
Series Number : 120087
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : 443030K05M020

Documents and Resources

Drawings

1200870236_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	120087
Description	M8 Signal, A-Coded, Double-Ended Cordset, 3 Poles, Female (Straight) to Male (Straight), 0.34mm² (22 AWG), Yellow TPE Cable, 2.0m (6.56') Length
IP Rating	IP67
Product Name	M8 Signal,Nano-Change (M8)
Type	Double Ended
UPC	78678887474

Agency

UL	E152210

Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	60V AC / 75V DC

Physical

Cable Diameter	5.00mm (.197")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Yellow
Connector End A	M8 Signal
Connector End B	M8 Signal
Coupling Style	Threaded
Gender	Female-Male

Downloaded from Arrow.com.

Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	288.000/g
Orientation	Straight to Straight
Poles	3
Temperature Range - Operating	-25° to +80°C
Wire/Cable Type	PLTC/ITC
Wire Size (AWG)	22

Downloaded from Arrow.com.