



Representative Image

Catalog No. L-11-40-9-D

Description: CABLE TIE 40LB 11 NAT NYLON 1-PC B

UPC No 728494933047

Home > Wire & Cable Management > Catamount > Cable ties

Intermediate Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 279mm (11 Inches), Width of 3.6mm (0.14 Inches), Thickness of 1.4mm (0.06 Inches), Bundle Diameter 2mm (0.08 Inches) to 69mm (2.72 Inches),Tensile Strength Rating of 178 Newtons (40 Pounds), Bulk Pack

Descriptors

Category	Cable ties
----------	------------

Specifications

Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Plastic Pawl
Tensile Strength	40 pounds , 178 newtons

Classifications

Brand Name	Catamount
Standard	UL E49405 UL E49405

Dimensions

Width	0.14 in , 3.6 mm
Length	11 in , 279 mm
Thickness	0.06 in , 1.4 mm
Bundle Diameter	0.08 to 2.72 in , 2 to 69 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000046 Cable tie
Band width	3.6 mm
Length belt/tape/tie	279 mm
Length belt/tape/tie	11 inch

by ABB

ETIM	EC000046 Cable tie
Tie thickness	1.4 mm
Tie thickness	0.06 inch
Max. bundle diameter	69 mm
Min. holding force	178 N
Operation temperature	-40-+85 °C
Operation temperature	-40-+185 °F
Model	Internal toothing
Band closure	Plastic lip/-cam
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N