






| REV. | DATE     | DESCRIPTION            |
|------|----------|------------------------|
| A    | 10/28/99 | MODIFY FERRULE PLATING |



RECOMMENDED  
CABLE STRIPPING DIM'S



|   |             |              |         |                                                                                                                                                                                                                                                  |           |        |                                                                                       |                                                                       |          |            |       |        |
|---|-------------|--------------|---------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------|--------|---------------------------------------------------------------------------------------|-----------------------------------------------------------------------|----------|------------|-------|--------|
|   | DESCRIPTION | MATERIAL     | FINISH  | UNLESS OTHERWISE SPECIFIED<br>DIMENSIONS ARE IN MILLIMETERS                                                                                                                                                                                      | APPROVALS | DATE   |  |                                                                       |          |            |       |        |
| 1 | BODY        | BRASS        | NICKEL  | DIMENSIONS IN [ ] ARE IN INCHES<br>FOR CUSTOMER REFERENCE ONLY<br><br>UNLESS OTHERWISE SPECIFIED<br>TOLERANCES FOR MILLIMETERS ARE:<br>0.5-6 = ± 0.2<br>6-30 = ± 0.4<br>30-120 = ± 0.6<br>120-315 = ± 1<br>315-1000 = ± 1.6<br>1000-2000 = ± 2.4 | DRAWN     | G.R.S. | 10/25/99                                                                              | TITLE<br>BNC STRAIGHT CRIMP JACK<br>(FOR RG-316/U DOUBLE BRAID CABLE) |          |            |       |        |
| 2 | INSULATOR   | DELRIN       | NATURAL |                                                                                                                                                                                                                                                  | CHECKED   |        |                                                                                       |                                                                       |          |            |       |        |
| 3 | CONTACT PIN | PHOS. BRONZE | GOLD    |                                                                                                                                                                                                                                                  | ISSUED    |        |                                                                                       |                                                                       |          |            |       |        |
| 4 | SLEEVE      | DELRIN       | NATURAL |                                                                                                                                                                                                                                                  |           |        |                                                                                       | SIZE                                                                  | FSCM NO. | DWG. NO.   | REV.  |        |
| 5 | FERRULE     | BRASS        | NICKEL  |                                                                                                                                                                                                                                                  |           |        |                                                                                       | A                                                                     | 99001    | 112529.DWG | A     |        |
| 6 |             |              |         |                                                                                                                                                                                                                                                  |           |        |                                                                                       |                                                                       |          |            |       |        |
| 7 |             |              |         |                                                                                                                                                                                                                                                  |           |        |                                                                                       |                                                                       |          |            |       |        |
| 8 |             |              |         | DO NOT SCALE DRAWING                                                                                                                                                                                                                             |           |        | SCALE                                                                                 | NA                                                                    | PART NO. | 112529     | SHEET | 1 OF 1 |