



Part Number : [734151630](#)
Product Description : MCX Jack, Straight, PCB
Receptacle, Surface Mount, Tri-Metal Plated, 100
Pieces Per Bag, 75 Ohms
Series Number : 73366
Status : Active
Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings

[734151630 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[PS-89675-183-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c); 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73366
Description	MCX Jack, Straight, PCB Receptacle, Surface Mount, Tri-Metal Plated, 100 Pieces Per Bag, 75 Ohms
Application	RF
Product Name	MCX
Style	PCB
Type	Microminiature
UPC	822348064335

Electrical

Frequency	6 GHz
Impedance	75Ω
Power / Voltage	VOLTAGE: 335 Vrms@Sea Level

Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	N/A
Net Weight	0.110/g
Orientation	Straight

Packaging Type	Bag
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	Surface Mount
PCB Thickness - Recommended	Various
Reverse Polar	No
Wire/Cable Type	N/A

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	REFLOW
Max-Cycle	2
Max-Temp	260

This document was generated on Sep 27, 2025