1SNA176705R0300 ✔ ACTIVE

ENTRELEC | ENTRELEC Miniblocks

TE Internal #: 1SNA176705R0300

Jumper Bar, 3 Pole, 5 mm [.196 in] Spacing, -55 – 110 °C [-67 – 230 °F], ENTRELEC Miniblocks

View on TE.com >

Connectors > Terminal Blocks & Strips > Terminal Block & Strip Accessories > Terminal Block & Strip Conducting Accessories



Conducting Accessory Type: **Jumper Bar**

Number of Poles: **3**

Product Spacing: **5 mm [.196 in]**

Contact Current Rating (Max): **24 A**

Operating Temperature Range: **-55 – 110 °C [-67 – 230 °F]**

Features

Product Type Features

Conducting Accessory Type	Jumper Bar

Configuration Features

Number of Poles	3

Contact Features

Contact Current Rating (Max)	24 A

Dimensions

Product Spacing	5 mm[.196 in]

Usage Conditions

Operating Temperature Range	-55 – 110 °C[-67 – 230 °F]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量超出标准 Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250)

Downloaded from Arrow.com.

	Candidate List Declared Against: JUNE 2025 (250) SVHC > Threshold: Pb (3.5% in Component) **Article Safe Usage Statements:** Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # 1SNA115510R1600
DR1.5/5




TE Part # 1SNA112086R0200
DR1.5/5.1

Also in the Series | ENTRELEC Miniblocks




Terminal Block & Strip Conducting Accessories(7)



Terminal Block & Strip Insulating Accessories(1)

Customers Also Bought


Downloaded from Arrow.com.



TE Part #1SNL900100R0000
EP5-6



TE Part #1SNK900001R0000
BAM4



TE Part #1SNA115490R1300
MA2.5/5.D2



TE Part #1SNL506410R0000
C4/6.SF

Documents

Product Drawings

BJMI5DR

English

Datasheets & Catalog Pages

BJMI5DR-3

English

ENTRELEC Terminal Block - Master Catalog

ENTRELEC Terminal Block - Master Catalog

English

ENTRELEC Terminal Blocks Catalogue (RUS)

Downloaded from Arrow.com.