



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INTIAL RELEASE	19JUN2015	DL	CW
	B	ECR-20-008190	09SEP2020	WQR	CW


















TYPE 1: BODY + STAINLESS STEEL LOCKING

TYPE 3: BODY + STAINLESS STEEL LOCKING
BOTTOM CUT OUT
OTHER SPEC REFER TO TYPE 1



TYPE 2: BODY + STAINLESS STEEL LOCKING
SILVER WHITE COATED
OTHER SPEC REFER TO TYPE 1

NOTES:
1. TECHNICAL CHARACTERISTICS:
   BODY MATERIAL: DIE CAST ALUMINIUM ALLOY
   SURFACE TREATMENT: POWDER-COATED, COLOR SEE TABLE
   DEGREE OF PROTECTION: IP65 (MATED)

注释：
1. 技术参数：
   主体材料： 铝合金
   表面处理： 粉末喷涂， 颜色见表格
   防护等级： IP65(配合)

ASSEMBLY PART NUMBER	TYPE	ASSEMBLY PART DESCRIPTION	COLOR	IG1	IG2
T1440161121-000	TYPE 1	H16B-SGRS-PG21	GRAY	PG21	-
T1440161125-000		H16B-SGRS-M25		M25	-
T1440161221-000		H16B-SGRS-2PG21		PG21	PG21
T1440161225-000		H16B-SGRS-2M25		M25	M25
T1440161121-100	TYPE 2	H16B-SGRS-PG21	SILVER WHITE	PG21	-
T1440160000-000	TYPE 3	H16B-SGRS-T	GRAY	-	-

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL -
-

FINISH -
-

DWN DAVID LI 19JUN2015
CHK CHRIS WANG 19JUN2015
APVD XU XIANG 19JUN2015
PRODUCT SPEC 108-137013
APPLICATION SPEC 114-137013
WEIGHT -

TE Connectivity

NAME H16B-SGRS-PG/M


SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	-	C-T144016XXXXX00	


CUSTOMER DRAWING | SCALE 1:1 | SHEET 1 OF 2 | REV B


Downloaded from Arrow.com.


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-


















TYPE 4: BODY + STEEL LOCKING
OTHER SPEC REFER TO TYPE 1

TYPE 6: BODY + STEEL LOCKING
BOTTOM 1 HOLE
OTHER SPEC REFER TO TYPE 4



TYPE 5: BODY+ STEEL LOCKING
FRONT/BACK 6 HOLE
OTHER SPEC REFER TO TYPE 4

ASSEMBLY PART NUMBER	TYPE	ASSEMBLY PART DESCRIPTION	COLOR	IG1	IG2	IG3	IG4
TI440162121-000	TYPE 4	HI6B-SGR-PG21	GRAY	PG21	-	-	-
TI440162125-000		HI6B-SGR-M25		M25	-	-	-
TI440162221-000		HI6B-SGR-2PG21		PG21	PG21	-	-
TI440162225-000		HI6B-SGR-2M25		M25	M25	-	-
TI440161625-000		HI6B-SGR-M25/PG16		M25	PG16	-	-
TI440162521-000		HI6B-SGR-M25/PG21		M25	PG21	-	-
TI440162532-000		HI6B-SGR-M25/M32		M25	M32	-	-
TI440162609-000	TYPE 5	HI6B-SGR-6PG9		-	-	PG9	-
TI440165125-000	TYPE 6	HI6B-SGR-TM25		-	-	-	M25

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN DAVID LI 19JUN2015
CHK CHRIS WANG 19JUN2015
APVD XU XIANG 19JUN2015

TE Connectivity

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

NAME HI6B-SGR-PG/M

PRODUCT SPEC 108-137013
APPLICATION SPEC 114-137013

MATERIAL - -
FINISH - -
WEIGHT -

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	-	C-TI44016XXXXX00	

CUSTOMER DRAWING | SCALE 4:5 | SHEET 2 OF 2 | REV B

Downloaded from Arrow.com.