



PRODUCT NB	DIM"C" & DIM"D"
95264-YXX(H)(LF)	SEE SHEET 2/2


WHEN NEEDED, SUFFIX LETTER "LF"
INDICATES THE PRODUCT IS RoHS
COMPATIBLE, SEE NOTE 5

EXAMPLE MISSING TERMINAL



SECTION A-A

(SEE NOTE 4)





SECTION B-B

NOTES:

- 1 - MATERIAL HOUSING: THERMOPLASTIC POLYESTER, 30% GLASS FILLED, COLOUR BLUE. FLAME RETARDANT PER UL-94 CATEGORY V0.
- 2 - MATERIAL TERMINAL: PHOSPHOR BRONZE EXTRA HARD.
- 3 - MATERIAL HOUSING VERSION HIGH TEMPERATURE: PCT 30% GLASS FILLED, COLOUR GREY. FLAME RETARDANT PER UL-94 CATEGORY V0.
- 4 - THE DASH "H" AT THE END OF THE P/N TO INDICATE A HIGH TEMPERATURE HOUSING.
- 5 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS
 - a - PLATING:
 - "LF" MEANS THE PRODUCT IS LEAD-FREE, 2µm MINIMUM MATTE TIN OVER 1.27µm MINIMUM NICKEL UNDERPLATE.
 - b - MANUFACTURING PROCESS COMPATIBILITY
 - THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C ±5°C SOLDER BATH TEMPERATURE FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.6mm MIN THICK CIRCUIT BOARD.
- 6 - LABELING:
 - MEETS PACKAGING SPECS AS PER GS-14-920
- d - LEGAL STATEMENT: SEE GS-22-008
- 6 - END STAND-OFFS FOR 2x2 UP TO 2X5 POS
NO END STAND-OFFS FOR 2x6 UP TO 2x50 POS

mat'l. code SEE NOTES				surface ISO 1902	tolerance ISO 406 ISO 101	projection mm	product family DX VCC DR
H	F80638	VMO	98.10.14	tolerances unless otherwise specified	±0.3	mm	title SPREADER LEGS
J	F20161	DLE	02.02.25	angles	linear	scale 10:1	.300 SELECT. LOADED
K	F04-0347	DLE	04.11.15	±2°			dwg no
L	F06-0137	DLE	06.02.27	dr	O. MATHEVON	96.06.07	sheet 1 of 2 size
M	F06-0204	DLE	06.06.28	engr	JM.PHAMVAN	96.06.07	A2
N	F06-0323	DLE	06.11.21	chr	P.NIZZI	96.06.07	95264
P	F11-0043	JCO	11.02.22	app	JM.P	96.06.07	type
sheet	revision	P	H				CUSTOMER Drawing
index	sheet	1	2				

PRODUCT N°	NB of POS.	DIM"C"	DIM"D"	CONTACT PLACED IN CAVITY (SEE VIEW "A")																			
				1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
95264—Y01(H)(LF)	2x10	22.86	25.32	X		X		X	X	X	X	X	X										
				X		X		X	X	X	X	X	X										
95264—Y02(H)(LF)	2x15	35.56	38.02	X		X		X		X		X		X	X	X	X	X	X				
				X		X		X		X		X		X	X	X	X	X	X				
95264—Y03(H)(LF)	2x11	35.56	38.02	X	X	X	X	X	X	X	X			X	X								
				X	X	X	X	X	X	X				X	X								
95264—Y04(H)(LF)	2x10	22.86	25.32	X		X		X	X	X	X	X	X	X									
				X		X		X	X	X	X	X	X	X									
95264—Y05(H)(LF)	2x4	7.62	10.08	X		X																	
				X	X			X															
95264—Y06(H)(LF)	2x5	10.16	12.62	X	X			X	X														
				X	X			X	X														
95264—Y07(H)(LF)	2x3	5.08	7.54	X		X																	
				X		X																	
95264—Y08(H)(LF)	2x7	15.24	17.7	X		X			X		X												
				X		X			X		X												
95264—Y09(H)(LF)	2x14	33.02	35.48	X	X	X	X	X	X	X	X	X	X				X	X					
				X	X	X	X	X	X	X	X	X	X				X	X					
95264—Y10(H)(LF)	2x20	48.26	50.72	X			X			X			X			X				X			X
				X			X			X			X			X			X				X



95264-6XX(H)	2µm Au MIN. OVER 1.3µm Ni MIN.	SnPb OVER Ni
95264-8XX(H)	0.4µm Au MIN. OVER 1.3µm Ni MIN.	SnPb OVER Ni
95264-4XX(H)	5µm SnPb MIN. OVER 0.1µm Ni MIN.	SnPb OVER Ni
95264-3XX(H)	0.75µm Au MIN. OVER 1.3µm Ni MIN.	SnPb OVER Ni
PLATING CODE	CONTACT AREA	SOLDER TAIL
PLATING EXPLANATION		

95264-6XX(H)LF	2µm Au MIN. OVER 1.3µm Ni MIN.	Sn OVER Ni
95264-8XX(H)LF	0.4µm Au MIN. OVER 1.3µm Ni MIN.	Sn OVER Ni
95264-4XX(H)LF	5µm Sn MIN. OVER 1.27µm Ni MIN.	Sn OVER Ni
95264-3XX(H)LF	0.75µm Au MIN. OVER 1.3µm Ni MIN.	Sn OVER Ni
PLATING CODE	CONTACT AREA	SOLDER TAIL
PLATING EXPLANATION		

CUSTOMER COPY FOR REFERENCE ONLY									
mat'l. code SEE NOTES				surface ISO 1302		tolerance ISO 406 ISO 1001		projection 1001	
lfr ecn no dr date				tolerances unless otherwise specified		mm		product family DX VCC DR	
H F06-0204 DLE 06.06.28				angles linear		±0.3		Title SPREAD LEGS .300 SELECT. LOADED	
C F70103 JMC 97.01.10 ±2°				scale 10:1		FCI		dwg no 95264	
D F70629 PNZ 97.09.25 dr P.NIZZI 96.10.23								sheet 2 of 2 size A2	
E F80638 VMO 98.10.14 engr J.M.PHAMVAN 96.10.23									
F F20161 DLE 02.02.25 chr P.NIZZI 96.10.23									
G F04-0347 DLE 04.11.15 app J.M.P 96.10.23								type CUSTOMER Drawing	
sheet index		revision							