










NOTE:

1.Material:

Terminal: Brass C2680-1/2H(HV120~140),T=0.2±0.02mm.

Shell : Brass C2680-EH(HV160~175),T=0.5±0.02mm.

Housing : LCP(E130I)+30%.G.F.(UL94-O),Black.

2.Plating:

Terminal: Au plated on contact area (see order information),
100u" Sn plated on solder tail area,
both over 50u" min. Ni underplated overall.

Shell : 100u"min. weldable Ni overall.

3.Mechanical Characteristics:

Insertion force : 4.5Kgf max.

Withdrawing force : 1Kgf ~ 4Kgf.

4.ELECTRICAL CHARACTERISTIC

Contact Resistance: 30m Ohm Max

Insulation Resistance: 100M Ohm Min(unmated)

Dielectric Withstanding Voltage: 500V AC Min

5.TEMPERATURE

Operating Temperature: -40°C~+85°C

Storage Temperature: -60°C~+105°C

2014/06/06	Jody		Structural changes		A1
2012/03/06	XIE		NEW DWG		A0
DATE	DR.BY	ECN.NO.	DESCRIPTION	MARK	VER.
-TOLERANCES- UNLESS OTHERWISE SPECIFIED			CnC Tech,LLC		
			TITLE: HDMI AF SMT 四脚DIP有耳		
X.X ±0.25	X.X* ±3.00*	APPD:	PRODUCT NO:2000-1-2-23-00-BK		
X.XX ±0.20	X.XX* ±1.00*	CHECK:	DATE	SCALE	UNIT TYPE PAGE
X.XXX ±0.15	X.XXX* ±0.500*	DRAW:	2017/10/12	1:1	mm Z 1/1