






A



B



PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)



C

TIN LEAD PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S24A.PV00
15	39.14	33.32	25.18	24.54	19.18	D15S24A.PV00
25	53.03	47.04	39.12	38.25	33.12	D25S24A.PV00
37	69.32	63.50	55.68	54.71	49.68	D37S24A.PV00

Plating: 4 --> flash AU
Plating: 6 --> 0.76μ AU

D

LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S24A.PV00LF
15	39.14	33.32	25.18	24.54	19.18	D15S24A.PV00LF
25	53.03	47.04	39.12	38.25	33.12	D25S24A.PV00LF
37	69.32	63.50	55.68	54.71	49.68	D37S24A.PV00LF

Plating: 4 --> flash AU
Plating: 6 --> 0.76μ AU

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0000

European Views

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101	projection 	mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED					
Dr	JOUBERT	1996/09/10	ANGULAR	LINEAR	0.X	±0.1	size	Scale
Eng	PESSON	1996/09/10			0.XX	±0.1	A3	2
Chr	LEGARE	1996/09/10			0.XX	±0.1	ECN	L506-0097
Appr	LEGARE	1996/09/10	Product family			D-SUB	Spec ref -	
			FEMALE CONNECTOR STD EURO			Rev.		
title			straight solder type for			D		
catalog no			-			CUSTOMER sheet 1 of 1		

rev	ecn no	dr	date
A	-	JOU	1996/09/10
B	L505-001	MPE	2005/03/14
C	L505-0056	MPE	2005/06/27
D	L506-0097	LGO	2006/07/28
-	-	-	-
-	-	-	-
-	-	-	-