

 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



TE Part Number: 2-5499376-8

✓ Active

 Add to Part List

 Always EU RoHS/ELV Compliant (Statement of Compliance)

- Connector Type = Universal Ejection Pin Headers
- Standard Profile
- Number of Positions = 34
- 2.54 x 2.54 mm Centerline, Matrix
- PCB Mount Angle = Right Angle

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [View Mating Products \(7\)](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

- [HEADER ASSY, UNIVERSAL, AMP-LATCH \(PDF, English\)](#)

- None Available

- [AMP-LATCH* and IDC Header Connectors, .100 x .100 In...](#)
(PDF, English)

- None Available

- None Available

- None Available

- Product Line Information

- Tooling
- Mating Products (7)

List all Documents

- Connector Type = Universal Ejection Pin Headers
- Profile = Standard
- Number of Positions = 34
- PCB Mount Angle = Right Angle
- PCB Retention Feature = No
- Mating Polarization Method = Center, Dual Polarizing Bar, Military
- Mating Connector Lock = With
- Housing Style = 4-Sided
- Ejection Latches = With
- Post Size (mm [in]) = 0.64 [.025]
- Shrouded = Yes
- PCB Thickness (mm [in]) = 3.18 [0.125]
- Mating Polarization = With
- Latch Type = Short
- Mating Connector Lock Type = Latch

- Termination (Solder) Post Length (mm [in]) = 3.94 [0.155]
- Solder Tail Contact Plating = Tin over Nickel

- Centerline, Matrix (mm [in]) = 2.54×2.54
[.100 x .100]

- Contact Mating Area Plating Material = Gold (30) over Nickel
- Contact Shape = Square

- Housing Material = Nylon
- Housing Flammability Rating = UL 94V-0
- Housing Color = Blue

- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

- Temperature Rating = Standard

- Brand = AMP