



Part Number : [5030952200](#)

Product Description : 2.00mm Pitch, iGrid Female Crimp Terminal, 0.10µm Gold (Au) Plating, 28-26 AWG, Reel

Series Number : 503095

Status : Active

Product Category : Crimp Terminals



Documents and Resources

Drawings

[5030952200_sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications


[5030952200-SPK-201.pdf](#)

[5016460000-PS-000.pdf](#)

[5016461000-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 33; 44; 34
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	503095
Description	2.00mm Pitch, iGrid Female Crimp Terminal, 0.10µm Gold (Au) Plating, 28-26 AWG, Reel
Application	Signal, Wire-to-Board
Product Name	iGrid
UPC	193264212125

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	250V AC (RMS)/DC

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Nickel
Net Weight	46.490/mg
Packaging Type	Reel

Plating min - Mating	0.100µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	0.85-1.50mm
Wire Size (AWG)	26, 28
Wire Size mm ²	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
iGrid Dual Row Receptacle Housings	<u>501646</u>

Application Tooling

Global

Description	Part Number
Extraction Tool for MX150L, MX150, PT Bulb Socket, iGrid, SPOX, and Wire-to-Motor Terminals	<u>638131500</u>
Hand Crimp Tool for 2.00mm Pitch Wire-to-Board Crimp Terminals, 28-26 AWG Wire	<u>638192400</u>
FineAdjust Applicator	<u>638618100</u>

This document was generated on Jun 07, 2026