


APPROVED: _____


DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/17/05	
A		CHANGE TERMINAL	8/15/08	
B		REDRAWN	3/12/09	SS
C		UPDATED MARKINGS	12/18/12	SS
D		REVISED SPEC.	12/20/12	
E		REDRAWN	12/20/12	
F		ADDED MARKING	10/12/18	AY/RC












RECOMMENDED PANEL CUT−OUT




PANEL THICKNESS	DIMENSIONS
	A
.031-.071 [0.80-1.80]	1.240 [31.50]
.075-.126 [1.90-3.20]	1.248 [31.70]



SECTION A-A





TERMINAL OPTIONS		
-1	-2	-3
.187 Q.C.	.250 Q.C.	.157 Solder
		

SPECIFICATIONS:
Material:
Insulator: Nylon 66, glass reinforced, rated UL 94V−0
Insulator color: Black
Contacts: Brass
Plating:
Tin over Copper underplate overall
Electrical:
Operating voltage: 250 VAC
Current rating: UL & CSA: 15 Amp
ENEC: 10 Amp
Insulation resistance: 100 Mohms min @ 500 VDC
Dielectric withstanding voltage: 3,000 VAC for 1 minute
Environmental:
Lead free, RoHS compliant

RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	SS	6/17/05
CHECKED		
APPROVED	SS	3/17/09

ADAM TECH INTERCONNECTS
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
IEC MALE INLET, SNAP-IN PANEL MOUNT
5 x 20mm FUSE HOLDER

SIZE	PART NO.	REV.
X	IEC-G-X	F

REF: S00087C | SCALE: NTS | SHEET 1 OF 1

Downloaded from Arrow.com.