

PART NO.	"A" REF.	"B"±.016 (±0.41)	INTERCHANGE WITH SCANBE
RSDC–250	2.5 (63.5)	1.5 (38.1)	11633–1
RSDC–300	3.0 (76.2)	2.0 (50.8)	
RSDC–350	3.5 (88.9)	2.5 (63.5)	
RSDC–400	4.0 (101.6)	3.0 (76.2)	
RSDC–450	4.5 (114.3)	3.5 (88.9)	11633–2
RSDC–500	5.0 (127.0)	4.0 (101.6)	
RSDC–550	5.5 (139.7)	4.5 (114.3)	
RSDC–600	6.0 (152.4)	5.0 (127.0)	
RSDC–650	6.5 (164.1)	5.5 (139.7)	11633–3
RSDC–700	7.0 (177.8)	6.0 (152.4)	
RSDC–750	7.5 (190.5)	6.5 (165.1)	
RSDC–800	8.0 (203.2)	7.0 (177.8)	11633–6





RECOMMENDED MOUNTING HOLES
PANEL THICKNESS: .047–.090 (1.2–2.3)

NOTES:
1. MATERIAL: NYLON 6/6 (RMS–48).
2. COLOR: NATURAL.

REV	DESCRIPTION	ENGR DATE
F	SEE ECN #831 FOR CHANGES	SM 08.09.04
E	COMPLETELY REDRAWN	SM 02.11.02
D	REM. "NO TAMPER AND RAMP" ON PRINT	JL 08.07.00
C	DIM. .225 (5.7) WAS .255 (6.5)	RS 01.25.93
B	DIM. "A" WAS REF.	RS 11.25.92
A	METRIC DIMS CORRECTED	RS 08.17.92

TITLE: SNAP–IN CARD GUIDE

DWG IN IN (MM)

TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC=±1/64 ANG=±1°	FILE # RSDC	DWN: P.B.	APP:	FINAL
	MAT'L: SEE NOTES	DT: 04.–05–94	DT:	PART # SEE TABLE
	RE: RICHCO, INC.	RICHCO INC. PO BOX 804238,CHICAGO,60680 (773) 539–4060		PRINT TYPE CA

Downloaded from Arrow.com.