

15A, 600V - 800V Low V_F Standard Bridge Rectifier

FEATURES

- AEC-Q101 qualified available
- Low forward drop enhance the efficiency
- Oxide planar chip junction
- High surge current capability
- UL Recognized File # E-326243
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21


APPLICATIONS

- Switching mode power supply (SMPS)
- Adapters
- Lighting application


MECHANICAL DATA

- Case: GBU
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Polarity: As marked
- Weight: 4.00g (approximately)

KEY PARAMETERS		
PARAMETER	VALUE	UNIT
I_F	15	A
V_{RRM}	600 - 800	V
I_{FSM}	200	A
$T_{J\ MAX}$	150	°C
Package	GBU	
Configuration	Quad	



GBU



ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

PARAMETER	SYMBOL	GBU15L05	GBU15L06	UNIT
Marking code on the device		GBU15L05	GBU15L06	
Repetitive peak reverse voltage	V_{RRM}	600	800	V
Reverse voltage, total rms value	$V_{R(RMS)}$	420	560	V
Forward current	I_F	15		A
Surge peak forward current single half sine-wave superimposed on rated load	$t = 8.3\text{ms}$	200		A
	$t = 1.0\text{ms}$	630		A
Rating for fusing ($t < 8.3\text{ms}$)	I^2t	166		A ² s
Junction temperature	T_J	- 55 to +150		°C
Storage temperature	T_{STG}	- 55 to +150		°C

THERMAL PERFORMANCE

PARAMETER	SYMBOL	TYP	UNIT
Junction-to-ambient thermal resistance	$R_{\theta JA}$	15	°C/W
Junction-to-case thermal resistance	$R_{\theta JC}$	3	°C/W

ELECTRICAL SPECIFICATIONS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

PARAMETER		CONDITIONS	SYMBOL	TYP	MAX	UNIT
Forward voltage per diode ⁽¹⁾	GBU15L05	I _F = 7.5A, T _J = 25°C	V _F	0.87	0.90	V
		I _F = 7.5A, T _J = 125°C		0.75	-	V
	GBU15L06	I _F = 7.5A, T _J = 25°C		0.93	0.96	V
		I _F = 7.5A, T _J = 125°C		-	-	V
Reverse current @ rated V _R per diode ⁽²⁾		T _J = 25°C	I _R	-	5	μA
		T _J = 125°C		-	150	μA

Notes:

1. Pulse test with $PW = 0.3\text{ms}$
2. Pulse test with $PW = 30\text{ms}$

ORDERING INFORMATION

ORDERING CODE ⁽¹⁾⁽²⁾	PACKAGE	PACKING
GBU15L0x	GBU	20 / Tube
GBU15L0xH	GBU	20 / Tube

Notes:

1. "x" defines voltage from 600V(GBU15L05) to 800V(GBU15L06)
2. "H" means AEC-Q101 qualified

CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.1 Forward Current Derating Curve




Fig.2 Typical Junction Capacitance




Fig.3 Typical Reverse Characteristics




Fig.4 Typical Forward Characteristics






Fig.5 Maximum Non-Repetitive Forward Surge Current



PACKAGE OUTLINE DIMENSIONS



DIM.	Unit (mm)		Unit (inch)	
	Min.	Max.	Min.	Max.
A	3.30	3.56	0.130	0.140
A2	1.90	2.16	0.075	0.085
b	1.02	1.27	0.040	0.050
b2	1.65	2.03	0.065	0.080
b4	2.16	2.54	0.085	0.100
c	0.46	0.56	0.018	0.022
D	18.30	18.80	0.720	0.740
D1	7.40	7.90	0.291	0.311
D2	1.65	2.16	0.065	0.085
E	21.80	22.30	0.858	0.878
E1	3.50	4.10	0.138	0.161
e	4.83	5.33	0.190	0.210
L	17.50	18.00	0.689	0.709
L4	1.52	2.03	0.060	0.080

MARKING DIAGRAM



P/N = Marking Code
 G = Green Compound
 YWW = Date Code
 F = Factory Code

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.