

# MOSFET – Power, Single, P-Channel, TSOP-6 -60 V, -2.9 A

## NTGS5120P, NVGS5120P

### Features

- 60 V BVds, Low  $R_{DS(on)}$  in TSOP-6 Package
- 4.5 V Gate Rating
- NVGS Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

### Applications

- High Side Load Switch
- Power Switch for Printers, Communication Equipment

### MAXIMUM RATINGS ( $T_J = 25^\circ\text{C}$ unless otherwise stated)


Parameter			Symbol	Value	Unit
Drain-to-Source Voltage			$V_{DSS}$	-60	V
Gate-to-Source Voltage			$V_{GS}$	$\pm 20$	V
Continuous Drain Current (Note 1)	Steady State	$T_A = 25^\circ\text{C}$	$I_D$	-2.5	A
		$T_A = 85^\circ\text{C}$		-2.0	
	$t \leq 5\text{ s}$	$T_A = 25^\circ\text{C}$		-2.9	
Power Dissipation (Note 1)	Steady State	$T_A = 25^\circ\text{C}$	$P_D$	1.1	W
	$t \leq 5\text{ s}$			1.4	
Continuous Drain Current (Note 2)	Steady State	$T_A = 25^\circ\text{C}$	$I_D$	-1.8	A
		$T_A = 85^\circ\text{C}$		-1.3	
Power Dissipation (Note 2)		$T_A = 25^\circ\text{C}$	$P_D$	0.6	W
Pulsed Drain Current	$t_p = 10\text{ }\mu\text{s}$		$I_{DM}$	-20	A
Operating Junction and Storage Temperature			$T_J, T_{STG}$	-55 to 150	°C
Lead Temperature for Soldering Purposes (1/8" from case for 10 s)			$T_L$	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Surface-mounted on FR4 board using 1 in sq pad size (Cu area = 1.127 in sq [2 oz] including traces)
2. Surface-mounted on FR4 board using the minimum recommended pad size.

$V_{(BR)DSS}$	$R_{DS(ON)} \text{ MAX}$	$I_D \text{ MAX}$
-60 V	111 mΩ @ -10 V	-2.9 A
	142 mΩ @ -4.5 V	

### P-Channel




### MARKING DIAGRAM



XX = Device Code  
M = Date Code  
■ = Pb-Free Package  
(Note: Microdot may be in either location)

### PIN ASSIGNMENT



### ORDERING INFORMATION

See detailed ordering and shipping information on page 5 of this data sheet.

# NTGS5120P, NVGS5120P

## THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Junction-to-Ambient – Steady State (Note 3)	$R_{\theta JA}$	102	°C/W
Junction-to-Ambient – $t = 5$ s (Note 3)	$R_{\theta JA}$	77.6	
Junction-to-Ambient – Steady State (Note 4)	$R_{\theta JA}$	200	

3. Surface-mounted on FR4 board using 1 in sq pad size (Cu area = 1.127 in sq [2 oz] including traces)

4. Surface-mounted on FR4 board using the minimum recommended pad size.

## ELECTRICAL CHARACTERISTICS ( $T_J = 25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Condition		Min	Typ	Max	Unit
<b>OFF CHARACTERISTICS</b>							
Drain-to-Source Breakdown Voltage	$V_{(\text{BR})\text{DSS}}$	$V_{\text{GS}} = 0$ V, $I_D = -250$ $\mu\text{A}$	$-60$				V
Zero Gate Voltage Drain Current	$I_{\text{DSS}}$	$V_{\text{GS}} = 0$ V, $V_{\text{DS}} = -48$ V	$T_J = 25^\circ\text{C}$			-1.0	$\mu\text{A}$
			$T_J = 125^\circ\text{C}$			-5.0	
Gate-to-Source Leakage Current	$I_{\text{GSS}}$	$V_{\text{DS}} = 0$ V, $V_{\text{GS}} = \pm 12$ V				$\pm 100$	nA
		$V_{\text{DS}} = 0$ V, $V_{\text{GS}} = \pm 20$ V				$\pm 200$	nA

## ON CHARACTERISTICS (Note 5)

Gate Threshold Voltage	$V_{\text{GS}(\text{TH})}$	$V_{\text{GS}} = V_{\text{DS}}, I_D = -250$ $\mu\text{A}$	-1.0		-3.0	V
Drain-to-Source On Resistance	$R_{\text{DS}(\text{on})}$	$V_{\text{GS}} = -10$ V, $I_D = -2.9$ A		72	111	$\text{m}\Omega$
		$V_{\text{GS}} = -4.5$ V, $I_D = -2.5$ A		88	142	
Forward Transconductance	$g_{\text{FS}}$	$V_{\text{DS}} = -5.0$ V, $I_D = -6.0$ A		10.1		S

## CHARGES, CAPACITANCES AND GATE RESISTANCE

Input Capacitance	$C_{\text{ISS}}$	$V_{\text{GS}} = 0$ V, $f = 1$ MHz, $V_{\text{DS}} = -30$ V		942		pF
Output Capacitance	$C_{\text{OSS}}$			72		
Reverse Transfer Capacitance	$C_{\text{RSS}}$			48		
Total Gate Charge	$Q_{\text{G}(\text{TOT})}$	$V_{\text{GS}} = -10$ V, $V_{\text{DS}} = -30$ V; $I_D = -2.9$ A		18.1		nC
Threshold Gate Charge	$Q_{\text{G}(\text{TH})}$			1.2		
Gate-to-Source Charge	$Q_{\text{GS}}$			2.7		
Gate-to-Drain Charge	$Q_{\text{GD}}$			3.6		

## SWITCHING CHARACTERISTICS (Note 6)

Turn-On Delay Time	$t_{\text{d}(\text{ON})}$	$V_{\text{GS}} = -10$ V, $V_{\text{DS}} = -30$ V, $I_D = -1.0$ A, $R_G = 6.0$ $\Omega$		8.7		ns
Rise Time	$t_r$			4.9		
Turn-Off Delay Time	$t_{\text{d}(\text{OFF})}$			38		
Fall Time	$t_f$			12.8		

## DRAIN-SOURCE DIODE CHARACTERISTICS

Forward Diode Voltage	$V_{\text{SD}}$	$V_{\text{GS}} = 0$ V, $I_S = -0.9$ A	$T_J = 25^\circ\text{C}$		-0.75	-1.0	V
Reverse Recovery Time	$t_{\text{RR}}$	$V_{\text{GS}} = 0$ V, $dI_S/dt = 100$ A/ $\mu\text{s}$ , $I_S = -0.9$ A			18.3		ns
Charge Time	$t_a$				15.5		
Reverse Recovery Charge	$Q_{\text{RR}}$				15.1		nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

5. Pulse Test: pulse width  $\leq 300$   $\mu\text{s}$ , duty cycle  $\leq 2\%$

6. Switching characteristics are independent of operating junction temperatures

TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance vs. Gate Voltage




Figure 4. On-Resistance vs. Drain Current and Gate Voltage




Figure 5. On-Resistance Variation with Temperature









Figure 6. Drain-to-Source Leakage Current vs. Voltage

TYPICAL CHARACTERISTICS



# NTGS5120P, NVGS5120P

## TYPICAL CHARACTERISTICS




Figure 12. Thermal Response

Table 1. ORDERING INFORMATION


Part Number	Marking (XX)	Package	Shipping <sup>†</sup>
NTGS5120PT1G	P6	TSOP-6 (Pb-Free)	3000 / Tape & Reel
NVGS5120PT1G	VP6	TSOP-6 (Pb-Free)	3000 / Tape & Reel

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.




**TSOP-6 3.00x1.50x0.90, 0.95P**  
CASE 318G  
ISSUE W


DATE 26 FEB 2024




TOP VIEW



SIDE VIEW



END VIEW




DETAIL Z  
SCALE 3:1

GAUGE PLANE  
SEATING PLANE

H  
L  
M

MILLIMETERS			
DIM	MIN	NOM	MAX
A	0.90	1.00	1.10
A1	0.01	0.06	0.10
A2	0.80	0.90	1.00
b	0.25	0.38	0.50
c	0.10	0.18	0.26
D	2.90	3.00	3.10
E	2.50	2.75	3.00
E1	1.30	1.50	1.70
e	0.85	0.95	1.05
L	0.20	0.40	0.60
L2	0.25 BSC		
M	0°	---	10°



RECOMMENDED MOUNTING FOOTPRINT

\*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference manual, SOLDERMM/D.

DOCUMENT NUMBER:	98ASB14888C	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	TSOP-6 3.00x1.50x0.90, 0.95P	PAGE 1 OF 2

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**TSOP-6 3.00x1.50x0.90, 0.95P**

CASE 318G

ISSUE W

DATE 26 FEB 2024

**GENERIC  
MARKING DIAGRAM\***

**IC**

XXX = Specific Device Code  
 A = Assembly Location  
 Y = Year  
 W = Work Week  
 ▪ = Pb-Free Package

**STANDARD**

XXX = Specific Device Code  
 M = Date Code  
 ▪ = Pb-Free Package

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present. Some products may not follow the Generic Marking.

**STYLE 1:**  
 PIN 1. DRAIN  
 2. DRAIN  
 3. GATE  
 4. SOURCE  
 5. DRAIN  
 6. DRAIN

**STYLE 2:**  
 PIN 1. Emitter 2  
 2. Base 1  
 3. Collector 1  
 4. Emitter 1  
 5. Base 2  
 6. Collector 2

**STYLE 3:**  
 PIN 1. ENABLE  
 2. N/C  
 3. R BOOST  
 4. Vz  
 5. Vin  
 6. Vout

**STYLE 4:**  
 PIN 1. N/C  
 2. Vin  
 3. NOT USED  
 4. GROUND  
 5. ENABLE  
 6. LOAD

**STYLE 5:**  
 PIN 1. Emitter 2  
 2. Base 2  
 3. Collector 1  
 4. Emitter 1  
 5. Base 1  
 6. Collector 2

**STYLE 6:**  
 PIN 1. COLLECTOR  
 2. COLLECTOR  
 3. BASE  
 4. Emitter  
 5. COLLECTOR  
 6. COLLECTOR

**STYLE 7:**  
 PIN 1. COLLECTOR  
 2. COLLECTOR  
 3. BASE  
 4. N/C  
 5. COLLECTOR  
 6. Emitter

**STYLE 8:**  
 PIN 1. Vbus  
 2. D(in)  
 3. D(in)+  
 4. D(out)+  
 5. D(out)  
 6. GND

**STYLE 9:**  
 PIN 1. LOW VOLTAGE GATE  
 2. DRAIN  
 3. SOURCE  
 4. DRAIN  
 5. DRAIN  
 6. HIGH VOLTAGE GATE

**STYLE 10:**  
 PIN 1. D(OUT)+  
 2. GND  
 3. D(OUT)-  
 4. D(IN)-  
 5. VBUS  
 6. D(IN)+

**STYLE 11:**  
 PIN 1. SOURCE 1  
 2. DRAIN 2  
 3. DRAIN 2  
 4. SOURCE 2  
 5. GATE 1  
 6. DRAIN 1/GATE 2

**STYLE 12:**  
 PIN 1. I/O  
 2. GROUND  
 3. I/O  
 4. I/O  
 5. VCC  
 6. I/O

**STYLE 13:**  
 PIN 1. GATE 1  
 2. SOURCE 2  
 3. GATE 2  
 4. DRAIN 2  
 5. SOURCE 1  
 6. DRAIN 1

**STYLE 14:**  
 PIN 1. ANODE  
 2. SOURCE  
 3. GATE  
 4. CATHODE/DRAIN  
 5. CATHODE/DRAIN  
 6. CATHODE/DRAIN

**STYLE 15:**  
 PIN 1. ANODE  
 2. SOURCE  
 3. GATE  
 4. DRAIN  
 5. N/C  
 6. CATHODE

**STYLE 16:**  
 PIN 1. ANODE/CATHODE  
 2. BASE  
 3. Emitter  
 4. COLLECTOR  
 5. ANODE  
 6. CATHODE

**STYLE 17:**  
 PIN 1. Emitter  
 2. BASE  
 3. ANODE/CATHODE  
 4. ANODE  
 5. CATHODE  
 6. COLLECTOR

<b>DOCUMENT NUMBER:</b>	98ASB14888C	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
<b>DESCRIPTION:</b>	TSOP-6 3.00x1.50x0.90, 0.95P	<b>PAGE 2 OF 2</b>

**onsemi** and **ONSEMI** are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

**onsemi**, **ONSEMI**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)

