

MC32PF3000A8EP :Part Detail

[General Information](#) |
 [Package Information](#) |
 [Environmental and Compliance Information](#) |
 [Manufacturing Information](#) |
 [Ordering Information](#) |
 [Operating Characteristics](#) |
 [Reliability Data Lookup](#)

General Information

Part Number	MC32PF3000A8EP
Description	Power Management IC, i.MX7, pre-prog, 4 buck, 6 LDO, 1 boost, QFN 48, Tray
Product Line	G32PF300
PTI	ANPG
Material Type	Tested Packaged Device
Life Cycle Description (code)	PRODUCT NEWLY INTRO D/RAMP-UP
Status	Active
Application/Qualification Tier	5-YEARS APPLICATION LIFE

Package Information

Package Type and Termination Count	QFN-EP 48
Package Description and Mechanical Drawing	QFN-EP 48 7*7*0.85 P0.5
Device Weight(g)	0.13950
Package Length (nominal)(mm)	7.000
Package Width (nominal)(mm)	7.000
Package Thickness (nominal)(mm)	0.850
Tape & Reel	No

Environmental and Compliance Information

Pb-Free	
RoHS Compliant	
Halogen Free	Yes
Material Composition Declaration (MCD)	Download MCD Report Download MCD Report
RoHS Certificate of Analysis (CoA)	Contact Us
2nd Level Interconnect	e3
Moisture Sensitivity Level (MSL)	3
Floor Life	168 HOURS
Peak Package Body Temperature (PBT)(°C)	260

Maximum Time at Peak Temperature (s)	40
Number of Reflow Cycles	3
REACH SVHC	NXP REACH Statement
UL94 (plastics flammability test)	V0;Burning stops within 10 seconds on a vertical specimen;no drips allowed

Manufacturing Information

Micron Size(μm)	.13
-----------------	-----

Ordering Information

Minimum Package Quantity (MPQ)	260
MPQ Container	TRAY
Exempt from Minimum Delivery Value	Yes
Preferred Order Quantity (POQ)	1300
POQ Container	BOX
Leadtime (weeks)	12
Export Control Classification Number (US)	EAR99
Harmonized Tariff (US) Disclaimer	8542.39.0000
CCATS Document	-
ENC Status	-
Other Trade Compliance Documents	-
Budgetary Price excluding tax(US\$) Change Currency	-

Order

Operating Characteristics

Ambient Operating Temperature (Min-Max) (°C)	-40 to 85
MCU Supported	i.MX7S i.MX7D
Sample Exception Availability	N

Reliability Data Lookup

[Investors](#)

[Partners](#)

[Careers](#)

[Mobile Apps](#)

[Press, News, Blogs](#)

[Contact Us](#)



NXP Achieves its First Certified Thread Stack as Thread Group Opens its Certification Program

[Read More](#)

[Privacy](#) | [Terms of Use](#) | [Terms of Sale](#) | [Feedback](#)

©2006-2017 NXP Semiconductors. All rights reserved.