


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
	H1	REVISED PER ECO-12-016795		18JAN2013	RZ	MY	



- 1 BRASS PER QQ-B-626
- 2 BRASS PER QQ-B-613
- 3 BERYLLIUM COPPER PER ASTM B 196
- 4 BERYLLIUM COPPER PER QQ-C-533
- 5 PTFE PER MIL-P-19468
- 6 SILICONE RUBBER PER ZZ-R-765
- 7 NICKEL PLATE PER QQ-N-290 2.54μm [.000100] MIN THK
- 8 NICKEL PLATE PER QQ-N-290 4.45μm [.000175] MIN THK
- 9 GOLD PLATE PER MIL-G-45204 1.27μm [.000050] MIN THK OVER NICKEL PLATE PER QQ-N-290 1.27μm [.000050] MIN THK
- 10 TIN PLATE PER ASTM-B-545 2.54μm [.000100] MIN THK
- 11 SILVER PLATE PER QQ-S-365 5.08μm [.000200] MIN THK
- 12 GOLD PLATE PER MIL-G-45204 1.27μm [.000050] MIN THK OVER COPPER PLATE PER MIL-C-14550A 2.54μm [.000100] MIN THK
- 13 NON-MAGNETIC

OBSOLETE	9	11	11	11	11	11	4.29[.169]	3.10[.122]	9-2257975-1	
OBSOLETE	9	7	7	7	7	8	4.29[.169]	3.10[.122]	9-225975-0	
OBSOLETE	13	12	11	11	11	11	4.29[.169]	3.10[.122]	225975-7	
	9	7	7	7	7	8	3.89[.153]	2.79[.110]	225975-6	
	9	7	7	7	7	8	4.29[.169]	3.10[.122]	225975-5	
	9	7	7	7	7	8	5.33[.210]	3.86[.152]	225975-4	
	9	7	7	7	7	8	4.29[.169]	3.10[.122]	225975-3	
	9	11	11	11	11	11	5.33[.210]	3.86[.152]	225975-2	
	9	11	11	11	11	11	4.29[.169]	3.10[.122]	225975-1	
		CENTER CONTACT PLATING	INNER FERRULE PLATING	OUTER CONTACT PLATING	WASHER PLATING	SHELL PLATING	COLLAR PLATING	B	A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	J. LIPPERT	1-10-91
CHK	M. PHILLIPS	1-18-91
APVD	M. PHILLIPS	1-18-91

TE Connectivity

PLUG ASSEMBLY, RIGHT ANGLE, DUAL CRIMP, BNC

108-12020

SCALE: 2:1 SHEET 1 OF 1 REV H1