





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/07/10	
A		UPDATE DRAWING	5/24/21	JJ/LL



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

Material:

Insulator: Nylon 66, Reinforced, rated UL 94V-2

Insulator color: Natural

Contacts: Brass

Plating:

Tin over nickel underplate

Electrical:

Operation voltage: 250V AC

Current rating: 10A

Contact resistance: 10 mohms max

Insulation resistance: 1000 mohms min.

Dielectric withstanding voltage: 1500 VAC for 1 minute

Temperature rating:

-25°C to +85°C

Environmental:

Lead Free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	ØX ± .10
.XX ± .020	ØXX ± .015
.XXX ± .015	ØXXX ± .010

DRAWN	DY	9/07/10
CHECKED		
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH



909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE .200 [5.08] RIGHT ANGLE HEADER	
SIZE X	PART NO. DDR-04
REV. A	
REF: S00123T	SCALE: NTS
SHEET 1 OF 1	