



- NOTES:
- MATERIALS AND FINISHES:
BODY - BRASS, NICKEL PLATING
MALE CONTACT - BRASS SILVER PLATING
FEMALE CONTACT - BeCu, SILVER PLATING
INSULATOR - PA66+23%GF
INSULATOR - PA66+30%GF
 - ELECTRICAL:
A. IMPEDANCE: 50 OHM
B. FREQUENCY RANGE: DC - 2 GHz
 - MECHANICAL:
A. DURABILITY: 500 CYCLES MIN.
B. TEMPERATURE RANGE: -65° C TO +165° C
 - PACKAGING:
A. QUANTITY: SINGLE PACK
B. MARKING: BAG TO BE MARKED
"AMPHENOL RF, 31-223, AND DATE CODE"

THIRD ANGLE PROJ.





RECOMMENDED MOUNTING
HOLE DIMENSIONS

REVISIONS				
REV	DESCRIPTION	DATE	ECO	APPR
A	RELEASE TO MFG.	--	--	--
T	ADD '31-223' MARKING TO BAG	04-Jun-99	43003	CPM
U	SYNCH THE DRAWING WITH DANBURY\RD-DM11031401R3	23-Mar-11	48488	RM
W	INSUALTOR MATERIAL WAS PA66+23%GF \RD-DM15051501S2	25-May-15	50432	EW
Y	UPDATE DRAWING	04-Jun-15	50594	EW



SCALE 2.500



CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm ± 0.05mm 0.5 - 6mm ± 0.1mm 6 - 30mm ± 0.2mm 30 - 120mm ± 0.3mm ANGLES ± 1°	MATERIAL -	DRAWN S.DUAN	DATE 04-Jun-15	TITLE SPECIAL TWIN CONTACT BNC RECEPTACLE		Amphenol RF Danbury CT USA, Tainan, Taiwan, Shenzhen, China www.amphenolrf.com	
		ENGINEER D.ROYCE	DATE 03-Apr-87				
		REFERENCE TEKTRONIX 100X-3308-1 DOR 22-25-5542	APPROVED S.HSIEH	DATE 04-Jun-15	SCALE: 6.0:1.0 SHEET 2 OF 2		DRAWING NO. 31-223
		FINISH	Root Folder/BNC/31-223		DWG SIZE B	REV Y	ITEM NO. 31-223 PART NO. 31-223