


Part number description :

10134336-XXXLF

LF: Lead Free, RoHs compliant, see note

XXX : Color ref or/and version



Note : THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES
AND OTHER COUNTRY REGULATIONS AS PER GS-47-0004

PN	Colour	Version
10134336-001LF	grey	
10134336-002LF	blue	

TECHNICAL DATA / DIMENSIONS

Dimensions	
Width mm	5.0
Length mm	53.0
Height mm	28.5
Mounting type (EN 60715)	Omega TH35
Technical data	
Maximum load current	32A
Insulating material	PA
Self-extinguishing degree acc. to UL94	V0
Rated surge voltage	6kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Nominal Voltage	630V
Nominal Current	24A
Connection data	
Conductor cross-section solid min/max	/ 4 mm ²
Conductor cross-section stranded min/max	/ 4 mm ²
AWG min/max	24-12AWG
Max conductor cross-section stranded with ferrule with plastic sleeve	2.5 mm ² / L=12 mm
Max conductor cross-section stranded with ferrule without plastic sleeve	4 mm ² / L=12 mm
Stripping length	max 12 mm

ACCESSORIES

Item	Description
Marking	
10134397-001LF	Blank large marking tags for screwless terminals
10134419-001LF	Vertical marking tags

DIN RAIL system - Mounting and Installation material

10134392-001LF	Steel Omega Rail TH35x7,5mm -2mt length
10134393-001LF	Slotted Steel Omega Rail TH35x7,5mm -2mt length
10134394-001LF	Steel Omega Rail TH35x15mm -2mt length
10134395-001LF	Slotted Steel Omega Rail TH35x15mm -2mt length
10134387-001LF	Angled support bracket
10134389-001LF	End Bracket for TH35 Omega rail -Width 9mm
10134390-001LF	End Bracket for TH35 Omega rail -Width 6mm
10134391-001LF	Fast-snap End Bracket for TH35 Omega rail

Additional items

10134342-001LF	End Plate for Screwless Terminal Block Q - QE 2.5
10134273-001LF	Jumper bar 2 poles, pitch 5,1mm J2,5
10134273-002LF	Jumper bar 3 poles, pitch 5,1mm J2,5
10134273-003LF	Jumper bar 24 poles, pitch 5,1mm J2,5
10134271-001LF	Ratchet Cutting Tool for jumper bar J2,5 -orange
10134276-001LF	Red test plug adapter
10134276-002LF	Black test plug adapter

APPROVALS



AWG 24-12- 600V - 20A

EN60947-7-1 2.5mm² - 630V - 24A

spec ref	dir Aymeric Soudy	30-06-2015	projection	size A3	scale 1:1
tolerance std ISO 406 ISO 1101	eng Aymeric Soudy	30-06-2015	mm	ecn no	
TOLERANCES UNLESS OTHERWISE SPECIFIED		chr		rel level	
		appr Aymeric Soudy			
surface ISO 1302	linear 0.X ± 0.3 0.XX ± 0.1 0.XXX ± 0.05	FCJ	product family DIN Terminal Block	dwg no 10134336	rev A
angular 0° ± 2°		www.fcj.com	cat. no.	Product customer drawing	sheet 1 of 1