

[Home](#) › [Products](#) › [Memories for Embedded Systems](#) › [nvSRAM](#) › [nvSRAM Serial](#) › [CY14ME064Q2A-SXQT](#)

CY14ME064Q2A-SXQT
[RoHS](#)
[PB Free](#)

Status: In Production
Datasheet



English

(pdf, 1.03 MB)
 File Type: PDF
 Updated: Feb 22, 2016



CY14ME064Q2A-SXQT	
Automotive Qualified	N
Density (Kb)	64
Frequency (MHz)	40
Interface	SPI
Max. Operating Temp. (°C)	105
Max. Operating VCCQ (V)	3.60
Max. Operating Voltage (V)	5.50
Min. Operating Temp. (°C)	-40
Min. Operating VCCQ (V)	2.70
Min. Operating Voltage (V)	4.50
Organization (X x Y)	8Kb x 8
Part Family	Serial nvSRAM
Speed (ns)	0
Tape & Reel	Y
Temp. Classification	Industrial(Q)

PRICING & INVENTORY AVAILABILITY

Availability	Quantity	Ships In	Buy from Cypress	Buy from Distributors
Out of Stock	0	Please click here to check lead times	Contact Sales	Contact Sales

* Prices are shown in United States dollars and are for budgetary use only for volume of 1ku

PACKAGING/ORDERING	
Package	SOIC
No. of Pins	8
Package Dimensions	193 L x 1.5 H x 150 W (Mils)
Package Weight	76.45 (mgs)
Package Cross Section Drawing	Download
Package Carrier	REEL
Package Carrier Drawing / Orientation	Reel Drawing , Tape Drawing , Package Orientation
Standard Pack Quantity	2500
Minimum Order Quantity (MOQ)	2500
Order Increment	2500
Estimated Lead Time (days)	28

Downloaded from [Arrow.com](#) 32.0040

DESIGN SUPPORT

- [Development Kits](#)
- [Forums](#)
- [Knowledge Base](#)
- [Packaging](#)
- [Product Brochures](#)
- [Quality & Reliability](#)
- [Samples](#)
- [Technical Support](#)
- [Technical Training](#)
- [Third Party Network \(CYPros\)](#)

TRAINING

- [Workshops](#)
- [Training On-Demand](#)
- [Webinars](#)

ECCN	(B.2.A.)
ECCN Suball	3A991

QUALITY AND ROHS

Moisture Sensitivity Level (MSL)	3
Peak Reflow Temp. (°C)	260 (Cypress Reflow Profile)
RoHS Compliant	Y Print RoHS Certificate of Compliance
PB Free	Y
Lead/Ball Finish	Ni/Pd/Au
Marking	Cypress Marking Format

Package Material Declaration

8L-SOIC Pb-Free Package Material Declaration Datasheet Last Update: Feb 13, 2017

IPC 1752 Material Declaration

IPC1752 MATERIAL DECLARATION SOIC08 (SZ08)- AMKOR PHIL - AU WIRE Last Update: Nov 10, 2016

IPC1752 MATERIAL DECLARATION SOIC 08 (SZ08) - CML - AU WIRE Last Update: Nov 10, 2016

IPC1752 MATERIAL DECLARATION SOIC 08 (SZ08) - OSE - AU WIRE Last Update: Nov 10, 2016

Device Qualification Reports

FIT/MTBF, ESD (HBM/CDM) and Latch-up data available in the Device Qualification Report.

QTP 102204: 1MEG (INDUS) SERIAL NON-VOLATILE SRAM PRODUCT FAMILY, S8 TECHNOLOGY, CMI (FAB 4).pdf Last Update: Sep 15, 2016

TECHNICAL DOCUMENTS
Product Change Notice (PCN) (1) PCN135221 Feb 08, 2016 Qualification of Copper Wire Bonds for select Lead Frame Products at Amko Philippines andn Cypress Philippines and transfer of PDIP and PLCC parts from MMT to Amkor Product Information Notice (PIN) (4) PIN135200 Feb 05, 2016 Barcode Inclusion on Cypress Packing List PIN145273 Feb 05, 2016 Improvement of Cypress Minnesota Back-End-of-Line Integration for 130nm SONOS Product Families PIN145277 Feb 05, 2016 Changes to Cypress Address Labels PIN145281 Feb 05, 2016 Qualification of New Carrier Tape Supplier at Cypress Philippines

Solutions

Automotive
Industrial
Consumer

Products

Wireless
Microcontrollers (MCUs)
Universal Serial Bus (USB)
Memory
Touch Sensing
Power Management
Clocks & Buffers

Design Support

Community
Videos
Development Kits
Quality & Reliability
Product Roadmaps

Buy & Sample

Request Samples
Buy Devices
Buy Development Kits

About Us

Investors
Careers

CORPORATE HEADQUARTERS

Cypress Semiconductor
Corp.
198 Champion Court
San Jose, CA 95134 USA
Tel: +1-408-943-2600

CUSTOMER SERVICE SUPPORT

+1-800-541-4736
Hours:
8:00AM - 5:00PM (local
time)
Create a MyCase

INTERNATIONAL SUPPORT

+1-408-943-2600
United States +1-800-
541-4736
Hours:
4:30AM - 1:30PM
(pacific time)
7:30PM - 4:30AM
(standard time)

OTHER REQUESTS

Contact Us
Report a Website
Problem

[ABOUT US](#)[CAREERS](#)[INVESTORS](#)

© Cypress Semiconductor Corporation. All rights reserved.