


Data Sheet | Item Number: 2003-500

Test plug adapter N; for 2003-6641 and 2003-6640 Multilevel Installation Terminal Blocks; for vertical test slot; 1-pole; gray

<https://www.wago.com/2003-500>



Color: gray

Electrical data

Ratings per IEC/EN

Nominal voltage (III/3)	500 V
Rated impulse withstand voltage (III / 3)	6 kV
Rated current	16 A

General information

Wiring direction	Side-entry wiring
------------------	-------------------

Connection Data

Clamping units	1
Total number of potentials	1

Connection 1

Connection technology	CAGE CLAMP®
Solid conductor	0.5 ... 2.5 mm² / 20 ... 16 AWG
Stranded conductor	0.5 ... 1.5 mm² / 20 ... 16 AWG
Fine-stranded conductor	0.5 ... 2.5 mm² / 20 ... 16 AWG
Strip length	9 ... 11 mm / 0.35 ... 0.43 inches
Wiring direction	Side-entry wiring

Material data

Note (material data)	Information on material specifications can be found here
Color	gray
Material group	I
Insulation material (main housing)	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.056 MJ
Weight	3 g



Environmental requirements		
Processing temperature		-35 ... +85 °C
Continuous operating temperature		-60 ... +105 °C

Commercial data		
Product Group		22 (TOPJOB S)
PU (SPU)		100 (25) pcs
Packaging type		Box
Country of origin		DE
GTIN		4050821322139
Customs tariff number		85366990990

Product Classification		
UNSPSC		39121402
eCl@ss 10.0		27-14-11-48
eCl@ss 9.0		27-14-11-48
ETIM 9.0		EC002555
ETIM 10.0		EC002555
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant, No Exemption

Downloads		
Environmental Product Compliance		
Compliance Search		
Environmental Product Compliance 2003-500		


Documentation				
Bid Text				
2003-500	19.02.2019	xml 2.59 KB		
2003-500	28.04.2017	doc 23.50 KB		



CAD/CAE-Data	
CAD data	CAE data
2D/3D Models 2003-500	WSCAD Universe 2003-500
	

Installation Notes

Testing



Multilevel installation terminal block fitted with an N-test plug adapter for insulation resistance measurement of the N-potential