

3W, 11V - 200V Surface Mount Silicon Zener Diode

FEATURES

- AEC-Q101 qualified
- Ideal for automated placement
- Glass passivated chip junction
- Low inductance
- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

APPLICATIONS

- Voltage regulating
- Reference voltage
- Protection circuit

MECHANICAL DATA

- Case: DO-214AA (SMB)
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Polarity: Indicated by cathode band
- Weight: 0.100g (approximately)

KEY PARAMETERS		
PARAMETER	VALUE	UNIT
V_Z	11 - 200	V
Test current I_{ZT}	1.9 - 34.1	mA
P_{tot}	3	W
$T_{J\ MAX}$	150	°C
Package	DO-214AA (SMB)	
Configuration	Single die	



DO-214AA (SMB)



ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ unless otherwise noted)			
PARAMETER	SYMBOL	VALUE	UNIT
DC power dissipation at $T_L=75^\circ\text{C}$, measure at zero lead length (Note 1) derate above 75°C	P_D	3	W
		40	mW/°C
DC power dissipation at $T_A=25^\circ\text{C}$ Derate above 25°C	P_D	550	mW
		4.4	mW/°C
Junction temperature	T_J	-55 to +150	°C
Storage temperature	T_{STG}	-55 to +150	°C

Note:

1. Mounted on Cu-Pad size 5mm x 5mm on PCB

THERMAL PERFORMANCE			
PARAMETER	SYMBOL	TYP	UNIT
Junction-to-lead thermal resistance	$R_{\theta JL}$	25	°C/W
Junction-to-ambient thermal resistance	$R_{\theta JA}$	226	°C/W

ELECTRICAL SPECIFICATIONS (TA = 25°C unless otherwise noted)

Device (Note 1)	Device Marking Code	Nominal Zener Voltage			Test current	Zener Impedance (Note 3)			Leakage Current		Maximum DC Zener Current		
		V _Z @I _{ZT}				I _{ZT}	Z _{ZT} @ I _{ZT}	Z _{ZK} @I _{ZK}		I _R @V _R		I _{ZM}	
		V				mA	Ω	Ω	mA	μA		V	mA(DC)
		Min	Nom (Note 2)	Max									
1SMB5926H	926B	10.45	11	11.55	34.1	5.5	550	0.25	1	8.4	136		
1SMB5927H	927B	11.40	12	12.60	31.2	6.5	550	0.25	1	9.1	125		
1SMB5928H	928B	12.35	13	13.65	28.8	7.0	550	0.25	1	9.9	115		
1SMB5929H	929B	14.25	15	15.75	25.0	9.0	600	0.25	1	11.4	100		
1SMB5930H	930B	15.20	16	16.80	23.4	10.0	600	0.25	1	12.2	94		
1SMB5931H	931B	17.10	18	18.90	20.8	12.0	650	0.25	1	13.7	83		
1SMB5932H	932B	19.00	20	21.00	18.7	14.0	650	0.25	1	15.2	75		
1SMB5933H	933B	20.90	22	23.10	17.0	17.5	650	0.25	1	16.7	68		
1SMB5934H	934B	22.80	24	25.20	15.6	19	700	0.25	1	18.2	63		
1SMB5935H	935B	25.65	27	28.35	13.9	23	700	0.25	1	20.6	56		
1SMB5936H	936B	28.50	30	31.50	12.5	26	750	0.25	1	22.8	50		
1SMB5937H	937B	31.35	33	34.65	11.4	33	800	0.25	1	25.1	45		
1SMB5938H	938B	34.20	36	37.80	10.4	38	850	0.25	1	27.4	42		
1SMB5939H	939B	37.05	39	40.95	9.6	45	900	0.25	1	29.7	38		
1SMB5940H	940B	40.85	43	45.15	8.7	53	950	0.25	1	32.7	35		
1SMB5941H	941B	44.65	47	49.35	8.0	67	1000	0.25	1	35.8	32		
1SMB5942H	942B	48.45	51	53.55	7.3	70	1100	0.25	1	38.8	29		
1SMB5943H	943B	53.20	56	58.80	6.7	86	1300	0.25	1	42.6	27		
1SMB5944H	944B	58.90	62	65.10	6.0	100	1500	0.25	1	47.1	24		
1SMB5945H	945B	64.60	68	71.40	5.5	120	1700	0.25	1	51.7	22		
1SMB5946H	946B	71.25	75	78.75	5.0	140	2000	0.25	1	56.0	20		
1SMB5947H	947B	77.90	82	86.10	4.6	160	2500	0.25	1	62.2	18		
1SMB5948H	948B	86.45	91	95.55	4.1	200	3000	0.25	1	69.2	16		
1SMB5949H	949B	95.00	100	105.00	3.7	250	3100	0.25	1	76.0	15		
1SMB5950H	950B	104.50	110	115.50	3.4	300	4000	0.25	1	83.6	13		
1SMB5951H	951B	114.00	120	126.00	3.1	360	4500	0.25	1	91.2	12		
1SMB5952H	952B	123.50	130	136.50	2.9	450	5000	0.25	1	98.8	11		
1SMB5953H	953B	142.50	150	157.50	2.5	600	6000	0.25	1	114.0	10		
1SMB5954H	954B	152.00	160	168.00	2.3	700	6500	0.25	1	121.6	9		
1SMB5955H	955B	171.00	180	189.00	2.1	900	7000	0.25	1	136.8	8		
1SMB5956H	956B	190.00	200	210.00	1.9	1200	8000	0.25	1	152.0	7		

Notes:

1. Tolerance and type number designation the type numbers listed indicate a tolerance of 5%
2. Zener voltage (V_Z) measurement: Nominal Zener voltage is measured with the device junction in thermal equilibrium with ambient temperature 25°C
3. Zener impedance (Z_Z) derivation : Z_{YT} and Z_{ZK} are measured by dividing the AC voltage drop across the device
by the AC current applied.
4. The specified limits are for I_Z(AC) = 0.1 I_Z(DC) with the AC frequency = 60 Hz

ORDERING INFORMATION

ORDERING CODE⁽¹⁾	PACKAGE	PACKING
1SMB59xH	DO-214AA (SMB)	3,000 / Tape & Reel

Notes:

1. "x" defines voltage from 11V(1SMB5926H) to 200V(1SMB5956H)

CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.1 Steady State Power Derating




Fig.2 Maximum Surge Power




Fig.3 Zener Voltage vs. Temperature Coefficient





Fig.4 Zener Voltage vs. Temperature Coefficient



CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.5 $V_z = 3.3$ thru 10 V




Fig.6 $V_z = 12$ thru 82 V




Fig.7 Effect Of Zener Voltage





Fig.8 Effect Of Zener Current



CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.9 Capacitance Curve




Fig.10 Typical Pulse Rating Curve




Fig.11 Pulse Waveform






Fig.12 Pulse Waveform




PACKAGE OUTLINE DIMENSIONS

DO-214AA (SMB)



DIM.	Unit (mm)		Unit (inch)	
	Min.	Max.	Min.	Max.
A	1.95	2.65	0.077	0.104
A1	0.05	0.20	0.002	0.008
b	1.95	2.20	0.077	0.087
c	0.15	0.31	0.006	0.012
D	3.30	3.95	0.130	0.156
E	5.10	5.60	0.201	0.220
E1	4.05	4.60	0.159	0.181
L	0.75	1.60	0.030	0.063

SUGGESTED PAD LAYOUT



Symbol	Unit (mm)	Unit (inch)
A	2.30	0.091
B	2.50	0.098
C	4.30	0.169
D	1.80	0.071
E	6.80	0.268

MARKING DIAGRAM



P/N = Marking Code
 G = Green Compound
 YW = Date Code
 F = Factory Code

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.