

TLP559(IGM)

**TRANSISTOR INVERTER
INVERTER FOR AIR CONDITIONER
LINE RECEIVER
IPM INTERFACES**


Unit: mm

The TOSHIBA TLP559(IGM) consists of a GaAIAs high-output light emitting diode and a high speed detector of one chip photo diode-transistor.

This unit is 8-lead DIP package.

TLP559(IGM) has no internal base connection, and a Faraday shield integrated on the photodetector chip provides an effective common mode noise transient immunity.


TLP559(IGM) guarantees minimum and maximum of propagation delay time, switching time dispersion, and high common mode transient immunity. There for TLP559(IGM) is suitable for isolation interface between IPM(Intelligent Power Module) and control IC circuits in motor control application.




Weight: 0.54 g

- Isolation Voltage : 2500 Vrms (Min)
- Common Mode Transient Immunity : ±10kV/μs (Min)
@V_{CM} = 1500 V
- Switching Time : t_{pHL} , t_{pLH} = 0.1μs (Min)
= 0.8μs (Max)
@I_F = 10 mA , V_{CC} = 15 V , R_L = 20 kΩ , Ta = 25°C
- Switching Time Dispersion : 0.7μs (Max)
(|t_{pLH} - t_{pHL}|)
- TTL Compatible
- UL Recognized : UL1577, File No. E67349

PIN CONFIGURATION(Top view)



SCHEMATIC



MAXIMUM RATINGS (Ta = 25°C)

CHARACTERISTIC		SYMBOL	RATING	UNIT
LED	Forward Current (Note 1)	I_F	25	mA
	Pulse Forward Current (Note 2)	I_{FP}	50	mA
	Peak Transient Forward Current (Note 3)	I_{FPT}	1	A
	Reverse Voltage	V_R	5	V
	Diode Power Dissipation (Note 4)	P_D	45	mW
DETECTOR	Output Current	I_O	8	mA
	Peak Output Current	I_{OP}	16	mA
	Output Voltage	V_O	-0.5~20	V
	Supply Voltage	V_{CC}	-0.5~30	V
	Output Power Dissipation (Note 5)	P_O	100	mW
Operating Temperature Range		T_{opr}	-55~100	°C
Storage Temperature Range		T_{stg}	-55~125	°C
Lead Solder Temperature(10s) (Note 6)		T_{sol}	260	°C
Isolation Voltage(AC, 1min., R.H.≤60%, Ta=25°C) (Note 7)		BV_S	2500	Vrms

(Note 1) Derate 0.5mA above 70°C.

(Note 2) 50% duty cycle, 1ms pulse width.

Derate -1.0mA/°C above 70°C.

(Note 3) Pulse width $PW \leq 1\mu s$, 300pps.

(Note 4) Derate 0.9mW/°C above 70°C.

(Note 5) Derate 2mW/°C above 70°C.

(Note 6) Soldering portion of lead : up to 2mm from the body of the device.

(Note 7) Device considered a two terminal device : pins 1,2,3 and 4 shorted together and pins 5,6,7 and 8 shorted together.

ELECTRICAL CHARACTERISTICS (Ta = 25°C)

CHARACTERISTIC		SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
LED	Forward Voltage	V_F	$I_F = 16 \text{ mA}$	—	1.65	1.85	V
	Forward Voltage Temperature Coefficient	$\Delta V_F / \Delta T_a$	$I_F = 16 \text{ mA}$	—	-2	—	mV / °C
	Reverse Current	I_R	$V_R = 5 \text{ V}$	—	—	10	μA
	Capacitance between Terminal	CT	$V = 0, f = 1 \text{ MHz}$	—	45	—	pF
DETECTOR	High Level Output Current	$I_{OH(1)}$	$I_F = 0 \text{ mA}, V_{CC} = V_O = 5.5 \text{ V}$	—	3	500	nA
		$I_{OH(2)}$	$I_F = 0 \text{ mA}, V_{CC} = 30 \text{ V}$ $V_O = 20 \text{ V}$	—	—	5	μA
		I_{OH}	$I_F = 0 \text{ mA}, V_{CC} = 30 \text{ V}$ $V_O = 20 \text{ V}, T_a = 70^\circ\text{C}$	—	—	50	
	High Level Supply Voltage	I_{CCH}	$I_F = 0 \text{ mA}, V_{CC} = 30 \text{ V}$	—	0.01	1	μA
	Supply Voltage	V_{CC}	$I_{CC} = 0.01 \text{ mA}$	30	—	—	V
	Output Voltage	V_O	$I_O = 0.5 \text{ mA}$	20	—	—	V

COUPLED ELECTRICAL CHARACTERISTICS (Ta = 25°C)

CHARACTERISTIC	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Current Transfer Ratio	I _O / I _F	I _F = 10 mA, V _{CC} = 4.5 V V _O = 0.4 V	25	35	75	%
		I _F = 10 mA, V _{CC} = 4.5 V V _O = 0.4 V, Ta = -25~100°C	15	—	—	
Low Level Output Voltage	V _{OL}	I _F = 16 mA, V _{CC} = 4.5 V I _O = 2.4 mA	—	—	0.4	V

ISOLATION CHARACTERISTICS (Ta = 25°C)

CHARACTERISTIC	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Capacitance Input to Output	CS	V = 0, f = 1 MHz	—	0.8	—	pF
Isolation Resistance	R _S	R.H. ≤ 60%, V _S = 500 V	5 × 10 ¹⁰	10 ¹⁴	—	Ω
Isolation Voltage	BV _S	AC, 1minute	2500	—	—	Vrms
		AC, 1second, in oil	—	5000	—	
		DC, 1minute, in oil	—	5000	—	Vdc

SWITCHING CHARACTERISTICS (Ta = 25°C, V_{CC} = 15 V)



CHARACTERISTIC	SYMBOL	TEST CIRCUIT	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Propagation Delay Time (H→L)	t _{pHL}	1	I _F = 10 mA, R _L = 20 kΩ	0.1	0.45	0.8	μs
Propagation Delay Time (L→H)	t _{pLH}		I _F = 10 mA, R _L = 20 kΩ Ta = 0~85°C	0.1	0.45	0.9	
			I _F = 10 mA, R _L = 20 kΩ Ta = -25~100°C	0.1	0.45	1.0	
Switching Time Dispersion between ON and OFF	t _{pLH} - t _{pHL}	1	I _F = 10 mA, R _L = 20 kΩ	—	0.15	0.7	μs
			I _F = 10 mA, R _L = 20 kΩ Ta = 0~85°C	—	0.25	0.8	
			I _F = 20 mA, R _L = 20 kΩ Ta = -25~100°C	—	0.25	0.9	
Common Mode Transient Immunity at Logic High Output (Note 8)	CM _H	2	I _F = 0 mA, V _{CM} = 1500 V _{p-p} , R _L = 20 kΩ	10000	15000	—	V / μs
Common Mode Transient Immunity at Logic Low Output (Note 8)	CM _L		I _F = 10 mA, V _{CM} = 1500 V _{p-p} , R _L = 20 kΩ	-10000	-15000	—	V / μs

(Note 8) CM_L is the maximum rate of fall of the common mode voltage that can be sustained with the output voltage in the logic low state (V_O < 1V).



CM_H is the maximum rate of rise of the common mode voltage that can be sustained with the output voltage in the logic high state (V_O > 4V).

(Note 9) Maximum electrostatic discharge voltage for any pins : 100V (C=200pF, R=0)

TEST CIRCUIT 1 : Switching time test circuit



TEST CIRCUIT 2 : Common mode noise immunity test circuit



$$CM_H = \frac{1200(V)}{t_r(\mu s)}, \quad CM_L = \frac{1200(V)}{t_f(\mu s)}$$

RESTRICTIONS ON PRODUCT USE

000707EBC

- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property.
In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc..
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.
- Gallium arsenide (GaAs) is a substance used in the products described in this document. GaAs dust and fumes are toxic. Do not break, cut or pulverize the product, or use chemicals to dissolve them. When disposing of the products, follow the appropriate regulations. Do not dispose of the products with other industrial waste or with domestic garbage.
- The products described in this document are subject to the foreign exchange and foreign trade laws.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA CORPORATION for any infringements of intellectual property or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any intellectual property or other rights of TOSHIBA CORPORATION or others.
- The information contained herein is subject to change without notice.