


Similar to illustration



Electrical data	
Operating voltage	≤30 VAC; ≤50 VDC
Nominal current	1 A

Safety and protection	
Rated voltage	50 V
Rated surge voltage	0.8 kV
Pollution degree	2
Protection type	IP00; Notice! Live parts can be easily touched! Protection against direct contact must be provided by the equipment manufacturer, e.g., using a WAGO 709 Series Cover (see “Accessories”) or a similar cover. The installation guidelines must be observed for each individual application.

Insulation type	Basic insulation
-----------------	------------------

Connection data	
Performance level	3 / 50 mating cycles

Connection 1	
Connector	DIN 41651 connector; male connector
Pole number 1	50
Connection type 1	System
Note (conductor cross-section)	12 AWG: THHN, THWN
Mating direction	vertical
Connection type	Male connector; pluggable connector per DIN 41651

Connection 2	
Design 2	PCB terminal blocks (double-row)
Pole number 2	50
Connection type 2	Field
Connection technology 2	CAGE CLAMP®
WAGO connector 2	WAGO 236 Series
Solid conductor 2	0.08 ... 2.5 mm² / 28 ... 12 AWG
Fine-stranded conductor 2	0.08 ... 2.5 mm² / 28 ... 12 AWG
Strip length 2	5 ... 6 mm / 0.2 ... 0.24 inches



Physical data		
Width		151 mm / 5.945 inches
Height		63.5 mm / 2.5 inches
Depth from upper-edge of DIN-rail		28 mm / 1.102 inches

Mechanical data		
Mounting type		DIN-35 rail
Housing design		PCB with mounting feet

Material data		
Contact material (connector)		Au over Ni
Fire load		0.081 MJ
Weight		90 g

Environmental requirements		
Ambient temperature (operation)		-20 ... +55 °C
Ambient temperature (storage)		-40 ... +70 °C
Relative humidity		≤ 85% (non-condensing)
Operating altitude (max.)		2000 m

Standards and specifications		
Standards/specifications		EN 61010-2-201

Commercial data		
Product Group		6 (INTERFACE ELECTRONIC)
eCl@ss 10.0		27-14-11-52
eCl@ss 9.0		27-14-11-52
ETIM 8.0		EC002780
ETIM 7.0		EC002780
PU (SPU)		4 (1) pcs
Packaging type		Box
Country of origin		DE
GTIN		4045454353438
Customs tariff number		85366990990

Environmental Product Compliance		
RoHS Compliance Status		Compliant,No Exemption

Downloads

Environmental Product Compliance



Compliance Search			
Environmental Product Compliance 289-408			↓

Documentation			
Bid Text		Instruction Leaflet	
289-408	19.02.2019	xml 3.26 KB	↓
289-408	09.02.2015	doc 25.00 KB	↓

CAD/CAE-Data	
CAD data	CAE data
2D/3D Models 289-408	EPLAN Data Portal 289-408
↓	↓
	WSCAD Universe 289-408
	↓
	ZUKEN Portal 289-408
	↓

1 Compatible Products
1.1 Optional Accessories
1.1.1 Installation
1.1.1.1 Cover



Item No.: 709-153

Cover; Type 1; suitable for cover carrier, type 1; 1 m long; transparent

1.1.1.2 Cover carrier



Item No.: 709-167

Cover carrier; Type 1; incl. fixing/retaining screws and knurled nut; suitable for 279 to 282 and 880 Series rail-mounted terminal blocks; suitable for 264 Series miniature rail-mounted terminal blocks; suitable for 270 Series sensor and actuator terminal blocks; gray

1.1.2 Tool

1.1.2.1 Operating tool




Item No.: 210-720


Operating tool; Blade: 3.5 x 0.5 mm; with a partially insulated shaft; multicoloured

Installation Notes

Conductor termination



Conductor termination – screwdriver actuation parallel to conductor entry



Conductor termination – screwdriver actuation perpendicular to conductor entry