



Micro Commercial Components



Micro Commercial Components  
20736 Marilla Street Chatsworth  
CA 91311  
Phone: (818) 701-4933  
Fax: (818) 701-4939

**2SA933AS-Q**  
**2SA933AS-R**  
**2SA933AS-S**

## Features

- Lead Free Finish/Rohs Compliant ("P" Suffix designates Compliant. See ordering information)
- Epoxy meets UL 94 V-0 flammability rating
- Moisture Sensitivity Level 1
- Marking: type number
- Power dissipation:  $P_{CM} = 0.2W(T_{amb}=25^{\circ}C)$
- Collector current:  $I_{CM} = -0.15A$
- Collector-base voltage:  $V_{(BR)CBO} = -60V$
- Operating and storage junction temperature range  
 $T_J, T_{stg}: -55^{\circ}C \text{ to } +150^{\circ}C$
- Halogen free available upon request by adding suffix "-HF"

## Electrical Characteristics @ 25°C Unless Otherwise Specified


Symbol	Parameter	Min	Typ	Max	Unit
$V_{CEO}$	Collector-Emitter Voltage ( $I_C = -50 \mu A, I_E = 0$ )	-50	---	---	V
$V_{CBO}$	Collector-Base Voltage ( $I_C = -1 \mu A, I_B = 0$ )	-60	---	---	V
$V_{EBO}$	Emitter-Base Voltage ( $I_E = -50 \mu A, I_C = 0$ )	-6.0	---	---	V
$I_{CBO}$	Collector cut-off Current ( $V_{CB} = -20V, I_E = 0$ )	---	---	-0.1	$\mu A$
$I_{EBO}$	Emitter cut-off Current ( $V_{EB} = -5V, I_C = 0$ )	---	---	-0.1	$\mu A$
$h_{FE}$	DC current gain ( $V_{CE} = -2V, I_C = -0.1A$ )	120	---	560	---
$V_{CE(sat)}$	Collector-Emitter Saturation Voltage ( $I_C = -2A, I_B = -0.1A$ )	---	---	-0.5	V
$f_T$	Transition Frequency ( $V_{CE} = 2.0Vdc, I_C = 0.5Adc$ )	120	---	---	MHz

## CLASSIFICATION OF $h_{FE}$

Rank	Q	R	S
Range	120-270	180-390	270-560

## PNP Plastic-Encapsulate Transistors

TO-92S



DIMENSIONS					
DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	.056	.064	1.42	1.62	
B	.154	.161	3.90	4.10	
C	.120	.128	3.05	3.25	
D	.050		1.27		Straight Lead
	.086	.110	2.20	2.80	Bent Lead
E	.096	.104	2.44	2.64	Straight Lead
	.173	.220	4.40	5.60	Bent Lead
L	.594	.610	15.10	15.50	

\* For ammo packing detailed specification, click here to visit our website of product packaging for details.

[www.mccsemi.com](http://www.mccsemi.com)

## Ordering Information :

Device	Packing
Part Number-AP	Ammo Packing: 30Kpcs/Carton
Part Number-BP	Bulk: 100Kpcs/Carton

Note : Adding "-HF" suffix for halogen free, eg. Part Number-BP-HF

### \*\*\*IMPORTANT NOTICE\*\*\*

**Micro Commercial Components Corp.** reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp .** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp .** and all the companies whose products are represented on our website, harmless against all damages.

### \*\*\*LIFE SUPPORT\*\*\*

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

### \*\*\*CUSTOMER AWARENESS\*\*\*

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.