Your search criteria matched only one product, shown below

HSTTPN50-713-Q



- Low shrink temperature (store below 90° F) to speed installation
- Crystal clear material ensures easy to read labels and splice inspections
- Highly flame retardant product manufactured from a material that is rated UL224 VW -1
- Shrink ratio of 2:1 insulates a wide range of diameters and irregular shapes

Meets Mil Spec AMS-DTL-23053/2 Class 2.

Part Number	HSTTPN50713-Q
RoHS Compliancy Status	Compliant
Part Description	Crystal Clear PVC Heat Shrink
Material	Highly flame retardant non cross-linked PVC
Color	Clear
Military Specification	AMS-DTL-23053/2 Class 2
Length (In.)	7.13
Length (mm)	181.0
Continuous Use Temperature Range	-31°F to 221°F (-35°C to 105°C)
Max. Recovered I.D. (In.)	.25
Max. Recovered I.D. (mm)	6.4
Min. Expanded I.D. (In.)	.50
Min. Expanded I.D. (mm)	12.7
Nominal Diameter (In.)	1/2
Nominal Diameter (mm)	12.7
Nominal I.D. (In.)	.50
Nominal I.D. (mm)	12.7
Nominal Recovered Wall Thickness (In.)	.30
Nominal Recovered Wall Thickness (mm)	0.8
Pricing Description	.50" (12.7mm) PVC Heat Shrink Clear
Temperature Range	-31°F to 221°F (-35°C to 105°C)
Min. Order UOM	PC
Min. Order Qty.	25
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please register to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.

Copyright © 1995-2008, PANDUIT CORP. All rights reserved. Legal Information | Privacy Policy

Downloaded from Arrow.com.