

Metallized Polypropylene (PP) Capacitors in PCM 7.5 mm to 37.5 mm. Capacitances from 1000 pF to 10 µF. Rated Voltages from 100 VDC to 2000 VDC.

Special Features

- High volume/capacitance ratio
- Self-healing
- Very low dissipation factor
- Negative capacitance change versus temperature
- Very low dielectric absorption
- According to RoHS 2011/65/EU

Typical Applications

For high frequency applications e.g.

- Sample and hold
- Timing
- Oscillating circuits
- High frequency coupling and decoupling

Construction


Dielectric:

Polypropylene (PP) film

Capacitor electrodes:

Vacuum-deposited

Internal construction:



Encapsulation:

Solvent-resistant, flame-retardant plastic case with epoxy resin seal, UL 94 V-0

Terminations:

Tinned wire.

Marking:

Colour: Red. Marking: Black.

Electrical Data

Capacitance range:

0.01 µF to 68 µF

Rated voltages:

100 VDC, 250 VDC, 400 VDC, 630 VDC, 1000 VDC, 1250 VDC

Capacitance tolerances:

±20%, ±10%, ±5%

Operating temperature range:

–55° C to +105° C

Climatic test category:

55/100/56 in accordance with IEC

Insulation resistance at +20° C:

$C \leq 0.33 \mu\text{F}$: $\geq 1 \times 10^5 \text{ M}\Omega$

$C > 0.33 \mu\text{F}$: $\geq 30\,000 \text{ sec (M}\Omega \times \mu\text{F)}$

Measuring voltage: 100 V/1 min.

Dissipation factors at +20° C:

at f	$C \leq 0.1 \mu\text{F}$	$0.1 \mu\text{F} < C \leq 1.0 \mu\text{F}$	$C > 1.0 \mu\text{F}$
1 kHz	$\leq 6 \times 10^{-4}$	$\leq 6 \times 10^{-4}$	$\leq 6 \times 10^{-4}$
10 kHz	$\leq 8 \times 10^{-4}$	$\leq 8 \times 10^{-4}$	–
100 kHz	$\leq 25 \times 10^{-4}$	–	–

Maximum pulse rise time:

Capacitance µF	max. pulse rise time V/µsec at $T_A < 40^\circ \text{C}$					
	100 VDC	250 VDC	400 VDC	630 VDC	1000 VDC	1250 VDC
0.01 ... 0.022	450	450	450	500	550	600
0.033 ... 0.068	250	250	300	350	400	450
0.1 ... 0.22	150	150	200	250	300	350
0.33 ... 0.68	100	100	150	200	200	250
1.0 ... 2.2	75	100	100	150	150	200
3.3 ... 4.7	60	100	100	120	140	160
6.8 ... 10	40	50	60	85	–	–
12 ... 68	20	20	40	50	–	–

for pulses equal to the rated voltage

Mechanical Tests

Pull test on pins:

$d \leq 0.8 \phi$: 10 N in direction of pins

$d > 0.8 \phi$: 20 N in direction of pins

according to IEC 60068-2-21

Vibration:

6 hours at 10 ... 2000 Hz and 0.75 mm

displacement amplitude or 10 g in

accordance with IEC 60068-2-6

Low air density:

1 kPa = 10 mbar in accordance with

IEC 60068-2-13

Bump test:

4000 bumps at 390 m/sec²

in accordance with IEC 60068-2-29

Test specifications:

In accordance with IEC 60384-16

Test voltage: 1.6 U_r , 2 sec.

Dielectric absorption:

0.05%

Voltage derating:

A voltage derating factor of 1.35 % per K must be applied from +85° C for DC voltages and from +75° C for AC voltages.

Reliability:

Operational life > 300 000 hours

Failure rate < 2 fit ($0.5 \times U_r$ and 40° C).

Packing

Available taped and reeled up to and

including case size 15 x 26 x 31.5 /

PCM 27.5 mm.

Detailed taping information and graphs

at the end of the catalogue.

For further details and graphs please refer to Technical Information.

Continuation

General Data

Capacitance	100 VDC/63 VAC*					250 VDC/160 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
0.01 μ F	3	8.5	10	7.5	MKP4D021002B00	3	8.5	10	7.5	MKP4F021002B00
0.015 "	3	8.5	10	7.5	MKP4D021502B00	3	8.5	10	7.5	MKP4F021502B00
0.022 "	3	8.5	10	7.5	MKP4D022202B00	3	8.5	10	7.5	MKP4F022202B00
0.033 "	3	8.5	10	7.5	MKP4D023302B00	3	8.5	10	7.5	MKP4F023302B00
	4	9	13	10	MKP4D023303C00	4	9	13	10	MKP4F023303C00
0.047 "	4	9	10	7.5	MKP4D024702C00	4	9	10	7.5	MKP4F024702C00
	4	9	13	10	MKP4D024703C00	4	9	13	10	MKP4F024703C00
0.068 "	4	9	10	7.5	MKP4D026802C00	4	9	10	7.5	MKP4F026802C00
	4	9	13	10	MKP4D026803C00	4	9	13	10	MKP4F026803C00
0.1 μ F	4.5	9.5	10.3	7.5	MKP4D031002D00	4.5	9.5	10.3	7.5	MKP4F031002D00
	4	9	13	10	MKP4D031003C00	4	9	13	10	MKP4F031003C00
0.15 "	5	10.5	10.3	7.5	MKP4D031502E00	5	10.5	10.3	7.5	MKP4F031502E00
	5	11	13	10	MKP4D031503F00	5	11	13	10	MKP4F031503F00
0.22 "	6	12	13	10	MKP4D032203G00	6	12	13	10	MKP4F032203G00
	5	11	18	15	MKP4D032204B00	5	11	18	15	MKP4F032204B00
0.33 "	6	12.5	18	15	MKP4D033304C00	6	12.5	18	15	MKP4F033304C00
0.47 "	7	14	18	15	MKP4D034704D00	7	14	18	15	MKP4F034704D00
0.68 "	8	15	18	15	MKP4D036804F00	8	15	18	15	MKP4F036804F00
	6	15	26.5	22.5	MKP4D036805B00	6	15	26.5	22.5	MKP4F036805B00
1.0 μ F	7	16.5	26.5	22.5	MKP4D041005D00	7	16.5	26.5	22.5	MKP4F041005D00
						9	19	31.5	27.5	MKP4F041006A00
1.2 "	10.5	19	26.5	22.5	MKP4D041205G00	10.5	19	26.5	22.5	MKP4F041205G00
						9	19	31.5	27.5	MKP4F041206A00
1.5 "	10.5	19	26.5	22.5	MKP4D041505G00	10.5	19	26.5	22.5	MKP4F041505G00
						11	21	31.5	27.5	MKP4F041506B00
1.8 "	11	21	26.5	22.5	MKP4D041805I00	11	21	26.5	22.5	MKP4F041805I00
						11	21	31.5	27.5	MKP4F041806B00
2.2 "	11	21	26.5	22.5	MKP4D042205I00	11	21	26.5	22.5	MKP4F042205I00
	9	19	31.5	27.5	MKP4D042206A00	11	21	31.5	27.5	MKP4F042206B00
2.7 "	9	19	31.5	27.5	MKP4D042706A00	11	21	31.5	27.5	MKP4F042706B00
3.3 "	9	19	31.5	27.5	MKP4D043306A00	14.5	29.5	26.5	22.5	MKP4F043305M00
						13	24	31.5	27.5	MKP4F043306D00
3.9 "	14.5	29.5	26.5	22.5	MKP4D043905M00	14.5	29.5	26.5	22.5	MKP4F043905M00
	11	21	31.5	27.5	MKP4D043906B00	13	24	31.5	27.5	MKP4F043906D00
4.7 "	14.5	29.5	26.5	22.5	MKP4D044705M00	15	26	31.5	27.5	MKP4F044706F00
	13	24	31.5	27.5	MKP4D044706D00	13	24	41.5	37.5	MKP4F044707C00
5.6 "	14.5	29.5	26.5	22.5	MKP4D045605M00	17	29	31.5	27.5	MKP4F045606G00
	13	24	31.5	27.5	MKP4D045606D00	15	26	41.5	37.5	MKP4F045607D00
6.8 "	15	26	31.5	27.5	MKP4D046806F00	17	29	31.5	27.5	MKP4F046806G00
						15	26	41.5	37.5	MKP4F046807D00
8.2 "	15	26	31.5	27.5	MKP4D048206F00	17	34.5	31.5	27.5	MKP4F046806I00
						17	29	41.5	37.5	MKP4F046807E00
10 μ F	17	29	31.5	27.5	MKP4D051006G00	20	39.5	31.5	27.5	MKP4F051006J00
	13	24	41.5	37.5	MKP4D051007C00	19	32	41.5	37.5	MKP4F051007F00
12 "	17	29	31.5	27.5	MKP4D051206G00	20	39.5	41.5	37.5	MKP4F051207G00
	15	26	41.5	37.5	MKP4D051207D00					
15 "	17	34.5	31.5	27.5	MKP4D051506I00	20	39.5	41.5	37.5	MKP4F051507G00
	17	29	41.5	37.5	MKP4D051507E00					
18 "	20	39.5	31.5	27.5	MKP4D051806J00	24	45.5	41.5	37.5	MKP4F051807H00
	19	32	41.5	37.5	MKP4D051807F00					
22 "	20	39.5	41.5	37.5	MKP4D052207G00	24	45.5	41.5	37.5	MKP4F052207H00
						28	38	41.5	37.5	MKP4F052207L00
27 "	20	39.5	41.5	37.5	MKP4D052707G00	31	46	41.5	37.5	MKP4F052707I00
33 "	28	38	41.5	37.5	MKP4D053307L00	35	50	41.5	37.5	MKP4F053307J00
	24	45.5	41.5	37.5	MKP4D053307H00					
39 "	31	46	41.5	37.5	MKP4D053907I00	40	55	41.5	37.5	MKP4F053907K00
47 "	35	50	41.5	37.5	MKP4D054707J00					
56 "	35	50	41.5	37.5	MKP4D055607J00					
68 "	40	55	41.5	37.5	MKP4D056807K00					

* AC voltage: $f \leq 400 \text{ Hz}$; $1.4 \times U_{\text{rms}} + U_{\text{DC}} \leq U_{\text{r}}$

** PCM = Printed circuit module = pin spacing

Dims. in mm.

Rights reserved to amend design data without prior notification.

Continuation

General Data

Capacitance	400 VDC/220 VAC*					630 VDC/280 VAC*									
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number					
0.01 μF	3	8.5	10	7.5	MKP4G021002B00_____	3	8.5	10	7.5	MKP4J021002B00_____					
0.015 "	4	9	10	7.5	MKP4G021502C00_____	4	9	13	10	MKP4J021003C00_____					
	4	9	13	10	MKP4G021503C00_____	4	9	13	10	MKP4J021502C00_____					
0.022 "	4.5	9.5	10.3	7.5	MKP4G022202D00_____	4.5	9.5	10.3	7.5	MKP4J022202D00_____					
	4	9	13	10	MKP4G022203C00_____	4	9	13	10	MKP4J022203C00_____					
0.033 "	5	10.5	10.3	7.5	MKP4G023302E00_____	5	10.5	10.3	7.5	MKP4J023302E00_____					
	4	9	13	10	MKP4G023303C00_____	4	9	13	10	MKP4J023303C00_____					
0.047 "	5	10.5	10.3	7.5	MKP4G024702E00_____	5.7	12.5	10.3	7.5	MKP4J024702F00_____					
	5	11	13	10	MKP4G024703F00_____	5	11	13	10	MKP4J024703F00_____					
0.068 "	5.7	12.5	10.3	7.5	MKP4G026802F00_____	6	12	13	10	MKP4J026803G00_____					
	5	11	13	10	MKP4G026803F00_____	6	12.5	18	15	MKP4J026804C00_____					
0.1 μF	6	12	13	10	MKP4G031003G00_____	7	14	18	15	MKP4J031004D00_____					
	5	11	18	15	MKP4G031004B00_____	8	15	18	15	MKP4J031504F00_____					
0.15 "	6	12.5	18	15	MKP4G031504C00_____										
0.22 "	7	14	18	15	MKP4G032204D00_____						6	15	26.5	22.5	MKP4J031505B00_____
						9	16	18	15	MKP4J032204J00_____					
7						16.5	26.5	22.5	MKP4J032205D00_____						
0.33 "	8	15	18	15	MKP4G033304F00_____	8.5	18.5	26.5	22.5	MKP4J033305F00_____					
	6	15	26.5	22.5	MKP4G033305B00_____	10.5	19	26.5	22.5	MKP4J034705G00_____					
0.47 "	7	16.5	26.5	22.5	MKP4G034705D00_____										
0.68 "	8.5	18.5	26.5	22.5	MKP4G036805F00_____						11	21	31.5	27.5	MKP4J034706B00_____
						11	21	31.5	27.5	MKP4J036806B00_____					
1.0 μF						11	21	26.5	22.5	MKP4G041005I00_____	14.5	29.5	26.5	22.5	MKP4J041005M00_____
	11	21	31.5	27.5	MKP4G041006B00_____	13	24	31.5	27.5	MKP4J041006D00_____					
1.2 "	11	21	31.5	27.5	MKP4G041206B00_____	15	26	31.5	27.5	MKP4J041206F00_____					
1.5 "	11	21	31.5	27.5	MKP4G041506B00_____	15	26	31.5	27.5	MKP4J041506F00_____					
						13	24	41.5	37.5	MKP4J041507C00_____					
17						29	31.5	27.5	MKP4J041806G00_____						
1.8 "	14.5	29.5	26.5	22.5	MKP4G041805M00_____	17	29	31.5	27.5	MKP4J041806G00_____					
	13	24	31.5	27.5	MKP4G041806D00_____	15	26	41.5	27.5	MKP4J041807D00_____					
2.2 "	15	26	31.5	27.5	MKP4G042206F00_____	17	34.5	31.5	27.5	MKP4J042206I00_____					
	13	24	41.5	37.5	MKP4G042207C00_____	17	29	41.5	37.5	MKP4J042207E00_____					
2.7 "	17	29	31.5	27.5	MKP4G042706G00_____	17	29	41.5	37.5	MKP4J042707E00_____					
3.3 "	17	29	31.5	27.5	MKP4G043306G00_____	20	39.5	31.5	27.5	MKP4J043306J00_____					
	15	26	41.5	37.5	MKP4G043307D00_____	19	32	41.5	37.5	MKP4J043307F00_____					
4.7 "	20	39.5	31.5	27.5	MKP4G044706J00_____	20	39.5	41.5	37.5	MKP4J044707G00_____					
	19	32	41.5	37.5	MKP4G044707F00_____	24	45.5	41.5	37.5	MKP4J045607H00_____					
5.6 "	20	39.5	41.5	37.5	MKP4G045607G00_____										
6.8 "	20	39.5	41.5	37.5	MKP4G046807G00_____	28	38	41.5	37.5	MKP4J045607L00_____					
						24	45.5	41.5	37.5	MKP4J046807H00_____					
						28	38	41.5	37.5	MKP4J046807L00_____					
8.2 "	24	45.5	41.5	37.5	MKP4G048207H00_____	31	46	41.5	37.5	MKP4J048207I00_____					
10 μF	24	45.5	41.5	37.5	MKP4G051007H00_____	35	50	41.5	37.5	MKP4J051007J00_____					
	28	38	41.5	37.5	MKP4G051007L00_____										
12 "	31	46	41.5	37.5	MKP4G051207I00_____						40	55	41.5	37.5	MKP4J051207K00_____
15 "	31	46	41.5	37.5	MKP4G051507I00_____										
18 "	35	50	41.5	37.5	MKP4G051807J00_____										
22 "	40	55	41.5	37.5	MKP4G052207K00_____										


* AC voltages: $f \leq 400 \text{ Hz}$; $1.4 \times U_{\text{rms}} + U_{\text{DC}} \leq U_r$

New values and box sizes.
The box sizes according
main catalogue 2019 are
still available on request.

** PCM = Printed circuit module
= pin spacing

Dims. in mm.

Rights reserved to amend design data without prior notification.



Ø d	PCM	W
0.5	7.5	= 3
0.6	7.5	≥ 4
0.6	10	
0.8	15 - 27.5	
1.0	37.5	

Part number completion:

Tolerance: 20 % = M
10 % = K
5 % = J

Packing: bulk = S

Pin length: 6-2 = SD

Taped version see page 170.

Continuation

General Data


Capacitance	1000 VDC/400 VAC*					1250 VDC/500 VAC*				
	W	H	L	PCM**	Part number	W	H	L	PCM**	Part number
0.01 μF	5.7	12.5	10.3	7.5	MKP4O121002F00_____	5	11	18	15	MKP4R021004B00_____
0.015 "	5	11	13	10	MKP4O121003F00_____	6	12.5	18	15	MKP4R021504C00_____
	5	11	18	15	MKP4O121504B00_____					
0.022 "	5	11	18	15	MKP4O122204B00_____	7	14	18	15	MKP4R022204D00_____
0.033 "	6	12.5	18	15	MKP4O123304C00_____	8	15	18	15	MKP4R023304F00_____
0.047 "	7	14	18	15	MKP4O124704D00_____	6	15	26.5	22.5	MKP4R024705B00_____
0.068 "	8	15	18	15	MKP4O126804F00_____	7	16.5	26.5	22.5	MKP4R026805D00_____
	6	15	26.5	22.5	MKP4O126805B00_____					
0.1 μF	9	16	18	15	MKP4O131004J00_____	10.5	19	26.5	22.5	MKP4R031005G00_____
	7	16.5	26.5	22.5	MKP4O131005D00_____	9	19	31.5	27.5	MKP4R031006A00_____
0.15 "	8.5	18.5	26.5	22.5	MKP4O131505F00_____	11	21	31.5	27.5	MKP4R031506B00_____
0.22 "	11	21	26.5	22.5	MKP4O132205I00_____	14.5	29.5	26.5	22.5	MKP4R032205M00_____
	11	21	31.5	27.5	MKP4O132206B00_____	13	24	31.5	27.5	MKP4R032206D00_____
0.33 "	11	21	31.5	27.5	MKP4O133306B00_____	15	26	31.5	27.5	MKP4R033306F00_____
						13	24	41.5	37.5	MKP4R033307C00_____
0.47 "	14.5	29.5	26.5	22.5	MKP4O134705M00_____	17	34.5	31.5	27.5	MKP4R034706I00_____
	13	24	31.5	27.5	MKP4O134706D00_____	15	26	41.5	37.5	MKP4R034707D00_____
0.68 "	17	29	31.5	27.5	MKP4O136806G00_____	20	39.5	31.5	27.5	MKP4R036806J00_____
	15	26	41.5	37.5	MKP4O136807D00_____	19	32	41.5	37.5	MKP4R036807F00_____
1.0 μF	20	39.5	31.5	27.5	MKP4O141006J00_____	20	39.5	41.5	37.5	MKP4R041007G00_____
	17	29	41.5	37.5	MKP4O141007E00_____					
1.2 "	19	32	41.5	37.5	MKP4O141207F00_____	20	39.5	41.5	37.5	MKP4R041207G00_____
1.5 "	20	39.5	41.5	37.5	MKP4O141507G00_____	24	45.5	41.5	37.5	MKP4R041507H00_____
1.8 "	20	39.5	41.5	37.5	MKP4O141807G00_____	24	45.5	41.5	37.5	MKP4R041807H00_____
2.2 "	24	45.5	41.5	37.5	MKP4O142207H00_____	31	46	41.5	37.5	MKP4R042207I00_____
	28	38	41.5	37.5	MKP4O142207L00_____					
2.7 "	31	46	41.5	37.5	MKP4O142707I00_____	35	50	41.5	37.5	MKP4R042707J00_____
3.3 "	31	46	41.5	37.5	MKP4O143307I00_____	40	55	41.5	37.5	MKP4R043307K00_____
3.9 "	35	50	41.5	37.5	MKP4O143907J00_____					
4.7 "	35	50	41.5	37.5	MKP4O144707J00_____					

* AC voltages: $f \leq 400 \text{ Hz}$; $1.4 \times U_{\text{rms}} + U_{\text{DC}} \leq U_r$

New values, box sizes and range. The box sizes according to main catalogue 2019 are still available on request.

** PCM = Printed circuit module = pin spacing

Dims. in mm.



$\varnothing d$	PCM	W
0.5	7.5	= 3
0.6	7.5	≥ 4
0.6	10	
0.8	15 - 27.5	
1.0	37.5	

Part number completion:

Tolerance: 20 % = M
10 % = K
5 % = J

Packing: bulk = S

Pin length: 6-2 = SD

Taped version see page 170.

Rights reserved to amend design data without prior notification.

Continuation page 64

Recommendation for Processing and Application of Through-Hole Capacitors

Soldering Process

Internal temperature of the capacitor must be kept as follows:

Polyester: preheating: $T_{\max.} \leq 125^{\circ}\text{C}$
soldering: $T_{\max.} \leq 135^{\circ}\text{C}$

Polypropylene: preheating: $T_{\max.} \leq 100^{\circ}\text{C}$
soldering: $T_{\max.} \leq 110^{\circ}\text{C}$

Single wave soldering

Soldering bath temperature: $T < 260^{\circ}\text{C}$


Dwell time: $t < 5\text{ sec}$

Double wave soldering

Soldering bath temperature: $T < 260^{\circ}\text{C}$

Dwell time: $\Sigma t < 5\text{ sec}$

Due to different soldering processes and heat requirements the graphs are to be regarded as a recommendation only.



WIMA Quality and Environmental Philosophy

ISO 9001:2015 Certification

ISO 9001:2015 is an international basic standard of quality assurance systems for all branches of industry. The approval according to ISO 9001:2015 of our factories by the infaz (Institut für Auditierung und Zertifizierung) certifies that organisation, equipment and monitoring of quality assurance in our factories correspond to internationally recognized standards.

WIMA WPCS

The WIMA Process Control System (WPCS) is a quality surveillance and optimization system developed by WIMA. WPCS is a major part of the quality-oriented WIMA production. Points of application during production process:

- incoming material inspection
- metallization
- film inspection
- schoopage
- pre-healing
- pin attachment
- cast resin preparation/encapsulation
- 100% final inspection
- Testing as per customer requirements

WIMA Environmental Policy

All WIMA capacitors, irrespective of whether through-hole devices or SMD, are made of environmentally friendly materials. Neither during manufacture nor in the product itself any toxic substances are used, e.g.

- | | |
|------------------------|------------|
| - Lead | - PBB/PBDE |
| - PCB | - Arsenic |
| - CFC | - Cadmium |
| - Hydrocarbon chloride | - Mercury |
| - Chromium 6+ | - etc. |

We merely use pure, recyclable materials for packing our components, such as:

- carton
- cardboard
- adhesive tape made of paper
- polystyrene

We almost completely refrain from using packing materials such as:

- adhesive tapes made of plastic
- metal clips

RoHS Compliance

According to the RoHS Directive 2011/65/EU as amended from time to time certain hazardous substances like e.g. lead, cadmium, mercury must not be used any longer in electronic equipment as of July 1st, 2006. For the sake of the environment WIMA has refrained from using such substances since years already.



WIMA Kondensatoren sind bleifrei konform RoHS 2011/65/EU

WIMA capacitors are lead free in accordance with RoHS 2011/65/EU

Tape for lead-free WIMA capacitors

DIN EN ISO 14001:2004

WIMA's environmental management has been established in accordance with the guidelines of DIN EN ISO 14001:2004 to optimize the production processes with regard to energy and resources.

Typical Dimensions for Taping Configuration




Diagram 1:
PCM 2.5/5/7.5mm

Diagram 2: PCM 10/15 mm

Diagram 3: PCM 22.5 and 27.5*mm

*PCM 27.5 tapping possible with two feed holes between components

Designation	Symbol	Dimensions for Radial Taping						
		PCM 2.5 tapping	PCM 5 tapping	PCM 7.5 tapping	PCM 10 tapping*	PCM 15 tapping*	PCM 22.5 tapping	PCM 27.5 tapping
Carrier tape width	W	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5	18.0 ±0.5
Hold-down tape width	W ₀	6.0 for hot-sealing adhesive tape	6.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape	12.0 for hot-sealing adhesive tape
Hole position	W ₁	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5	9.0 ±0.5
Hold-down tape position	W ₂	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.	0.5 to 3.0 max.
Feed hole diameter	D ₀	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2	4.0 ±0.2
Pitch of component	P	12.7 ±1.0	12.7 ±1.0	12.7 ±1.0	25.4 ±1.0	25.4 ±1.0	38.1 ±1.5	38.1 ±1.5 or 50.8 ±1.5
Feed hole pitch	P ₀	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch	12.7 ±0.3 cumulative pitch error max. 1.0 mm/20 pitch
Feed hole centre to pin	P ₁	5.1 ±0.5	3.85 ±0.7	2.6 ±0.7	7.7 ±0.7	5.2 ±0.7	7.8 ±0.7	5.3 ±0.7
Hole centre to component centre	P ₂	6.35 ±1.3	6.35 ±1.3	6.35 ±1.3	12.7 ±1.3	12.7 ±1.3	19.05 ±1.3	19.05 ±1.3
Feed hole centre to bottom edge of the component	H	16.5 ±0.3 18.5 ±0.5	16.5 ±0.3 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5	16.5 ±0.5 18.5 ±0.5
Feed hole centre to top edge of the component	H ₁	H+H _{component} < H ₁ 32.25 max.	H+H _{component} < H ₁ 32.25 max.	H+H _{component} < H ₁ 24.5 to 31.5	H+H _{component} < H ₁ 25.0 to 31.5	H+H _{component} < H ₁ 26.0 to 37.0	H+H _{component} < H ₁ 30.0 to 43.0	H+H _{component} < H ₁ 35.0 to 45.0
Pin spacing at upper edge of carrier tape	F	2.5 ±0.5	5.0 ^{+0.8} _{-0.2}	7.5 ±0.8	10.0 ±0.8	15 ±0.8	22.5 ±0.8	27.5 ±0.8
Pin diameter	d	0.4 ±0.05	0.5 ±0.05	0.5 ±0.05 or 0.6 ^{+0.06} _{-0.05}	0.5 ±0.05 or 0.6 ^{+0.06} _{-0.05}	0.8 ^{+0.08} _{-0.05}	0.8 ^{+0.08} _{-0.05}	0.8 ^{+0.08} _{-0.05}
Component alignment	Δh	± 2.0 max.	± 2.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.	± 3.0 max.
Total tape thickness	t	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2	0.6 ±0.2
Package (see also page 171)		ROLL/AMMO			AMMO			
		REEL ø 360 max. ø 30 ±1	B 52 ±2 58 ±2 } depending on comp. dimensions		REEL ø 360 max. ø 30 ±1	52 ±2 B 58 ±2 or 66 ±2	REEL ø 500 max. ø 25 ±1	54 ±2 B 60 ±2 68 ±2 } depending on PCM and component dimensions
Unit		see details page 172.						

Dims in mm.

* Diameter of pins see General Data.


* PCM 10 and PCM 15 can be crimped to PCM 7.5.

Position of components according to PCM 7.5 (sketch 11). P₀ = 12.7 or 15.0 is possible


Please clarify customer-specific deviations with the manufacturer.

Types of Tape Packaging of Capacitors for Automatic Radial Insertion


■ ROLL Packaging



■ AMMO Packaging



■ REEL Packaging



BAR CODE (Labelling)

Labelling of package units in plain text and with alphanumerical Bar Code

- WIMA supplier number
- Date code
- Customer's P/O number
- P/O line
- Customer's part number
- WIMA part number
- Quantity
- WIMA confirmation number
- Country of origin
- Customer name
- Handling unit number
- Week of delivery.

In addition part description of

- article
- capacitance value
- rated voltage
- dimensions
- technical note
- capacitance tolerance
- packing
- connecting information

WIMA Best Capacitors Made in Germany	
Werk Aurich	
Supplier-ID:	Date Code: 20210216
	
Purchase Order No. (P/O): Bestellung xyz	P/O line:
	
Customer Part No.: KUNDENTEILENUMMER	
	
WIMA Part No.: MKP1F041006B00KSSD	Quantity: 459
	
WIMA Confirmation No.: 0001105072000100	
	
Customer No.: 0000100002	RoHS 2011/65/EU
Gross Weight [g]: 4557	000: DE
	
WIMA - MKP 10 WIMA Part No.: MKP1F041006B00KSSD	
MKP 10 1.0 µF 250 VDC 11x21x31.5 RM27.5	
Standard 10% Lose - Standard Drähte 6-2	
Vorlage Debitur Inland	
	0001105072000100
1001988917	QTY: 459 Week 19/2021

BARCODE PDF417

BARCODE 2D Datamatrix



Packing Quantities for Capacitors with Radial Pins in PCM 2.5 mm to 22.5 mm

PCM	Size				bulk	pcs. per packing unit									
						ROLL		REEL				AMMO			
	H16.5	H18.5	ø 360	ø 500		340 × 340		490 × 370							
	W	H	L	Codes	S	N	O	F	I	H	J	A	C	B	D
2.5 mm	2.5	7	4.6	0B	5000	2200		2500		–		2800		–	
	3	7.5	4.6	0C	5000	2000		2300		–		2300		–	
	3.8	8.5	4.6	0D	5000	1500		1800		–		1800		–	
	4.6	9	4.6	0E	5000	1200		1500		–		1500		–	
	5.5	10	4.6	0F	5000	900		1200		–		1200		–	
5 mm	2.5	6.5	7.2	1A	5000	2200		2500		–		2800		–	
	3	7.5	7.2	1B	5000	2000		2300		–		2300		–	
	3.5	8.5	7.2	1C	5000	1600		2000		–		2000		–	
	4.5	6	7.2	1D	6000	1300		1500		–		1500		–	
	4.5	9.5	7.2	1E	4000	1300		1500		–		1500		–	
	5	10	7.2	1F	3500	1100		1400		–		1400		–	
	5.5	7	7.2	1G	4000	1000		1200		–		1200		–	
	5.5	11.5	7.2	1H	2500	1000		1200		–		1200		–	
	6.5	8	7.2	1I	2500	800		1000		–		1000		–	
	7.2	8.5	7.2	1J	2500	700		1000		–		1000		–	
	7.2	13	7.2	1K	2000	700		950		–		1000		–	
	8.5	10	7.2	1L	2000	600		800		–		800		–	
	8.5	14	7.2	1M	1500	600		800		–		800		–	
11	16	7.2	1N	1000	500		600		–		640		–		
7.5 mm	2.5	7	10	2A	5000	–		2500		4400		2500		–	
	3	8.5	10	2B	5000	–		2200		4300		2300		4150	
	4	9	10	2C	4000	–		1700		3200		1700		3100	
	4.5	9.5	10.3	2D	3500	–		1500		2900		1400		2700	
	5	10.5	10.3	2E	3000	–		1300		2500		1300		–	
	5.7	12.5	10.3	2F	2000	–		1000		2200		1100		–	
	7.2	12.5	10.3	2G	1500	–		900		1800		1000		–	
10 mm	3	9	13	3A	3000	–		1100		2200		–		1900	
	4	8.5	13.5	3A	3000	–		900		1600		–		1450	
	4	9	13	3C	3000	–		900		1600		–		1450	
	4	9.5	13	3D	3000	–		900		1600		–		1400	
	5	10	13.5	3B	2000	–		700		1300		–		1200	
	5	11	13	3F	3000	–		700		1300		–		1200	
	6	12	13	3G	2400	–		550		1100		–		1000	
	6	12.5	13	3H	2400	–		550		1100		–		1000	
8	12	13	3I	2000	–		400		800		–		740		
15 mm	5	11	18	4B	2400	–		600		1200		–		1150	
	5	13	19	4C	1000	–		600		1200		–		1200	
	6	12.5	18	4C	2000	–		500		1000		–		1000	
	6	14	19	4D	1000	–		500		1000		–		1000	
	7	14	18	4D	1600	–		450		900		–		850	
	7	15	19	4E	1000	–		450		900		–		850	
	8	15	18	4F	1200	–		400		800		–		740	
	8	17	19	4F	500	–		400		800		–		740	
	9	14	18	4H	1200	–		350		700		–		650	
	9	16	18	4J	900	–		350		700		–		650	
	10	18	19	4G	500	–		300		650		–		590	
11	14	18	4M	1000	–		300		600		–		540		
22.5 mm	5	14	26.5	5A	1200	–		–		800		–		770	
	6	15	26.5	5B	1000	–		–		700		–		640	
	7	16.5	26.5	5D	760	–		–		600		–		550	
	8	20	28	5H	500	–		–		500		–		480	
	8.5	18.5	26.5	5F	500	–		–		480		–		450	
	10	22	28	5I	570*	–		–		420		–		380	
	10.5	19	26.5	5G	594*	–		–		400		–		360	
	10.5	20.5	26.5	5H	594*	–		–		400		–		360	
	11	21	26.5	5I	561*	–		–		380		–		350	
	12	24	28	5J	480*	–		–		350		–		310	
	14.5	29.5	26.5	5M	286*	–		–		on request		–		on request	

* TPS (Tray-Packing-System). Plate versions may have different packing units.
Samples and pre-production needs on request.

■ Moulded versions.

Rights reserved to amend design data without prior notification.

Packing Quantities for Capacitors with Radial Pins in PCM 27.5 mm to 52.5 mm

PCM	Size				bulk	ROLL		pcs. per packing unit				AMMO			
								REEL							
	W	H	L	Codes		H16.5	H18.5	ø 360	ø 500	H16.5	H18.5	H16.5	H18.5	340 × 340	490 × 370
					S	N	O	F	I	H	J	A	C	B	D
27.5 mm	9	19	31.5	6A	567*	–	–	–	–	460/340*	–	–	–	420	–
	11	21	31.5	6B	459*	–	–	–	–	380/280*	–	–	–	350	–
	13	24	31.5	6D	378*	–	–	–	–	300	–	–	–	290	–
	13	25	33	FK	405*	–	–	–	–	–	–	–	–	–	–
	15	26	31.5	6F	324*	–	–	–	–	270	–	–	–	250	–
	15	26	33	FL	324*	–	–	–	–	–	–	–	–	–	–
	17	29	31.5	6G	198*	–	–	–	–	–	–	–	–	–	–
	17	34.5	31.5	6I	198*	–	–	–	–	–	–	–	–	–	–
	20	32	33	FM	162*	–	–	–	–	–	–	–	–	–	–
	20	39.5	31.5	6J	162*	–	–	–	–	–	–	–	–	–	–
37.5 mm	9	19	41.5	7A	441*	–	–	–	–	–	–	–	–	–	–
	11	22	41.5	7B	357*	–	–	–	–	–	–	–	–	–	–
	13	24	41.5	7C	294*	–	–	–	–	–	–	–	–	–	–
	15	26	41.5	7D	252*	–	–	–	–	–	–	–	–	–	–
	17	29	41.5	7E	154*	–	–	–	–	–	–	–	–	–	–
	19	32	41.5	7F	140*	–	–	–	–	–	–	–	–	–	–
	20	39.5	41.5	7G	126*	–	–	–	–	–	–	–	–	–	–
	24	45.5	41.5	7H	112*	–	–	–	–	–	–	–	–	–	–
	28	38	41.5	7L	84*	–	–	–	–	–	–	–	–	–	–
	31	46	41.5	7I	84*	–	–	–	–	–	–	–	–	–	–
	35	50	41.5	7J	35*	–	–	–	–	–	–	–	–	–	–
	40	55	41.5	7K	28*	–	–	–	–	–	–	–	–	–	–
48.5 mm	19	31	56	8D	120*	–	–	–	–	–	–	–	–	–	–
	23	34	56	8E	80*	–	–	–	–	–	–	–	–	–	–
	27	37.5	56	8H	84*	–	–	–	–	–	–	–	–	–	–
	33	48	56	8J	25*	–	–	–	–	–	–	–	–	–	–
	37	54	56	8L	25*	–	–	–	–	–	–	–	–	–	–
52.5 mm	25	45	57	9D	70*	–	–	–	–	–	–	–	–	–	–
	30	45	57	9E	60*	–	–	–	–	–	–	–	–	–	–
	35	50	57	9F	25*	–	–	–	–	–	–	–	–	–	–
	45	55	57	9H	20*	–	–	–	–	–	–	–	–	–	–
	45	65	57	9J	20*	–	–	–	–	–	–	–	–	–	–

* for 2-inch transport pitches.

* TPS (Tray-Packing-System). Plate versions may have different packing units.
Samples and pre-production needs on request.

■ Moulded versions. Rights reserved to amend design data without prior notification.

Updated data on www.wima.com

Field 1 - 4: Type description
Field 5 - 6: Rated voltage
Field 7 - 10: Capacitance
Field 11 - 12: Size and PCM
Field 13 - 14: Version code (e.g. Snubber versions)
Field 15: Capacitance tolerance
Field 16: Packing
Field 17 - 18: Pin length (untaped)

[illegible]

168