

## Han Pneumatic module, for 1,6+ 3+ 4mm



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 003 4501
Specification	Han Pneumatic module, for 1,6+ 3+ 4mm
HARTING eCatalogue	<a href="https://harting.com/09140034501">https://harting.com/09140034501</a>

### Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® Pneumatic module
Size of the module	Single module

### Version

Gender	Male Female
Number of contacts	3
Details	Please order contacts separately. Using of guiding pins is imperative!

### Technical characteristics

Limiting temperature	-40 ... +80 °C
Mating cycles	≥500

### Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	Blue
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



**Pushing Performance**  
Since 1945

## Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL

## Commercial data

Packaging size	2
Net weight	6 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140020115
eCl@ss	27440220 Module for industrial connectors (pneumatic)
ETIM	EC000438
UNSPSC 24.0	39121552