

YBM1CL1, Uninsulated Flag-Type Ring Terminal For 1 AWG

By Burndy

Catalog # **YBM1CL1**

Uninsulated Flag-Type Ring Terminal For 1 AWG.

Features


- Made of pure electrolytic copper for maximum conductivity and ductility
- Seamless extrusion tin plated to resist corrosion
- Beveled barrel for easy wire entry

General

Catalog Number	YBM1CL1
Connector Type	Flag Ring Terminal
Die Index	572
Feature - Barrel Style	Chamfered
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810080719
UPC 14 Digit GTIN	00781810080719

Dimensions

Dimension - B Length fraction	5/8 in
Dimension - B Length inch	0.59 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Length Overall inch	1.40 in
Dimension - N inch	0.3 in
Dimension - Outside Diameter inch	0.58 in
Dimension - Pad Width inch	0.66 in
Dimension - Z (inch)	0.42 in



Physical Attribute - Tongue Angle 90 Degree

Conductor Related

Conductor - Copper Str	AN 1
Aircraft Size	
Conductor - Copper Str Size	1
Conductor - Copper Str Size Range	1 AWG
Conductor Size	1 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications And Compliance

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	100
Pallet Quantity	57600

Product Assets

Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog
Customer Notices - Prop 65 Notice
Interactive Catalog - BURNDY Full-Line Digital Catalog
Sales Drawings - 50094169
Specifications - YBM1CL1



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
BRDY-YBM1CL1-SPEC-EN | REV 7/2025