





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/12/05	
A		REDRAWN	03/14/12	
B		UPDATE SPEC.	6/12/20	AY/RC



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-2

Insulator color: White

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Voltage rating: 250 VAC/DC

Current rating: 5A AC/DC

Insulation resistance: 1,000 Mohms min

Temperature Rating:

-25°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 2 thru 20

A = .156 [3.96] x No. of Positions

B = .156 [3.96] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED			ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
INCHES HOLES						
.X	± .10	Ø.X	±.10	TITLE .156 [3.96] POWER HEADER STRAIGHT, WITHOUT LOCK POLARIZER		
.XX	± .020	Ø.XX	±.015			
.XXX	± .015	Ø.XXX	±.010			
APPROVALS			DATE			
DRAWN		SS	4/12/05			
CHECKED						
APPROVED						
			SIZE X		PART NO. LHB-XX-SA2	
			REF: S00016T		REV. B	
			SCALE: NTS		SHEET 1 OF 1	