



MODU II SHROUDED POSTS

MODU II Stiftleiste

SINGLE ROW 3 TO 50 POS.
Einreihig 3 bis 50 pol.




DOUBLE ROW 2x3 TO 2x50 POS.
Zweireihig 2x3 bis 2x50 pol.




POS.	PART NUMBERS	PART NUMBERS	POS.	PART NUMBERS	PART NUMBERS
3 (2) TO 50	826467-3 BIS 5-826467-0	826468-3 BIS 5-826468-0	2x3 TO 2x50	826469-3 BIS 5-826469-0	826470-2 BIS 5-826470-0
	827295-2 BIS 3	827296-3 BIS 5-827296-0 3		827297-3 BIS 3	827298-3 BIS 3


MODU IV RECEPTACLE HOUSING
MODU IV Buchsengehäuse



SINGLE ROW
2 TO 36 POS.
Einreihig
2 bis 36 polig.




DOUBLE ROW
2x2 TO 2x36 POS.
Zweireihig
2x2 bis 2x36 polig



POS.	PART NUMBERS	POS.	PART NUMBERS	POS.	PART NUMBERS
2 TO 36	926475-2	2x2 TO 2x36	926476-2	2x3 TO 2x13	927009-3 3
	3-926475-6		3-926476-6		1-927009-3 3


RETENTION PLUG

Rastgabel




RETENTION PLUG
WITH STRAIN RELIEF


Rastgabel
mit Zugentlastung




KEYING PLUG
Kodierstift



KEYING BLOCK
Kodierblock



ASSEMBLED COMPONENTS
(FOR EXAMPLE)
Anwendungsbeispiel



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A.HO	08MAR1985	TE Connectivity	
DIMENSIONS: mm		CHK M.SCHAARSCHMIDT	02MAY1985		
TOLERANCES, UNLESS OTHERWISE SPECIFIED: ±0.2mm		APVD —	—	NAME AMPMODU II / AMPMODU IV	
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		PRODUCT SPEC —	—	SIZE A2	
MATERIAL —		APPLICATION SPEC —	—	CAGE CODE 00779	
FINISH —		WEIGHT —	—	DRAWING NO C=826467	
		CUSTOMER DRAWING		SCALE 2:1	RESTRICTED TO —
				SHEET 1 of 2	REV Y5

