

Johanson Part Number VPDP202W222K1GV001E

Johanson Part Number: VPDP202W222K1GV001E

Johanson Company: JDI

Legacy P/N: 202R29W222KV4E

Size for Capacitors (EIA): 1808

Description: Capacitors HVS PME, 1808, X7R, 2000V, 2200pF±10%, Ni/Sn (RoHS), 7" Reel Embossed Tape

Specification Number: None

Life Cycle Stage: Active

NCNR: No

AEC Q200 Qualified: No

Thickness (Max): 0.085

Schedule B: 8532.24.00.20

Thickness (Min): None

ITAR: No

End Band(Min): 0.01

ECCN: EAR99

End Band (max): 0.030

RoHS Compliance: Yes, RoHS 10/10

Standard Item: Yes

REACH: Yes

Lead Time Typical (Weeks)*: 16

Country of Origin: US, MX, TW, or CN

Length (Min): 0.165

Product Family: Capacitors

Length (Max): 0.205

Product Subfamily: Capacitors High Voltage SMD ≥ 500V

Width (Min):0.070

Capacitance Value: 2200.000

Width (Max): 0.090

Cap Unit of Meas: pF

Part Weight (mg): 89.00

Tolerance: ±10%

Packaged Width (lb) Arm: None

Voltage: 2000.0

Packaging: 7" Reel Embossed Tape

Dielectric Temp Coefficient: X7R

Packaging Qty: 2000

Termination: 68

Operating Temp Range: -55°C to +125°C

Marking: No Mark

Storage Temp Range (Packaged): +5°C to +40°C with RH 20% to 70%

Product Release Date: Jan. 3, 2006

Storage Temp Range (None Operating): -65°C to +125°C

Harmonization: 8532.24.00.20

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes.

Web Page Link: <https://www.johansondielectrics.com/high-voltage-mlc-capacitors>

Printed from: <https://www.johansontechnology.com/part/VPDP202W222K1GV001E/>