

C3M0060065L

Silicon Carbide Power MOSFET

C3M™ MOSFET Technology

N-Channel Enhancement Mode

Features

- 3rd generation SiC MOSFET technology
- Optimized package with separate driver source pin
- High blocking voltage with low on-resistance
- High-speed switching with low capacitances
- Fast intrinsic diode with low reverse recovery (Q_{rr})
- Halogen free, RoHS compliant



Benefits

- Reduce switching losses and minimize gate ringing
- Higher system efficiency
- Reduce cooling requirements
- Increase power density
- Increase system switching frequency

Applications

- Datacenter Power Supplies
- Telecom Power Supplies
- Energy Storage Systems
- Solar (PV) inverters
- High Voltage DC/DC converters

Package



Part Number	Package	Marking
C3M0060065L	TOLL	C3M0060065L

Maximum Ratings ($T_c = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter	Value	Unit	Note
$V_{DS\text{max}}$	Drain - Source Voltage	650	V	
$V_{GS\text{max}}$	Gate - Source Voltage	-8/+19	V	Note: 1
I_D	Continuous Drain Current, $V_{GS} = 15\text{ V}$	$T_c = 25^\circ\text{C}$	39	A
		$T_c = 100^\circ\text{C}$	25	
$I_{D(\text{pulse})}$	Pulsed Drain Current, Pulse width t_p limited by $T_{j\text{max}}$	99	A	Fig. 22
P_D	Power Dissipation, $T_c = 25^\circ\text{C}$, $T_j = 175^\circ\text{C}$	131	W	Fig. 20 Note: 2
T_j	Junction Temperature	-40 to +175	$^\circ\text{C}$	
T_c, T_{stg}	Case Temperature and Storage Temperature	-40 to +150	$^\circ\text{C}$	
T_L	Solder Temperature, 1.6mm (0.063") from case for 10s	260	$^\circ\text{C}$	

Note (1): Recommended turn off / turn on gate voltage V_{GS} - 4V...0V / +15V

Note (2): Verified by design

Electrical Characteristics ($T_c = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter	Min.	Typ.	Max.	Unit	Test Conditions	Note
$V_{(\text{BR})\text{DSS}}$	Drain-Source Breakdown Voltage	650			V	$V_{\text{GS}} = 0 \text{ V}, I_{\text{D}} = 100 \mu\text{A}$	
$V_{\text{GS}(\text{th})}$	Gate Threshold Voltage	1.8	2.8	3.6	V	$V_{\text{DS}} = V_{\text{GS}}, I_{\text{D}} = 3.64 \text{ mA}$	Fig. 11
			2.2		V	$V_{\text{DS}} = V_{\text{GS}}, I_{\text{D}} = 3.64 \text{ mA}, T_J = 175^\circ\text{C}$	
I_{DSS}	Zero Gate Voltage Drain Current		1	50	μA	$V_{\text{DS}} = 650 \text{ V}, V_{\text{GS}} = 0 \text{ V}$	
I_{GSS}	Gate-Source Leakage Current		10	250	nA	$V_{\text{GS}} = 15 \text{ V}, V_{\text{DS}} = 0 \text{ V}$	
$R_{\text{DS}(\text{on})}$	Drain-Source On-State Resistance		60	79	$\text{m}\Omega$	$V_{\text{GS}} = 15 \text{ V}, I_{\text{D}} = 13.2 \text{ A}$	Fig. 4, 5, 6
			84			$V_{\text{GS}} = 15 \text{ V}, I_{\text{D}} = 13.2 \text{ A}, T_J = 175^\circ\text{C}$	
g_{fs}	Transconductance		9		S	$V_{\text{DS}} = 20 \text{ V}, I_{\text{DS}} = 13.2 \text{ A}$	Fig. 7
			9			$V_{\text{DS}} = 20 \text{ V}, I_{\text{DS}} = 13.2 \text{ A}, T_J = 175^\circ\text{C}$	
C_{iss}	Input Capacitance		1170		pF	$V_{\text{GS}} = 0 \text{ V}, V_{\text{DS}} = 400 \text{ V}$	Fig. 17, 18
C_{oss}	Output Capacitance		72			$F = 1 \text{ MHz}$	
C_{rss}	Reverse Transfer Capacitance		6			$V_{\text{AC}} = 25 \text{ mV}$	
E_{oss}	C_{oss} Stored Energy		14		μJ	$V_{\text{DS}} = 600 \text{ V}, F = 1 \text{ MHz}$	
$C_{\text{o(er)}}$	Effective Output Capacitance (Energy Related)		85		pF	$V_{\text{GS}} = 0 \text{ V}, V_{\text{DS}} = 0 \dots 400 \text{ V}$	Note: 3
$C_{\text{o(tr)}}$	Effective Output Capacitance (Time Related)		122		pF		
E_{ON}	Turn-On Switching Energy (Body Diode FWD)		28		μJ	$V_{\text{DS}} = 400 \text{ V}, V_{\text{GS}} = -4 \text{ V}/15 \text{ V}, I_{\text{D}} = 13.2 \text{ A}, R_{\text{G(ext)}} = 2.5 \Omega, L = 135 \mu\text{H}, T_J = 25^\circ\text{C}$	
E_{OFF}	Turn-Off Switching Energy (Body Diode FWD)		11			FWD = Internal Body Diode	
$t_{\text{d(on)}}$	Turn-On Delay Time		6				
t_r	Rise Time		8		ns	$V_{\text{DD}} = 400 \text{ V}, V_{\text{GS}} = -4 \text{ V}/15 \text{ V}$	Fig. 26
$t_{\text{d(off)}}$	Turn-Off Delay Time		14			$I_{\text{D}} = 13.2 \text{ A}, R_{\text{G(ext)}} = 2.5 \Omega,$	
t_f	Fall Time		7			Timing relative to V_{DS} Inductive load	
$R_{\text{G(int)}}$	Internal Gate Resistance		4		Ω	$f = 1 \text{ MHz}, V_{\text{AC}} = 25 \text{ mV}$	
Q_{gs}	Gate to Source Charge		16		nC	$V_{\text{DS}} = 400 \text{ V}, V_{\text{GS}} = -4 \text{ V}/15 \text{ V}$	Fig. 12
Q_{gd}	Gate to Drain Charge		12			$I_{\text{D}} = 13.2 \text{ A}$	
Q_g	Total Gate Charge		46			Per IEC60747-8-4 pg 21	

Note (3): $C_{\text{o(er)}}$, a lumped capacitance that gives same stored energy as C_{oss} while V_{DS} is rising from 0 to 400V
 $C_{\text{o(tr)}}$, a lumped capacitance that gives same charging time as C_{oss} while V_{DS} is rising from 0 to 400V

Reverse Diode Characteristics ($T_c = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter	Typ.	Max.	Unit	Test Conditions	Note
V_{SD}	Diode Forward Voltage	4.6		V	$V_{GS} = -4\text{ V}, I_{SD} = 6.6\text{ A}, T_J = 25^\circ\text{C}$	Fig. 8, 9, 10
		4.1		V	$V_{GS} = -4\text{ V}, I_{SD} = 6.6\text{ A}, T_J = 175^\circ\text{C}$	
I_S	Continuous Diode Forward Current		22	A	$V_{GS} = -4\text{ V}, T_c = 25^\circ\text{C}$	
$I_{S,pulse}$	Diode pulse Current		99	A	$V_{GS} = -4\text{ V}, \text{ pulse width } t_p \text{ limited by } T_{jmax}$	
t_{rr}	Reverse Recover time	9		ns	$V_{GS} = -4\text{ V}, I_{SD} = 13.2\text{ A}, V_R = 400\text{ V}$ $dif/dt = 5570\text{ A}/\mu\text{s}, T_J = 25^\circ\text{C}$	Fig. 8, 9, 10
Q_{rr}	Reverse Recovery Charge	142		nC		
I_{rrm}	Peak Reverse Recovery Current	33		A		
t_{rr}	Reverse Recover time	10		ns	$V_{GS} = -4\text{ V}, I_{SD} = 13.2\text{ A}, V_R = 400\text{ V}$ $dif/dt = 2160\text{ A}/\mu\text{s}, T_J = 25^\circ\text{C}$	Fig. 8, 9, 10
Q_{rr}	Reverse Recovery Charge	60		nC		
I_{rrm}	Peak Reverse Recovery Current	10		A		

Thermal Characteristics

Symbol	Parameter	Typ.	Unit	Test Conditions	Note
R_{iJC}	Thermal Resistance from Junction to Case	0.89	°C/W		Fig. 21

Typical Performance





Figure 1. Output Characteristics $T_J = -40^\circ\text{C}$ Figure 2. Output Characteristics $T_J = 25^\circ\text{C}$ Figure 3. Output Characteristics $T_J = 175^\circ\text{C}$ 

Figure 4. Normalized On-Resistance vs. Temperature




Figure 5. On-Resistance vs. Drain Current For Various Temperatures




Figure 6. On-Resistance vs. Temperature For Various Gate Voltage

Typical Performance




Figure 7. Transfer Characteristic for Various Junction Temperatures




Figure 8. Body Diode Characteristic at $-40 \text{ }^\circ\text{C}$




Figure 9. Body Diode Characteristic at $25 \text{ }^\circ\text{C}$




Figure 10. Body Diode Characteristic at $175 \text{ }^\circ\text{C}$




Figure 11. Threshold Voltage vs. Temperature




Figure 12. Gate Charge Characteristics

Typical Performance







Figure 13. 3rd Quadrant Characteristic at $-40\text{ }^{\circ}\text{C}$ Figure 14. 3rd Quadrant Characteristic at $25\text{ }^{\circ}\text{C}$ Figure 15. 3rd Quadrant Characteristic at $175\text{ }^{\circ}\text{C}$

Figure 16. Output Capacitor Stored Energy



Typical Performance




Figure 19. Continuous Drain Current Derating vs. Case Temperature




Figure 20. Maximum Power Dissipation Derating vs. Case Temperature




Figure 21. Transient Thermal Impedance (Junction - Case)






Figure 22. Safe Operating Area

Figure 23. Clamped Inductive Switching Energy vs. Drain Current ($V_{DD} = 400V$)Figure 24. Clamped Inductive Switching Energy vs. $R_{G(ext)}$

Typical Performance




Figure 25. Clamped Inductive Switching Energy vs. Temperature




Figure 26. Switching Times vs. $R_{G(\text{ext})}$




Figure 27. Switching Times Definition



Test Circuit Schematic

Figure 28. Clamped Inductive Switching
Waveform Test Circuit


Package Dimensions





Recommended Solder Pad Layout

(Note: All Dimensions are listed in Millimeters)





Revision history

Document Version	Date of release	Description of changes
1.0	September-2022	Initial datasheet



Notes & Disclaimer

This document and the information contained herein are subject to change without notice. Any such change shall be evidenced by the publication of an updated version of this document by Wolfspeed. No communication from any employee or agent of Wolfspeed or any third party shall effect an amendment or modification of this document. No responsibility is assumed by Wolfspeed for any infringement of patents or other rights of third parties which may result from use of the information contained herein. No license is granted by implication or otherwise under any patent or patent rights of Wolfspeed.

Notwithstanding any application-specific information, guidance, assistance, or support that Wolfspeed may provide, the buyer of this product is solely responsible for determining the suitability of this product for the buyer's purposes, including without limitation for use in the applications identified in the next bullet point, and for the compliance of the buyers' products, including those that incorporate this product, with all applicable legal, regulatory, and safety-related requirements.

This product has not been designed or tested for use in, and is not intended for use in, applications in which failure of the product would reasonably be expected to cause death, personal injury, or property damage, including but not limited to equipment implanted into the human body, life-support machines, cardiac defibrillators, and similar emergency medical equipment, aircraft navigation, communication, and control systems, aircraft power and propulsion systems, air traffic control systems, and equipment used in the planning, construction, maintenance, or operation of nuclear facilities.

RoHS Compliance

The levels of RoHS restricted materials in this product are below the maximum concentration values (also referred to as the threshold limits) permitted for such substances, or are used in an exempted application, in accordance with EU Directive 2011/65/EC (RoHS2), as implemented January 2, 2013. RoHS Declarations for this product can be obtained from your Wolfspeed representative or from the Product Documentation sections of www.wolfspeed.com.

REACH Compliance

REACH substances of high concern (SVHCs) information is available for this product. Since the European Chemical Agency (ECHA) has published notice of their intent to frequently revise the SVHC listing for the foreseeable future, please contact your Wolfspeed representative to ensure you get the most up-to-date REACH SVHC Declaration. REACH banned substance information (REACH Article 67) is also available upon request.

Contact info:

4600 Silicon Drive
Durham, NC 27703 USA
Tel: +1.919.313.5300
www.wolfspeed.com/power

© 2022 Wolfspeed, Inc. All rights reserved. Wolfspeed® and the Wolfstreak logo are registered trademarks and the Wolfspeed logo is a trademark of Wolfspeed, Inc.
PATENT: <https://www.wolfspeed.com/legal/patents>

The information in this document is subject to change without notice.