
REVISIONS			
REV	ECN, ERN NO.	DATE	APPRD.
A	PRODUCT DRAWING	SEP26/08	K.L.



MECHANICAL DATA:

MATERIALS: ALL MATERIALS ARE RoHS COMPLIANT

SHELLS: STAMPED STEEL, TIN PLATED.


INSERT: HIGH TEMPERATURE RESISTANT THERMOPLASTIC, GLASS REINFORCED. FLAMMABILITY RATING UL94V-0, BLACK


CONTACT: COPPER ALLOY, 30 MICROINCHES [0.76 MICRONS] GOLD PLATED OVER NICKEL


HARDWARE: STEEL OR COPPER ALLOY, TIN PLATED.

ELECTRICAL DATA:

CURRENT RATING 40 AMPS







RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)

AMPHENOL PART NUMBER: FCE17-E2W2SB-4N1

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

DRAWN	K. LAMBIE	DATE SEP26/08
DESIGNED		
CHECKED		
I. E. APPRD.		
Q. A. APPRD.		
DWG. APPRD.		
ENG. REL. NO.	EAR 13352	
REF.		
DIMENSIONS ARE IN	INCHES [mm]	CODE ID. NO. 03554

Amphenol Canada Corp.

FCE17 COMBINATION 2W2 D-SUB SOCKET CONNECTOR, MIXED PIN & SOCKET 90° BEND POWER CONTACTS, 4-40 MTG HOLE, METAL BRACKETS, RoHS COMPLIANT

DWG	DRAWING NO.	REV.
C	P-FCE17-E2W2SB-4N1	A

SCALE 4/1 WT. ------ SURF. ----- SHEET 1 OF 1

Downloaded from Arrow.com.