




Part Number : [5025982593](#)
Product Description : 0.30mm Pitch Easy-On Back Flip FPC Connector, Right-Angle, Surface Mount, Dual Contact Style, 1.15mm Mated Height, 25 Circuits
Series Number : 502598
Status : Active
Product Category : FFC / FPC Connectors



Documents & Resources


Drawings
[Drawing 5025982593_sd.pdf](#)

3D Models and Design Files
[3D Model 5025982593_stp.zip](#)

Specifications
[Packaging Specification SPK-502598-001-001.pdf](#)
[Product Specification PS-502598-002-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents
- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	FFC / FPC Connectors
Series	502598
Description	0.30mm Pitch Easy-On Back Flip FPC Connector, Right-Angle, Surface Mount, Dual Contact Style, 1.15mm Mated Height, 25 Circuits
Product Family	Easy-On FFC FPC Connectors
Product Name	Easy-On
UPC	887191146454

Electrical

Current - Maximum per Contact	0.3A
Voltage - Maximum	50V

Physical

Actuator Type	Back Flip
Circuits (Loaded)	25
Color - Resin	Black, White
Contact Position	Dual
Durability (mating cycles max)	10
Mated Height	1.15mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	67.800/mg
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
PCB Locator	No

PCB Mounting	Surface Mount
PCB Retention	Yes
Pitch - Mating Interface	0.30mm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire/Cable Type	FPC only

Mates With / Use With

Mates with Part(s)

Description	Part Number
0.30mm Pitch Premo-Flex Etched Copper Polyimide Jumpers	<u>15015</u>

This document was generated on Mar 23, 2024