




Part Number : [465574245](#)

Product Description : SEARAY Slim Receptacle, 160 Circuits, 6.00mm Unmated Height, 4 Rows, with Pegs, Solder Charge Lead-Free

Series Number : 46557

Status : Active

Product Category : Board-to-Board Connectors



Documents and Resources

Drawings

[465574245 sd.pdf](#)

[PK-45971-002-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[SYM-46557-4245-001.zip](#)

[EE-45970-010-010.pdf](#)

[SP-45970-010-010.zip](#)

Specifications

[AS-45970-001-001.pdf](#)

[AS-45970-002-001.pdf](#)

[AS-45970-990-001.pdf](#)


[PS-45970-001-001.pdf](#)

[TS-45970-001-001.pdf](#)

[TS-45970-002-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006

EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	46557
Description	SEARAY Slim Receptacle, 160 Circuits, 6.00mm Unmated Height, 4 Rows, with Pegs, Solder Charge Lead-Free
Application	Board-to-Board, Signal, Mezzanine
Component Type	Receptacle
Product Name	SEARAY
UPC	883906530518

Agency

CSA	LR19980
-----	---------

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	2.7A
Grounding to PCB	No
Voltage - Maximum	240V AC

Physical

Circuits (Loaded)	160
Circuits (maximum)	160
Color - Resin	Black
Durability (mating cycles max)	100
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	No
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	2.171/g
Number of Rows	4
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	2.18mm
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Robotic Placement	Pick and Place Cap

Stackable	No
Temperature Range - Operating	-55° to +125°C
Termination Interface Style	Surface Mount
Unmated Height	8.00mm

Solder Process Data

Max-Duration	20
Lead-Free Process Capability	REFLOW
Max-Cycle	3
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
Searay Slim Plugs	<u>46556</u>

This document was generated on Apr 15, 2026