

VS-04-2X2X26C7/7-SDA/SDB/1,0 - USB cable



1654853

<https://www.phoenixcontact.com/us/products/1654853>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assembled USB cable, shielded, color: RAL 5021 (water blue), PUR outer sheath, USB type A/standard on USB type B/standard, length: 1 m

Commercial data

Item number	1654853
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB14
Product key	ABNDBA
Catalog page	Page 452 (C-2-2019)
GTIN	4017918984199
Weight per piece (including packing)	84.3 g
Weight per piece (excluding packing)	84.3 g
Customs tariff number	85444290
Country of origin	DE

VS-04-2X2X26C7/7-SDA/SDB/1,0 - USB cable



1654853

<https://www.phoenixcontact.com/us/products/1654853>

Technical data

Product properties

Product type	Data cable preassembled
Sensor type	USB 2.0
Number of positions	4
Shielded	yes

Data management status

Article revision	04
------------------	----

Insulation characteristics

Degree of pollution	2
---------------------	---

Electrical properties

Rated voltage (III/3)	125 V
Rated current	1 A
Transmission medium	Copper
Transmission characteristics (category)	USB 2.0
Transmission speed	480 Mbps
Wave impedance	100 Ω

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	------------

Material specifications

Housing material	PA
Outer sheath, material	PUR
Conductor material	Bare Cu litz wires

Connector

Connection 1

Type	Plug straight USB type A
------	--------------------------

Connection 2

Type	Plug straight USB type B
------	--------------------------

Cable/line

Cable length	1.00 m
--------------	--------

FireWire [980]

Cable weight	59 kg/km
Number of positions	6
Shielded	yes

VS-04-2X2X26C7/7-SDA/SDB/1,0 - USB cable



1654853

<https://www.phoenixcontact.com/us/products/1654853>

Cable type	FireWire [980]
Conductor structure	2x2xAWG26/7 + 2xAWG20/19, S/FTP
Signal runtime	4.6 ns/m
Signal speed	0.72 c
Conductor structure signal line	7x 0.15 mm
AWG signal line	26
Conductor cross section	2x 2x 0.14 mm ² (Signal line)
	2x 0.5 mm ² (Power supply)
Wire diameter incl. insulation	≤ 1.05 mm (Signal line)
	nom. 1.4 mm (Power supply)
External cable diameter	6.70 mm
Outer sheath, material	PUR
External sheath, color	water blue RAL 5021
Conductor material	Bare Cu litz wires
Material wire insulation	Cell PE (Signal line)
	PVC (Power supply)
Single wire, color	white-blue, white-orange, white, black
Twisted pairs	2 cores to the pair
Type of pair shielding	Aluminum-lined polyester foil
Overall twist	Two pairs and two power supply wires to the core
Max. conductor resistance	150 Ω/km
Insulation resistance	5 GΩ*km
Coupling resistance	5.00 mΩ/m (at 10 MHz)
Wave impedance	100 Ω ±5 % (at 100 MHz)
Working capacitance	42 pF (per meter)
Nominal voltage, cable	≤ 125 V
Test voltage	1000 V
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	5 x D
Smallest bending radius, fixed installation	34 mm
Smallest bending radius, movable installation	34 mm
Tensile strength	≤ 30 N
Shield attenuation	60.00 dB (up to 1000 MHz)
Flame resistance	complying with IEC 60332-2-2
Resistance to oil	in accordance with EN 60811-2-1
Other resistance	Microbe resistance as per DIN VDE 0282
	Hydrolysis resistance as per DIN 53504
Special properties	Free of substances which would hinder coating with paint or varnish
Ambient temperature (operation)	-40 °C ... 70 °C (cable, fixed installation)
	-10 °C ... 50 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

VS-04-2X2X26C7/7-SDA/SDB/1,0 - USB cable



1654853

<https://www.phoenixcontact.com/us/products/1654853>

Degree of protection	IP20
	IP20
Ambient temperature (operation)	-20 °C ... 60 °C (cable, fixed installation)
	0 °C ... 50 °C (Cable, flexible installation)
	Plug / socket

VS-04-2X2X26C7/7-SDA/SDB/1,0 - USB cable


1654853

<https://www.phoenixcontact.com/us/products/1654853>




Drawings

Schematic diagram



Pin assignment plug USB, type A

Schematic diagram



Plug pin assignment plug USB, type B


VS-04-2X2X26C7/7-SDA/SDB/1,0 - USB cable

1654853

<https://www.phoenixcontact.com/us/products/1654853>



Circuit diagram



VS-04-2X2X26C7/7-SDA/SDB/1,0 - USB cable

1654853

<https://www.phoenixcontact.com/us/products/1654853>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1654853>



EAC

Approval ID: 19060508

VS-04-2X2X26C7/7-SDA/SDB/1,0 - USB cable



1654853

<https://www.phoenixcontact.com/us/products/1654853>

Classifications

ECLASS

ECLASS-11.0	27060390
ECLASS-12.0	27060390
ECLASS-13.0	27060390

ETIM

ETIM 9.0	EC000748
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

VS-04-2X2X26C7/7-SDA/SDB/1,0 - USB cable



1654853

<https://www.phoenixcontact.com/us/products/1654853>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com