

HB-2X2-WWW

~100° wide beam

SPECIFICATION:

Dimensions	50.0 x 50.0
Height	10 mm
Fastening	tape, screw
ROHS compliant	yes ⓘ


MATERIALS:

Component	Type	Material	Colour	Finish	Length (mm)
HB-2X2-WWW	Multi-lens	PMMA	clear		



ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
C14724_HB-2X2-WWW » Box size: 480 x 280 x 300 mm	800	160	160	11.7





See also our general installation guide: www.ledil.com/installation_guide

OPTICAL RESULTS (MEASURED):





LED Bridgelux SMD 5050
 FWHM / FWTM 94.0° / 133.0°
 Efficiency 94 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files





LED J Series 5050C 6V E Class
 FWHM / FWTM 89.0° / 127.0°
 Efficiency 94 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED XD16
 FWHM / FWTM 92.0° / 131.0°
 Efficiency 94 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):





LED XD16
 FWHM / FWTM 93.0° / 132.0°
 Efficiency 91 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED XHP35 HD
 FWHM / FWTM 101.0° / 132.0°
 Efficiency 79 %
 Peak intensity 0.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED XM-L3
 FWHM / FWTM 97.0° / 140.0°
 Efficiency 91 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:

Light distribution files

OPTICAL RESULTS (MEASURED):





LED XP-G2
 FWHM / FWTM 106.0° / 144.0°
 Efficiency 92 %
 Peak intensity 0.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED PL-BRICK HP 3800 2x8 SSG
 FWHM / FWTM 98.0° / 131.0°
 Efficiency 93 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED PrevaLED Brick HP 2x8
 FWHM / FWTM 104.0° / 132.0°
 Efficiency 94 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):




LED LUXEON 5050 Round LES
 FWHM / FWTM 93.0° / 133.0°
 Efficiency 93 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files





LED LUXEON MZ
 FWHM / FWTM 94.0° / 131.0°
 Efficiency 92 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED LUXEON V
 FWHM / FWTM 96.0° / 137.0°
 Efficiency 93 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):




LED LUXEON V2
 FWHM / FWTM 95.0° / 134.0°
 Efficiency 93 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files





LED SST-10-B130
 FWHM / FWTM 96.0° / 138.0°
 Efficiency 94 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type Deep Red
 Required components:



Light distribution files



LED RecLED 122x50mm 1900lm 730 2x4 Opt G1
 FWHM / FWTM 96.0° / 126.0°
 Efficiency 95 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):





LED NVSW219F
 FWHM / FWTM 102.0° / 140.0°
 Efficiency 93 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files





LED NVSW219F
 FWHM / FWTM 97.0° / 139.0°
 Efficiency 92 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED NVSW319B
 FWHM / FWTM 104.0° / 144.0°
 Efficiency 92 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):





LED NVSW3x9A
 FWHM / FWTM 101.0° / 130.0°
 Efficiency 93 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files





LED NVSxE21A
 FWHM / FWTM 85.0° / 124.0°
 Efficiency 92 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED OSCONIQ C 3030
 FWHM / FWTM 89.0° / 123.0°
 Efficiency 95 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):

OSRAM
Opto Semiconductors


LED OSCONIQ P 3737 (3W version)
FWHM / FWTM 94.0° / 132.0°
Efficiency 93 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

OSRAM
Opto Semiconductors



LED OSLOM Square CSSRM2/CSSRM3
FWHM / FWTM 104.0° / 132.0°
Efficiency 94 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

OSRAM
Opto Semiconductors

LED OSLOM Square PC
FWHM / FWTM 105.0° / 136.0°
Efficiency 94 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):

OSRAM
Opto Semiconductors



LED OSLON SSL 80
FWHM / FWTM 82.0° / 124.0°
Efficiency 93 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

PHILIPS



LED Fortimo FastFlex LED 2x8 DA (U)HE
FWHM / FWTM 89.0° / 126.0°
Efficiency 96 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

PHILIPS

LED Fortimo FastFlex LED 2x8 DA G4
FWHM / FWTM 104.0° / 140.0°
Efficiency 92 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):

PHILIPS



LED	Fortimo FastFlex LED 2x8 DA G4+
FWHM / FWTM	101.0° / 136.0°
Efficiency	94 %
Peak intensity	0.4 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	



Light distribution files

PHILIPS


LED	Fortimo FastFlex LED 2x8 DA G5
FWHM / FWTM	95.0° / 129.0°
Efficiency	94 %
Peak intensity	0.4 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	



Light distribution files

SAMSUNG

LED	HiLOM RC12 Z (LH181B)
FWHM / FWTM	86.0° / 124.0°
Efficiency	96 %
Peak intensity	0.5 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	




Light distribution files

OPTICAL RESULTS (MEASURED):

SAMSUNG



LED HiLOM RH12 Z (LH351C)
FWHM / FWTM 98.0° / 133.0°
Efficiency 93 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

SAMSUNG



LED HiLOM RH16 (LH351C)
FWHM / FWTM 102.0° / 136.0°
Efficiency 94 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

SAMSUNG

LED HiLOM RM12 Z (LH502C)
FWHM / FWTM 91.0° / 129.0°
Efficiency 95 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):

SAMSUNG



LED HiLOM RM16 Z (LH502C)
 FWHM / FWTM 91.0° / 129.0°
 Efficiency 95 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

SAMSUNG



LED HiLOM RM8 Z (LH502C)
 FWHM / FWTM 91.0° / 129.0°
 Efficiency 96 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

SAMSUNG

LED LH351B
 FWHM / FWTM 102.0° / 135.0°
 Efficiency 81 %
 Peak intensity 0.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):

SAMSUNG


LED LH351D
 FWHM / FWTM 107.0° / 139.0°
 Efficiency 94 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

SAMSUNG



LED LH508A
 FWHM / FWTM 95.0° / 136.0°
 Efficiency 93 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED LED-Pa-L15c2W11c2-xxx-C050-01
 FWHM / FWTM 94.0° / 129.0°
 Efficiency 95 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):





LED 2x2 Y22 module - SMJQ-D48W16AA-XX
 FWHM / FWTM 83.0° / 126.0°
 Efficiency 93 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files





LED Z5M3
 FWHM / FWTM 96.0° / 137.0°
 Efficiency 93 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED Z5M4
 FWHM / FWTM 95.0° / 138.0°
 Efficiency 92 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):





LED Z8Y19
 FWHM / FWTM 83.0° / 126.0°
 Efficiency 93 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:



Light distribution files





LED Z8Y19
 FWHM / FWTM 83.0° / 126.0°
 Efficiency 93 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 4
 Light colour/type White
 Required components:



Light distribution files



LED Z8Y22
 FWHM / FWTM 85.0° / 126.0°
 Efficiency 94 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (MEASURED):



LED Z8Y22P
 FWHM / FWTM 93.0° / 134.0°
 Efficiency 94 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

TRIDONIC

LED RLE 2x4 2000lm HP EXC2 OTD
 FWHM / FWTM 99.0° / 134.0°
 Efficiency 94 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:

TRIDONIC

LED RLE 2x8 4000lm HP EXC2 OTD
 FWHM / FWTM 99.0° / 134.0°
 Efficiency 94 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):

TRIDONIC


LED RLE 2x8 6000lm HP HE EXC3 OTD
 FWHM / FWTM 91.0° / 129.0°
 Efficiency 95 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

TRIDONIC


LED RLE G1 49x121mm 2000lm xxx EXC OTD
 FWHM / FWTM 98.0° / 132.0°
 Efficiency 93 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

TRIDONIC

LED RLE G1 49x133mm 2000lm xxx EXC OTD
 FWHM / FWTM 98.0° / 132.0°
 Efficiency 94 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):

TRIDONIC



LED RLE G1 49x223mm 4000lm xxx EXC OTD
FWHM / FWTM 98.0° / 132.0°
Efficiency 93 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

TRIDONIC

LED RLE G1 49x245mm 4000lm xxx EXC OTD
FWHM / FWTM 98.0° / 132.0°
Efficiency 93 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED J Series 5050 Round LES
 FWHM / FWTM 98.0° / 131.0°
 Efficiency 94 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED J Series 5050B 6V K Class
 FWHM / FWTM 96.0° / 122.0°
 Efficiency 89 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

Protective plate, glass



LED J Series 5050B 6V K Class
 FWHM / FWTM 96.0° / 122.0°
 Efficiency 95 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED XHP35 HI
 FWHM / FWTM 99.0° / 133.0°
 Efficiency 93 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED XM-L RGBW (XMLDCL HI)
 FWHM / FWTM 102.0° / 126.0°
 Efficiency 95 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type RGBW
 Required components:



Light distribution files



LED XP-E2
 FWHM / FWTM 98.0° / 128.0°
 Efficiency 96 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED XP-G2 HE
 FWHM / FWTM 106.0° / 126.0°
 Efficiency 93 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED XP-G3
 FWHM / FWTM 96.0° / 130.0°
 Efficiency 91 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Protective plate, glass

Light distribution files



LED XP-G3
 FWHM / FWTM 98.0° / 132.0°
 Efficiency 94 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files


OPTICAL RESULTS (SIMULATED):



LED XP-G4
 FWHM / FWTM 99.0° / 126.0°
 Efficiency 90 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:


Protective plate, glass

Light distribution files



LED XP-L2
 FWHM / FWTM 104.0° / 129.0°
 Efficiency 94 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:


Light distribution files



LED XT-E
 FWHM / FWTM 96.0° / 126.0°
 Efficiency 89 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:

Protective plate, glass


Light distribution files



OPTICAL RESULTS (SIMULATED):




LED LUXEON 3535L
 FWHM / FWTM 92.0° / 128.0°
 Efficiency 94 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED LUXEON 5050 HE
 FWHM / FWTM 98.0° / 124.0°
 Efficiency 90 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Protective plate, glass

Light distribution files



LED LUXEON 5050 Square LES
 FWHM / FWTM 98.0° / 126.0°
 Efficiency 96 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):



LED LUXEON 5050 Square LES
 FWHM / FWTM 98.0° / 123.0°
 Efficiency 90 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:


Protective plate, glass



Light distribution files




LED LUXEON C
 FWHM / FWTM 108.0° / 140.0°
 Efficiency 94 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED LUXEON HL2X
 FWHM / FWTM 104.0° / 126.0°
 Efficiency 94 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED LUXEON HL4X
 FWHM / FWTM 104.0° / 122.0°
 Efficiency 95 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED LUXEON T
 FWHM / FWTM 112.0° / 135.0°
 Efficiency 92 %
 Peak intensity 0.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED LUXEON XR-HL2X (L2H2-xxxxxxxMLU010)
 FWHM / FWTM 104.0° / 124.0°
 Efficiency 85 %
 Peak intensity 0.3 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Protective plate, glass

Light distribution files

OPTICAL RESULTS (SIMULATED):




LED	LUXEON XR-HL2X (L2H2-xxxxxxxMLU010)
FWHM / FWTM	104.0° / 122.0°
Efficiency	95 %
Peak intensity	0.4 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	



Light distribution files



LED	SFT-40 Gen2
FWHM / FWTM	104.0° / 130.0°
Efficiency	86 %
Peak intensity	0.3 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	





Protective plate, glass

Light distribution files



LED	SFT-40 Gen2
FWHM / FWTM	106.0 + 105.0° / 132.0 + 130.0°
Efficiency	96 %
Peak intensity	0.4 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED SST-20 Gen2
 FWHM / FWTM 98.0° / 128.0°
 Efficiency 96 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED SST-20F-W
 FWHM / FWTM 98.0° / 126.0°
 Efficiency 96 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED SST-25-W
 FWHM / FWTM 98.0° / 126.0°
 Efficiency 96 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:





Light distribution files

OPTICAL RESULTS (SIMULATED):




LED SST-36F-W
 FWHM / FWTM 102.0° / 126.0°
 Efficiency 95 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED NV4WB35AM
 FWHM / FWTM 100.0° / 124.0°
 Efficiency 96 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED NVSxx19B/NVSxx19C
 FWHM / FWTM 100.0° / 127.0°
 Efficiency 95 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files


OPTICAL RESULTS (SIMULATED):

OSRAM
Opto Semiconductors

LED Duris S8
FWHM / FWTM 100.0° / 125.0°
Efficiency 91 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:

Protective plate, glass


Light distribution files



OSRAM
Opto Semiconductors

LED Duris S8
FWHM / FWTM 92.0° / 126.0°
Efficiency 94 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:


Light distribution files



OSRAM
Opto Semiconductors

LED OSCONIQ P 3030
FWHM / FWTM 96.0° / 130.0°
Efficiency 96 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:


Light distribution files



OPTICAL RESULTS (SIMULATED):

OSRAM
Opto Semiconductors


LED OSCONIQ P 3737 (2W version)
FWHM / FWTM 90.0° / 130.0°
Efficiency 94 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

OSRAM
Opto Semiconductors


LED OSCONIQ P 3737 (3W version)
FWHM / FWTM 93.0° / 130.0°
Efficiency 94 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

OSRAM
Opto Semiconductors

LED OSCONIQ P 3737 Flat
FWHM / FWTM 96.0° / 126.0°
Efficiency 96 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):

OSRAM
Opto Semiconductors


LED OSLON Pure 1414
FWHM / FWTM 97.0 + 96.0° / 122.0°
Efficiency 97 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

OSRAM
Opto Semiconductors

LED OSLON Square CSSRM2/CSSRM3
FWHM / FWTM 100.0° / 128.0°
Efficiency 85 %
Peak intensity 0.3 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Protective plate, glass

Light distribution files

OSRAM
Opto Semiconductors

LED OSLON Square Flat
FWHM / FWTM 97.0° / 123.0°
Efficiency 97 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):

OSRAM

Opto Semiconductors


LED	OSTAR Projection Compact (KW.CSLNM1.TG)
FWHM / FWTM	100.0° / 124.0°
Efficiency	97 %
Peak intensity	0.4 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	



Light distribution files

PHILIPS


LED	Fortimo FastFlex LED 2x8 DAX G4
FWHM / FWTM	98.0° / 132.0°
Efficiency	94 %
Peak intensity	0.4 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	



Light distribution files

SAMSUNG

LED	HiLOM RM16 Z (LH502C)
FWHM / FWTM	90.0° / 127.0°
Efficiency	88 %
Peak intensity	0.4 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	




Protective plate, glass

Light distribution files

OPTICAL RESULTS (SIMULATED):

SAMSUNG


LED LH502D
 FWHM / FWTM 97.0° / 124.0°
 Efficiency 98 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED MJT 5050
 FWHM / FWTM 98.0° / 122.0°
 Efficiency 95 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED SEOUL DC 5050 6V
 FWHM / FWTM 94.0° / 126.0°
 Efficiency 94 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED Z5M3-E1
 FWHM / FWTM 102.0° / 128.0° + 127.0°
 Efficiency 96 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED Z5M4-E1
 FWHM / FWTM 104.0° + 103.0° / 130.0°
 Efficiency 96 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files





LED Z5M4-E2
 FWHM / FWTM 104.0° / 128.0°
 Efficiency 96 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

OPTICAL RESULTS (SIMULATED):



GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 7
FI-24100 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Poznan, Poland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)