


Alchip™-MVY Series

- Endurance : 1,000 to 5,000 hours at 105°C
- Low impedance
- For digital equipment, especially DC-DC converters
- Solvent resistant type except 80 & 100V_{dc} (see PRECAUTIONS AND GUIDELINES)
- Vibration resistant structure
- RoHS2 Compliant
- AEC-Q200 compliant : Please contact Chemi-Con for more details, test data, information.




◆ SPECIFICATIONS

Items	Characteristics										
Category	-55 to +105°C (6.3 to 63V _{dc}) -40 to +105°C (80 & 100V _{dc})										
Temperature Range											
Rated Voltage Range	6.3 to 100V _{dc}										
Capacitance Tolerance	±20% (M) (at 20°C, 120Hz)										
Leakage Current	I=0.01CV or 3μA, whichever is greater. Where, I : Max. leakage current (μA), C : Nominal capacitance (μF), V : Rated voltage (V) (at 20°C after 2 minutes)										
Dissipation Factor (tan δ)	Rated voltage (V _{dc})		6.3V	10V	16V	25V	35V	50V	63V	80V	100V
	F55 to F80	0.24	0.20	0.16	0.14	0.12	0.12	—	—	—	—
	HA0 & JA0	0.28	0.24	0.20	0.16	0.14	0.12	—	—	—	—
Low Temperature Characteristics (Max. Impedance Ratio)	tan δ (Max.)	KE0 to MN0	0.26	0.22	0.18	0.16	0.14	0.12	0.14	0.10	0.10
	Rated voltage (V _{dc})		6.3V	10V	16V	25V	35V	50V	63V	80V	100V
	Z(-40°C)/Z(+20°C)	F55 to JA0	3	2	2	2	2	2	—	—	—
Endurance		KE0 to MN0	10	8	6	4	3	3	3	3	3
Shelf Life	The following specifications shall be satisfied when the capacitors are restored to 20°C after the rated voltage is applied for specified time at 105°C.										
	Time	F55 to F80 : 1,000 hours HA0 & JA0 : 2,000 hours KE0 to MN0 : 5,000 hours									
	Rated voltage	6.3V _{dc} (F55 to JA0)									
	Capacitance change	≤ ±30% of the initial value									
	D.F. (tan δ)	≤300% of the initial specified value									
	Leakage current	≤The initial specified value									
	Rated voltage	6.3V _{dc} (F55 to JA0)									
	Capacitance change	≤ ±30% of the initial value									
	D.F. (tan δ)	≤300% of the initial specified value									
	Leakage current	≤The initial specified value									



◆ DIMENSIONS [mm]

- Terminal Code : A
- Size code : F55 to MN0


- Terminal Code : G (Vibration resistant structure)
- Size code : F61 to MN0



Note : L±0.5 for HA0 to MN0




Note : L±0.5 for HA0 to MN0



■ : Dummy terminals

Size code	D	L	A	B	C	W	P
F55	6.3	5.2	6.6	6.6	7.2	0.5 to 0.8	1.9
F61	6.3	5.8	6.6	6.6	7.2	0.5 to 0.8	1.9
F80	6.3	7.7	6.6	6.6	7.2	0.5 to 0.8	1.9
HA0	8	10.0	8.3	8.3	9.0	0.7 to 1.1	3.1
JA0	10	10.0	10.3	10.3	11.0	0.7 to 1.1	4.5
KE0	12.5	13.5	13.0	13.0	13.7	1.0 to 1.3	4.2
KG5	12.5	16.0	13.0	13.0	13.7	1.0 to 1.3	4.2
LH0	16	16.5	17.0	17.0	18.0	1.0 to 1.3	6.5
LN0	16	21.5	17.0	17.0	18.0	1.0 to 1.3	6.5
MH0	18	16.5	19.0	19.0	20.0	1.0 to 1.3	6.5
MN0	18	21.5	19.0	19.0	20.0	1.0 to 1.3	6.5

◆ PART NUMBERING SYSTEM




Please refer to "Product code guide (surface mount type)"

◆ MARKING

F55 to JA0
EX) 6.3V100μF



KE0 to MN0
EX) 16V1,000μF





◆STANDARD RATINGS

WV (V _{dc})	Cap (μF)	Size code	Impedance (Ω max./20°C, 100kHz)	Rated ripple current (mA rms/105°C, 100kHz)	Part No.	WV (V _{dc})	Cap (μF)	Size code	Impedance (Ω max./20°C, 100kHz)	Rated ripple current (mA rms/105°C, 100kHz)	Part No.
6.3	100	F55	1.0	140	EMVY6R3ARA101MF55G	25	1,000	LH0	0.054	1,260	EMVY250□RA102MLH0S
	220	F55	1.0	140	EMVY6R3ARA221MF55G		1,000	MH0	0.054	1,350	EMVY250□RA102MMH0S
	330	F80	0.34	280	EMVY6R3□RA331MF80G		2,200	LN0	0.038	1,630	EMVY250□RA222MLN0S
	470	HA0	0.30	450	EMVY6R3□RA471MHA0G		2,200	MN0	0.038	1,750	EMVY250□RA222MMN0S
	680	HA0	0.30	450	EMVY6R3□RA681MHA0G		3,300	MN0	0.038	1,750	EMVY250□RA332MMN0S
	1,000	HA0	0.30	450	EMVY6R3□RA102MLH0S	35	22	F55	1.0	140	EMVY350ARA220MF55G
	1,500	JA0	0.15	670	EMVY6R3□RA152MJA0G		33	F55	1.0	140	EMVY350ARA330MF55G
	2,200	KE0	0.070	820	EMVY6R3□RA222MKE0S		47	F55	1.0	140	EMVY350ARA470MF55G
	2,200	LH0	0.054	1,260	EMVY6R3□RA222MLH0S		47	F61	1.0	140	EMVY350□RA470MF61G
	3,300	KG5	0.060	950	EMVY6R3□RA332MKG5S		68	F80	0.34	280	EMVY350□RA680MF80G
	3,300	MH0	0.054	1,350	EMVY6R3□RA332MMH0S		100	HA0	0.30	450	EMVY350□RA101MHA0G
	4,700	LN0	0.038	1,630	EMVY6R3□RA472MLN0S		220	HA0	0.30	450	EMVY350□RA221MHA0G
	4,700	MH0	0.054	1,350	EMVY6R3□RA472MMH0S		330	JA0	0.15	670	EMVY350□RA331MJA0G
	6,800	LN0	0.038	1,630	EMVY6R3□RA682MLN0S		470	KE0	0.070	820	EMVY350□RA471MKE0S
	6,800	MN0	0.038	1,750	EMVY6R3□RA682MMN0S		470	LH0	0.054	1,260	EMVY350□RA471MLH0S
	8,200	MN0	0.038	1,750	EMVY6R3□RA822MMN0S		1,000	LH0	0.054	1,260	EMVY350□RA102MLH0S
							1,000	MH0	0.054	1,350	EMVY350□RA102MMH0S
							2,200	MN0	0.038	1,750	EMVY350□RA222MMN0S
						50	10	F55	2.0	70	EMVY500ARA100MF55G
							22	F55	2.0	70	EMVY500ARA220MF55G
10	47	F55	1.0	140	EMVY100ARA470MF55G		33	F80	0.60	170	EMVY500□RA330MF80G
	100	F55	1.0	140	EMVY100ARA101MF55G		47	F80	0.60	170	EMVY500□RA470MF80G
	220	F80	0.34	280	EMVY100□RA221MF80G		68	HA0	0.60	300	EMVY500□RA680MHA0G
	330	HA0	0.30	450	EMVY100□RA331MHA0G		100	HA0	0.60	300	EMVY500□RA101MHA0G
	470	HA0	0.30	450	EMVY100□RA471MHA0G		220	JA0	0.30	500	EMVY500□RA221MJA0G
	680	JA0	0.15	670	EMVY100□RA681MJA0G		330	KE0	0.11	650	EMVY500□RA331MKE0S
	1,000	JA0	0.15	670	EMVY100□RA102MJA0G		330	LH0	0.087	900	EMVY500□RA331MLH0S
	2,200	KG5	0.060	950	EMVY100□RA222MKG5S		470	LH0	0.087	900	EMVY500□RA471MLH0S
	2,200	LH0	0.054	1,260	EMVY100□RA222MLH0S		470	MH0	0.087	1,060	EMVY500□RA471MMH0S
	3,300	LH0	0.054	1,260	EMVY100□RA332MLH0S		1,000	MN0	0.050	1,520	EMVY500□RA102MMN0S
	3,300	MH0	0.054	1,350	EMVY100□RA332MMH0S	63	68	KE0	0.19	500	EMVY630□RA680MKE0S
	4,700	LN0	0.038	1,630	EMVY100□RA472MLN0S		100	KE0	0.19	500	EMVY630□RA101MKE0S
	4,700	MN0	0.038	1,750	EMVY100□RA472MMN0S		220	KE0	0.19	500	EMVY630□RA221MKE0S
	6,800	MN0	0.038	1,750	EMVY100□RA682MMN0S		220	LH0	0.12	845	EMVY630□RA221MLH0S
16	33	F55	1.0	140	EMVY160ARA330MF55G		330	LH0	0.12	845	EMVY630□RA331MLH0S
	47	F55	1.0	140	EMVY160ARA470MF55G		330	MH0	0.12	905	EMVY630□RA331MMH0S
	100	F55	1.0	140	EMVY160ARA101MF55G		470	LN0	0.085	1,100	EMVY630□RA471MLN0S
	220	F80	0.34	280	EMVY160□RA221MF80G		470	MH0	0.12	905	EMVY630□RA471MMH0S
	330	HA0	0.30	450	EMVY160□RA331MHA0G	80	100	KE0	0.33	450	EMVY800□RA101MKE0S
	470	HA0	0.30	450	EMVY160□RA471MHA0G		220	KG5	0.26	550	EMVY800□RA221MKG5S
	680	JA0	0.15	670	EMVY160□RA681MJA0G		330	LN0	0.16	900	EMVY800□RA331MLN0S
	1,000	KE0	0.070	820	EMVY160□RA102MKE0S		330	MH0	0.24	700	EMVY800□RA331MMH0S
	1,000	LH0	0.054	1,260	EMVY160□RA102MLH0S		470	MN0	0.16	950	EMVY800□RA471MMN0S
	2,200	LH0	0.054	1,260	EMVY160□RA222MLH0S	100	47	KE0	0.33	450	EMVY101□RA470MKE0S
	2,200	MH0	0.054	1,350	EMVY160□RA222MMH0S		68	KE0	0.33	450	EMVY101□RA680MKE0S
	3,300	LN0	0.038	1,630	EMVY160□RA332MLN0S		100	KE0	0.33	450	EMVY101□RA101MKE0S
	3,300	MH0	0.054	1,350	EMVY160□RA332MMH0S		100	LH0	0.24	650	EMVY101□RA101MLH0S
	4,700	MN0	0.038	1,750	EMVY160□RA472MMN0S		220	LN0	0.16	900	EMVY101□RA221MLN0S
25	22	F55	1.0	140	EMVY250ARA220MF55G		220	MH0	0.24	700	EMVY101□RA221MMH0S
	33	F55	1.0	140	EMVY250ARA330MF55G		330	MN0	0.16	950	EMVY101□RA331MMN0S
	47	F55	1.0	140	EMVY250ARA470MF55G						
	100	F80	0.34	280	EMVY250□RA101MF80G						
	220	HA0	0.30	450	EMVY250□RA221MHA0G						
	330	HA0	0.30	450	EMVY250□RA331MHA0G						
	470	JA0	0.15	670	EMVY250□RA471MJA0G						

□ : Enter the appropriate terminal code.

*1: Assembly boards with the designated products attached cannot be cleaned.

◆RATED RIPPLE CURRENT MULTIPLIERS

●Frequency Multipliers

Size code	Capacitance(μF)	Frequency(Hz)	120	1k	10k	100k
F55 to JA0	10 to 100		0.40	0.75	0.90	1.00
	220 to 470		0.50	0.85	0.94	1.00
	680 to 1,500		0.60	0.87	0.95	1.00

Size code	Capacitance(μF)	Frequency(Hz)	120	1k	10k	100k
KE0 to MN0	47 to 100		0.40	0.75	0.90	1.00
	220 to 470		0.50	0.85	0.94	1.00
	1,000		0.60	0.87	0.95	1.00
	2,200 to 3,300		0.75	0.90	0.95	1.00
	4,700 to 8,200		0.85	0.95	0.98	1.00

The deterioration of aluminum electrolytic capacitors accelerates their life due to the internal heating produced by ripple current. For details, refer to Section "5-3 Ripple Current Effect on Lifetime" in the catalog, Technical Note.



- Always read "Notes on Use" before using the product in order to enable you to use the product correctly and prevent any faults and accidents from occurring.
- Request the Product Specification on the product of NIPPON CHEMI-CON CORPORATION to refer to it as well as this brochure prior to the order of the products. Some specific notes on use of the ordered product may be described in the specifications.
- The products listed in this catalog are designed and manufactured for general electronics equipment use and are not intended for use in applications that can adversely affect human life; where the malfunction of equipment may cause damage to life or property. In addition, our products are not intended to be used in specific applications that may cause a major social impact. Please consult with us in advance of usage of our products in the following listed applications. ① Aerospace equipment ② Power generation equipment such as thermal power, nuclear power etc. ③ Medical equipment ④ Transport equipment (automobiles, trains, ships, etc.) ⑤ Transportation control equipment ⑥ Disaster prevention / crime prevention equipment ⑦ Highly publicized information processing equipment ⑧ Submarine equipment ⑨ Other applications that are not considered general-purpose applications.
- The circuits described as examples in this catalog and the "delivery specifications" are featured in order to show the operations and usage of our products, however, this fact does not guarantee that the circuits are available to function in your equipment systems. We are not in any case responsible for any failures or damage caused by the use of information contained herein. You should examine our products, of which the characteristics are described in the "delivery specifications" and other documents, and determine whether or not our products suit your requirements according to the specifications of your equipment systems. Therefore, you bear final responsibility regarding the use of our products.
Please make sure that you take appropriate safety measures such as use of redundant design and malfunction prevention measures in order to prevent fatal accidents and/or fires in the event any of our products malfunction.
- We strongly recommend our customers to purchase Nippon Chemi-Con products only through our official sales channels. We assume no responsibility for any defects or damages caused by using products purchased from outside our official sales channel or of counterfeit goods. In addition, we will ask the customer to pay the investigation cost for products purchased outside our official sales channel.
- We reserve the right to discontinue production and delivery of products. We do not guarantee that all the products included in this catalog will be available in the future.
The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products
- We continually strive to improve the quality and reliability of our products, but in any case that our product does not meet our published specifications, please stop using it promptly and contact us immediately. As for compensation for non-conforming goods delivered by Chemi-Con, we will limit it only to goods found in non-compliance of our published specifications. This may be accomplished by a no cost replacement of non-conforming individual products, a credit of the piece price paid per each individual non-conforming product, or in other ways deemed necessary.
In addition, we have an established system with enhanced traceability, therefore we will limit the applicable lot items for any potential compensation.

[Part Numbering System](#)

[Part Numbering System \(Appendix\)](#)

[Standardization](#)

[Available Items by Manufacturing Locations](#)

[Environmental Measures](#)

[Technical Note](#)

[Precautions and Guidelines](#)

[Recommended Soldering Conditions](#)

[Taping, Lead-preforming and Packaging](#)

[Available Terminals for Snap-in and Screw Mount Type](#)