


Similar to illustration



- M12 sensor/actuator box, 8-way
- 4-pole (1 signal per contact)
- Cable length: 5, 10 and 25 m
- Green LED operating indicator
- Yellow LED status indicator
- incl. markers (10 pcs)
- incl. M12 protective caps (2 pcs)

Technical data	
Contact resistance (max.)	0.01 Ω
Supply voltage	10 ... 30 VDC; Rated voltage: 32 V ~ rms
Current carrying capacity (signal connections)	2 A
Current carrying capacity (supply connections)	9 A
Rated value of electrical isolation	500 V
Functionally separated potential groups	Kontakt/Kontakt
Insulation resistance	>10 ⁹ Ω
Signal characteristics	PNP
Indicators	LED (A) yellow: Signal status (1 x per contact); LED (U) green: Sensor/actuator box status



Connection data	
Connection technology: inputs/outputs	8 x M12 socket; 4-pole; incl. ground
Connection technology: trunk cable	1 x Fixed connecting cable
Length of connection cable	10 m
Strip length	100 mm / 3.94 inches
Wire colors	white, green, yellow, gray, pink, red, black, purple, green/yellow, brown, blue
Cable design	Wire cross-section: 0.34 mm²; Wire cross-section: 1 mm²

Physical data	
Width	60 mm / 2.362 inches
Height	26 mm / 1.024 inches
Depth	152 mm / 5.984 inches

Mechanical data	
Mounting type	Screw mount
Weight	1251 g

Material data	
Housing material	PA 66 (UL 94 V0); RAL 7035; silicon and halogen free
Halogen-free	Yes
Bending radius	10 x cable diameter (min.) for flexible application
Material properties of the connections	Contact: CuSn, nickel base-coat plating and 0.8 µm gold-plated; Threaded bush: die-cast Zn, nickel-plated; Seal: Viton; 50 mating cycles
Sheath material	PUR
Sheathed cable color	black
Encapsulation	Fully encapsulated with conformal coating (UL 94 V0)

Environmental requirements	
Ambient temperature (operation)	-25 ... +80 °C
Ambient (operating) temperature (dynamic)	-5 ... +80 °C
Ambient (operating) temperature (static)	-40 ... +90 °C
Protection type	IP68
Note on protection type	72 h at a depth of 1 m under water per EN 60529 in the fully locked position with its plugs or protective caps
Pollution degree	3 per VDE 0110
Vibration resistance	per IEC 60068-2-6
Shock resistance	per IEC 60068-2-27

Commercial data	
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4045454028473
Customs tariff number	85366990990



Product classification	
UNSPSC	39121421
eCl@ss 10.0	27-44-01-08
eCl@ss 9.0	27-44-01-08
ETIM 9.0	EC002585
ETIM 8.0	EC002585
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
CAS-No.	7439-92-1
REACH Candidate List Substance	Lead
RoHS Compliance Status	Compliant,With Exemption
RoHS Exemption	6(c)
SCIP notification number (Austria)	b9d8394a-26e5-4b08-bb8c-bbd37ffd8686
SCIP notification number (Belgium)	0109fbee-9e03-4177-9b3f-578dfe03645d
SCIP notification number (Bulgaria)	04ffc354-f292-439d-86da-01826d0ace2c
SCIP notification number (Czech Republic)	07428700-3862-4e55-b556-0417b59c59f1
SCIP notification number (Denmark)	5edb4956-fcf6-45d9-baba-6a9bdd152bf6
SCIP notification number (Finland)	6fddd376-cbcb-4611-a436-7d61f411d85a
SCIP notification number (France)	feeafeef-1c39-4078-b54a-b8d643bfeb0c
SCIP notification number (Germany)	9011bc3c-a73d-4bb5-b425-202324d705a2
SCIP notification number (Hungary)	f76e6ac9-7746-4634-ad97-db454695511c
SCIP notification number (Italy)	53471b99-c863-4893-9dff-16780cd6084c
SCIP notification number (Netherlands)	60e1f76d-b1cf-48cc-ab07-6616c0d89568
SCIP notification number (Poland)	f8e8398f-a747-4a8e-bc5e-98deca64e1c7
SCIP notification number (Romania)	894175fa-9ed6-4692-8be3-7ba87d21dd2c
SCIP notification number (Sweden)	77316688-6d14-411e-83e1-6315d2ebb961

Approvals / Certificates

General approvals



Approval	Standard	Certificate Name
UL UL International Germany GmbH (ORDINARY LOCATIONS)	UL 508	E175199 Sec.5

Downloads

Environmental Product Compliance

Compliance Search
Environmental Product Compliance 757-284/000-010





Documentation

System Description		
Sensor/Actuator Boxes – General Product Information	pdf 428.34 KB	

CAD/CAE-Data

CAD data	
2D/3D Models 757-284/000-010	

CAE data	
EPLAN Data Portal 757-284/000-010	
WSCAD Universe 757-284/000-010	
ZUKEN Portal 757-284/000-010	

1 Compatible Products

1.1 Optional Accessories

1.1.1 Cover

1.1.1.1 Cover



Item No.: 756-8102
M12 protective cap; for unused sockets

1.1.2 Installation

1.1.2.1 Intermediate plate



Item No.: 757-080
Spacer module for sensor/actuator box; 8-way

1.1.3 Marking

1.1.3.1 Marking device



Item No.: 210-110
Fiber-tip pen



1.1.3.2 Marking strip



Item No.: 757-011
Marker card; not stretchable; snap-on type