
Part Number : 2218919301
Product Description : EXTreme Ten60Power Board-to-Board Vertical Plug Assembly with Guide Pins, 1 Split Power Circuit
Series Number : 221891
Status : Active
Product Category : Board-to-Board Connectors



Documents and Resources

Drawings

2218919301_sd.pdf

2218919301-PK-000.pdf

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

2218910001-AS-000.pdf

2218910000-PS-000.pdf

2218910002-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	221891
Description	EXTreme Ten60Power Board-to-Board Vertical Plug Assembly with Guide Pins, 1 Split Power Circuit
Application	Board-to-Board, Mezzanine
Component Type	Plug
Keyword	Ten60
Product Name	EXTreme Ten60Power
UPC	196823594533

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	60.0A
Voltage - Maximum	125V / 250V

Physical

Breakaway	No
Circuits (Loaded)	1

Downloaded from Arrow.com.

Circuits (maximum)	1
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Side, Yes
Keying to Mating Part	No
Lock to Mating Part	No
Mated Height	21.23mm
Material - Metal	High Conductivity Copper
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer (LCP)
Net Weight	5.017/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	No
PCB Thickness - Recommended	1.58mm
Pitch - Mating Interface	6.00mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
(p)ower-(s)ignal Configuration	1sp - 0s
Shrouded	Unshrouded
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole - Compliant Pin

Mates With / Use With

Mates with Part(s)

Downloaded from Arrow.com.

Description	Part Number
EXTreme Ten60Power Vertical Receptacle with Guides, 1 Split Power Circuit	2218929301

This document was generated on Aug 08, 2026

Downloaded from Arrow.com.