
3.0V Radial Supercapacitors



ADCR-S03R0S

Request Samples Check Inventory

Various Sizes
RoHS/RoHS II Compliant
MSL Level = 1

Features

- High Voltage 3.0V Series
- High power density
- Minimal discharge rate, 72 hours @ discharge<20%
- Excellent cycle life
- Green, meet RoHS requirements.

Applications

- Power Assist Circuits
- Power Backup
- Micro Energy Storage
- IoT Energy Harvesting
- SSD applications
- DDR power back up
- RTC System power transfer to battery backup

Electrical Specifications

Part Number	Nominal Voltage (U_R)	Capacitance	Tol.	ESR (Max)	Nominal Current	Peak Current (Max)	Leakage Current	Stored Energy (Max)	Gravimetric Energy Density	Power Density	Volumetric Energy Density
ADCR-S03R0S	DC(V)	Farads	±%	mΩ	A	A	mA	mWh	Wh/kg	kW/kg	Wh/L
ADCR-S03R0SA105MB	3.0V	1	±20	350	0.28	1.11	0.008	1.25	1.37	3.53	1.91
ADCR-S03R0SA305MB	3.0V	3	±20	120	0.84	3.31	0.013	3.75	2.82	4.05	3.73
ADCR-S03R0SA335MB	3.0V	3.3	±20	120	0.92	3.55	0.013	4.13	1.77	4.02	4.11
ADCR-S03R0SA505MB	3.0V	5	±20	80	1.39	5.36	0.016	6.25	4.40	9.90	5.18
ADCR-S03R0SB505MB	3.0V	5	±20	75	1.40	5.45	0.016	6.25	4.03	9.68	3.98
ADCR-S03R0SA605MB	3.0V	6	±20	75	1.65	6.21	0.024	7.50	4.21	8.43	4.77
ADCR-S03R0SA605QB	3.0V	6	-10/+30	75	1.65	6.21	0.024	7.50	4.21	8.43	4.77
ADCR-S03R0SA106MB	3.0V	10	±20	65	2.65	9.09	0.032	12.50	5.71	7.90	6.37
ADCR-S03R0SA156MB	3.0V	15	±20	55	3.86	12.33	0.052	18.75	7.08	7.72	6.11
ADCR-S03R0SA256MB	3.0V	25	±20	30	6.52	21.43	0.075	31.25	5.04	6.05	6.22
ADCR-S03R0SA306MB	3.0V	30	±20	30	7.63	23.68	0.075	37.50	5.15	5.15	6.22

Operating Temperature: -40°C to +65°C
Storage: Temperature -30°C to +50°C, RH<60%, Max. Humidity <85% RH
Test Conditions: +25°C

All parameters are measured according to the IEC 62391-1 standard.
Capacitance and ESR are measured with $I(mA)= 8(C*U_R)$

Maximum Surge Voltage: 3.15V ≤ 30 seconds
Nominal Current: 5 Seconds to discharge from U_R to $1/2U_R$
Peak Current (Max.): 1 second to discharge to U_R to $1/2U_R$
Leakage Current: Measured after 72h at U_R


ABRACON
12117 Bee Caves Rd, Bldg-3, Suite 200
Bee Cave, TX 78738
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION E : 9/10/2026

ABRACON IS ISO9001-2015 CERTIFIED

Downloaded from Arrow.com.

3.0V Radial Supercapacitors




ADCR-S03R0S

Request Samples | Check Inventory

Various Sizes
RoHS/RoHS II Compliant
MSL Level = 1

Mechanical Specifications



Dimensions	D	L	P	d
ADCR-S03R0SA105MB	8±1.0	13±1.5	3.5±0.5	0.6±0.05
ADCR-S03R0SA305MB	8±1.0	20±1.5	3.5±0.5	0.6±0.05
ADCR-S03R0SA335MB	8±1.0	20±1.5	3.5±0.5	0.6±0.05
ADCR-S03R0SA505MB	8±1.0	24±1.0	3.5±0.5	0.6±0.05
ADCR-S03R0SB505MB	10±1.0	20±1.5	5.0±0.5	0.6±0.05
ADCR-S03R0SA605MB	10±1.0	20±1.5	5.0±0.5	0.6±0.05
ADCR-S03R0SA605QB	10±1.0	20±1.5	5.0±0.5	0.6±0.05
ADCR-S03R0SA106MB	10±1.0	25±2.0	5.0±0.5	0.6±0.05
ADCR-S03R0SA156MB	12.5±1.0	25±2.0	5.0±0.5	0.6±0.05
ADCR-S03R0SA256MB	16±1.0	25±2.0	7.5±0.5	0.8±0.05
ADCR-S03R0SA306MB	16±1.0	30±2.0	7.5±0.5	0.8±0.05

Dimensions: mm

ABRACON


12117 Bee Caves Rd, Bldg-3, Suite 200
Bee Cave, TX 78738
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION E : 9/10/2026

ABRACON IS
ISO9001-2015
CERTIFIED

Downloaded from Arrow.com.

3.0V Radial Supercapacitors



ADCR-S03R0S

Request Samples | Check Inventory

Various Sizes
RoHS/RoHS II Compliant
MSL Level = 1

Part Number Identification

ADCR – S [ ] [ ] [ ] [ ] [ ] [ ]

VDC
03R0: 3.0V

Rating
S: Standard

Dimensions Options*
A
B

Capacitance*
Refer to Electrical Specification table
E.g., 505: 50 x10^5 = 5F

Tolerance*
M: ±20%
Q: -10/+30

Packaging
B: Bulk

*Only part numbers listed in the Electrical Specs table are available. For custom builds, please contact us.

Part Marking



Example of the Markings of a 1.0F 3.0V capacitor

Capacitance (F)
Rated Voltage (V)
Polarity (negative bar on the sleeve to indicate the cathode)

ABRACON


12117 Bee Caves Rd, Bldg-3, Suite 200
Bee Cave, TX 78738
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION E : 9/10/2026

ABRACON IS
ISO9001-2015
CERTIFIED

Downloaded from Arrow.com.

3.0V Radial Supercapacitors




ADCR-S03R0S

Request Samples | Check Inventory

Various Sizes
RoHS/RoHS II Compliant
MSL Level = 1

Wave Soldering Profile



Zone	Description	Temperature	Times
1	Preheat	T_{SMIN} ~ T_{SMAX} 25°C ~ 130°C	80 sec. MAX
	Preheat Rate	$T_{PREHEAT}$ +4ºC/Sec MAX	
2	Wave Temperature	T_w 245°C ~ 260°C	10 sec. MAX Dual wave
	Wave Peak Temperature	T_P 260°C	5 sec. MAX/wave
3	Cooling Rate	$T_{COOLING}$	-5ºC/Sec MAX

ABRACON


12117 Bee Caves Rd, Bldg-3, Suite 200
Bee Cave, TX 78738
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION E : 9/10/2026

ABRACON IS
ISO9001-2015
CERTIFIED

Downloaded from Arrow.com.

3.0V Radial Supercapacitors



ADCR-S03R0S

Request Samples | Check Inventory

Various Sizes
RoHS/RoHS II Compliant
MSL Level = 1

Packaging

The product is packaged in a carton containing multiple inner boxes, each containing several trays.

Part Number	Quantity (PCS/Tray)	Quantity (PCS/Bundle)
ADCR-S03R0SA105MB	160	960
ADCR-S03R0SA305MB	120	720
ADCR-S03R0SA335MB	120	720
ADCR-S03R0SA505MB	100	600
ADCR-S03R0SB505MB	120	600
ADCR-S03R0SA605MB	120	600
ADCR-S03R0SA605QB	120	600
ADCR-S03R0SA106MB	80	400
ADCR-S03R0SA156MB	60	240
ADCR-S03R0SA256MB	50	200
ADCR-S03R0SA306MB	50	200

Transport of Product

This product is not subject to US DOT or IATA regulations UN3499 since maximum stored energy is below 10Wh and can be considered Non-Hazardous Goods. Please refer to the Abracon | UN/IATA Transportation Guidelines for more information.

ATTENTION: Abracon LLC's products are Commercial-Off-The-Shelf (COTS, which are designed, intended and validated for use in commercial, industrial and automotive applications. The customer is responsible for testing and verifying the performance of an Abracon solution to meet their system-level requirements.

ABRACON

12117 Bee Caves Rd, Bldg-3, Suite 200
Bee Cave, TX 78738
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION E : 9/10/2026

ABRACON IS ISO9001-2015 CERTIFIED

Downloaded from Arrow.com.