
Part Number : 1201080201
Product Description : Micro-Change (M12) Double-Ended Cordset, 4 Poles, D-Coded Male (Straight) to Male (90°), 22 AWG, Shielded PUR Cable, 2.0m (6.56') Length
Series Number : 120108
Status : Obsolete
Product Category : Industrial Cable Assemblies
Engineering Part Number : E11A06211M020



Documents and Resources

Drawings

1201080201_sd.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Obsolete

Downloaded from Arrow.com.

Part Details

General

Status	Obsolete
Category	Industrial Cable Assemblies
Series	120108
Description	Micro-Change (M12) Double-Ended Cordset, 4 Poles, D-Coded Male (Straight) to Male (90°), 22 AWG, Shielded PUR Cable, 2.0m (6.56') Length
IP Rating	IP67
Performance Category	5e
Product Name	Micro-Change (M12)
Type	Double Ended
UPC	78172535390

Agency

UL	E361772

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	30V

Physical

Cable Diameter	6.70mm (.264")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Green
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
Coupling Style	Threaded
Gender	Male-Male
Keyway	D-Coded
LED Indicator	None
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Contact	Copper Alloy

Obsolete

Downloaded from Arrow.com.

Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	186.765/g
Orientation	90° to Straight
Poles	4
Temperature Range - Operating	-20° to +60°C
Wire/Cable Type	Shielded PUR
Wire Size (AWG)	22

Obsolete

Downloaded from Arrow.com.