**Part Number :** 740990607
**Product Description :** SL Wire-to-Board Header, Surface Mount, Single Row, Vertical, 7 Circuits, Tin (Sn) Plating, Tape and Reel, with Pick-and-Place Cap
**Series Number :** 74099
**Status :** Active
**Product Category :** PCB Headers and Receptacles



## Documents and Resources

### Drawings

740990607_sd.pdf

PK-70873-9000-001.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

### Specifications

PS-70400-001.pdf

PS-70541-001.pdf

TS-70541-100-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | PCB Headers and Receptacles |
| Series | 74099 |
| Description | SL Wire-to-Board Header, Surface Mount, Single Row, Vertical, 7 Circuits, Tin (Sn) Plating, Tape and Reel, with Pick-and-Place Cap |
| Application | Wire-to-Board |
| Component Type | PCB Header |
| Product Name | SL |
| UPC | 887191449852 |

### Agency

| | |
|---|---|
| CSA | LR19980 |
| UL | E29179 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 3.0A |
| Voltage - Maximum | 250V |

### Physical

| | |
|---|---|
| Breakaway | No |

Downloaded from Arrow.com.

| | |
|---|---|
| Circuits (Loaded) | 7 |
| Circuits (maximum) | 7 |
| Color - Resin | Black |
| Durability (mating cycles max) | 25 |
| First Mate / Last Break | No |
| Gender | Male |
| Glow-Wire Capable | No |
| Material - Metal | Phosphor Bronze |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Material - Resin | High Temperature Thermoplastic |
| Net Weight | 1.586/g |
| Number of Rows | 1 |
| Orientation | Vertical |
| Packaging Type | Embossed Tape on Reel |
| PCB Thickness - Recommended | 1.57mm |
| Pitch - Mating Interface | 2.54mm |
| Pitch - Termination Interface | 2.54mm |
| Plating min - Mating | 3.810µm |
| Plating min - Termination | 3.810µm |
| Polarized to Mating Part | Yes |
| Shrouded | Shrouded |
| Temperature Range - Operating | -40° to +105°C |
| Termination Interface Style | Surface Mount |

### Solder Process Data

| | |
|---|---|
| Max-Duration | 40 |
| Lead-Free Process Capability | REFLOW |
| Max-Cycle | 3 |
| Max-Temp | 245 |

---

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|

Downloaded from Arrow.com.

| | |
|---|---|
| SL Single Row Crimp Housings and CPA Retainers | 70066 |
| SL Single Row Female Insulation Displacement Connector Assemblies | 70400 |
| SL Single Row Female Receptacles | 70430 |

**Use with Part(s)**

| Description | Part Number |
|---|---|
| SL Female Terminals | 70058 |
| SL Female Terminals | 71851 |



Downloaded from Arrow.com.